



Connectors > Lighting Connectors > Ballast Connectors



Number of Positions: 3

Lighting Product Type: **Connector**

Termination Method to Wire & Cable: **Poke-In**

Connector System: **Wire-to-Wire**

Centerline (Pitch): **4.5 mm**

Features

Electrical Characteristics

Operating Voltage (Max)	600 VAC
-------------------------	---------

Industry Standards

UL Flammability Rating	UL 94V-0
Compatible With Approved Standards Products	UL 1977

Body Features

Primary Product Color	Natural
-----------------------	---------

Mechanical Attachment

Mating Alignment	With
------------------	------

Packaging Features

Packaging Method	Loose Piece
Packaging Quantity	500

Configuration Features

Number of Rows	1
----------------	---



Number of Positions	3
---------------------	---

Product Type Features

Lighting Product Type	Connector
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Termination Features

Termination Method to Wire & Cable	Poke-In
------------------------------------	---------

Contact Features

Contact Current Rating (Max)	9 A
------------------------------	-----

Housing Features

Centerline (Pitch)	4.5 mm
--------------------	--------

Dimensions

Wire Size	16 – 22 AWG
-----------	-------------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2834054-2
PLUG, 3P LATCHED POKE-IN WTW
CONN.BK

Also in the Series | LIGHT-N-LOK Ballast Connector



Ballast Connectors(36)


Customers Also Bought



TE Part #2213362-4
RCPT ASSY, DIMMABLE
PHOTOCONTROL, 105C, 3/4



TE Part #2213194-1
LUMAWISE LED HOLDER OPTIC CLIP
Z50 TYPE1



TE Part #2834049-1
REC, 2P LATCHED POKE-IN WTW
CONN.NL



TE Part #41771-1
250 FASTON REC 22-18 AWG BR



TE Part #61988-1
250 FASTON REC 22-18 AWG BR

TE Part #2834055-4
REC, 3P LATCHED POKE-IN WTW CONN.RD

TE Part #2325807-2
LUMAWISE Z45 LED HOLDER 19X19

TE Part #2834054-1
PLUG, 3P LATCHED POKE-IN WTW CONN.NL

TE Part #843032-000
101A041-3-0

TE Part #1742906-1
GROUNDING CLIP 18-14 020 SST

Documents

Product Drawings

REC, 3P LATCHED POKE-IN WTW CONN.BK

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2834055-2_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2834055-2_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2834055-2_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

3 Position LIGHT-N-LOK Connector

English

LIGHT-N-LOK Brochure

English

3P Latched W2W Connector (Chinese)

English

Product Specifications



Application Specification

English

Instruction Sheets

Instruction Sheet (non U.S.)

English

Agency Approvals

LIGHT-N-LOK CB Test Certificate to IEC 61984

English

LIGHT-N-LOK CB Test Report to IEC 61984

English