




AMP-LATCH

TE Internal #: 1-1658527-5
Wire-to-Board, 50 Position, 2.54 mm [.1 in] Centerline, 2 Row,
Receptacle, Wire & Cable, Signal, Cable Mount (Free-Hanging),
Ribbon Cable Connectors

[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > Ribbon Cable Connectors



Connector System: **Wire-to-Board**
Number of Positions: **50**
Centerline (Pitch): **2.54 mm [.1 in]**
Row-to-Row Spacing: **2.54 mm [.1 in]**
Number of Rows: **2**

Features

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Body Features

Primary Product Color	Blue
-----------------------	------

Contact Features

Contact Mating Area Plating Material	Gold
Wire Contact Termination Area Plating Thickness	.127 µm[5 µin]
	30 µin
Wire Contact Termination Area Plating Material	Gold Flash
Mating Square Post Dimension	.64 mm[.025 in]
Contact Current Rating (Max)	1 A

Product Type Features

Connector Product Type	Connector Assembly
Connector System	Wire-to-Board
Connector & Housing Type	Receptacle













Connector & Contact Terminates To	Wire & Cable
Configuration Features	
Number of Positions	50
Number of Rows	2
Mechanical Attachment	
Mating Alignment Type	Polarization
Mating Retention	Without
Connector Mounting Type	Cable Mount (Free-Hanging)
Housing Features	
Centerline (Pitch)	2.54 mm[.1 in]
Dimensions	
Row-to-Row Spacing	2.54 mm[.1 in]
Usage Conditions	
Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
Operation/Application	
Circuit Application	Signal
Other	
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant
Product Compliance	
For compliance documentation, visit the product page on TE.com>	
EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability




Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


 TE Part # 1-5103308-0 A/L LOW PRO HDR 50P VERT BLACK	 TE Part # 1-1761681-5 IDC LOW PRO HDR 50P VERT HT BLACK	 TE Part # 3-1761712-5 IDC LOW PRO HDR 50P RA LG LAT BLACK	 TE Part # 3-1761606-5 IDC LOW PRO HDR 50P VERT LG LA
 TE Part # 1-111446-7 50 UNIV I/O, NO EARS,LEAD FREE	 TE Part # 3-1761603-5 IDC LOW PRO HDR 50P VERT BLUE	 TE Part # 1-1761606-5 IDC LOW PRO HDR 50P VERT LG LA	 TE Part # 1-5103310-0 A/L LOW PRO HDR 50P RA BLACK
 TE Part # 1-5103311-0 A/L LOW PRO HDR 50P RA BLACK	 TE Part # 3-1761605-5 IDC LOW PRO HDR 50P RA BLUE	 TE Part # 1-1761686-5 IDC LOW PRO HDR 50P VERT LG LAT	 TE Part # CAT-AM74-UN384H AMP-LATCH UNIVERSAL HEADERS




TE Part # 3-1761711-5
IDC LOW PRO HDR 50P VERT LG LA




TE Part # 1-5103309-0
A/L LOW PRO HDR 50P VERT BLACK



TE Part # 1-1761607-5
IDC LOW PRO HDR 50P RA LG LAT BLK




TE Part # 104128-9
050 LOPRO HDR SP 30DP LATCH BLK




TE Part # 5104338-9
A/L LOW PRO HDR 50P VERT HT



TE Part # 5104340-9
A/L LOW PRO HDR 50P RA HT



TE Part # 1-111506-4
50 UNIV I/O, SLOTTED, LEAD FREE




TE Part # 3-1761607-5
IDC LOW PRO HDR 50P RA LG LAT

Customers Also Bought



TE Part #1734577-4
MOD-JK,8P8C,SHD W/LED, G/Y,50U"



TE Part #1658525-3
622-5053LF, PCB IDC, LEAD FREE



TE Part #1676223-2
RN 0805 1K15 0.1% 10PPM 1KRL




TE Part #1-1879496-3
CRGH0805 5% 39K 0.33W



TE Part #1676280-2
RN 0805 29K4 0.1% 10PPM 1KRL



TE Part #1-1676123-0
1/2W SM M/OX 5% 2R0




TE Part #1445251-1
ORGANIZER PC/104



TE Part #6-1622796-4
YR1 0.1% 154R



TE Part #2-1879451-1
TE 600W 47R 5% Bracket



TE Part #5-2176474-7
RA73F 1J 2K1 0.1% 1K RL

Documents



Product Drawings

622-5041LF FEM SOCKT,LEAD FREE

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1658527-5_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1658527-5_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1658527-5_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Ribbon Cable Interconnect Solutions

English

Instruction Sheets

Instruction Sheet (U.S.)

English