






2 Pin样式



SECTION A-A



Part No	Pin	A	B
WAFER-XH2.54-2PZZ-Y62	2	2.5	7.5
WAFER-XH2.54-3PZZ-Y62	3	5.0	10.0
WAFER-XH2.54-4PZZ-Y62	4	7.5	12.5
WAFER-XH2.54-5PZZ-Y62	5	10.0	15.0
WAFER-XH2.54-6PZZ-Y62	6	12.5	17.5
WAFER-XH2.54-7PZZ-Y62	7	15.0	20.0
WAFER-XH2.54-8PZZ-Y62	8	17.5	22.5
WAFER-XH2.54-9PZZ-Y62	9	20.0	25.0
WAFER-XH2.54-10PZZ-Y62	10	22.5	27.5
WAFER-XH2.54-11PZZ-Y62	11	25.0	30.0
WAFER-XH2.54-12PZZ-Y62	12	27.5	32.5
WAFER-XH2.54-13PZZ-Y62	13	30.0	35.0
WAFER-XH2.54-14PZZ-Y62	14	32.5	37.5
WAFER-XH2.54-15PZZ-Y62	15	35.0	40.0
WAFER-XH2.54-16PZZ-Y62	16	37.5	42.5



适用线路板(PCB LAYOUT)

序号	品名	材质
1	XH2.5 胶芯	PA66 UL94V-2 Beige
2	XH2.5 直针 端子	Copper Alloy/ Tin Plating

Technical Index:

1. Temperature range: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
2. Rated voltage: 250V DC/AC(rms).
3. Rated current: 3.0A.
4. Contact resistance: $\leq 20\text{m}\Omega$.
5. Withstanding voltage: 1000V AC/minute.
6. Insulation resistance: $\geq 1000\text{M}\Omega$.

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: XH2.5 直针	
DECIMALS:		PAR	WAFER-XH2.54-NPZZ-Y62
ANGLES:		DWN	
X.:±0.50		CHKD	
X.X':±0.20		APVD	
.XX:±0.10		SCALE:1:1	UNIT:MM
X.XX':±1°		SIZE:A4	SHEET:1F1
CUSTOMER COPY			REV:A