




Connectors > Automotive Connectors > Automotive Connector Accessories > Automotive Connector EMC Shielding >
DT Highspeed Connector Shielding



Connector Shielding Accessory Type: **Ferrule**
Primary Product Material: **Copper Alloy**
EU RoHS Compliance: **Compliant**
EU ELV Compliance: **Compliant**

[All DT Highspeed Connector Shielding \(5\)](#)

Features

Configuration Features

Number of Positions	2
---------------------	---

Usage Conditions

Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]
-----------------------------	----------------------------

Product Type Features

Sealable	Yes
Connector Shielding Accessory Type	Ferrule

Body Features

Primary Product Material	Copper Alloy
--------------------------	--------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 9-2383999-1
4POS,DIA 1MM,PIN HSG ASSY,SLD




TE Part # CAT-AI5-DHCH
DT Highspeed Connector Housing



TE Part # 2399600-1
SDE DT Highspeed Ferrule 0.50 mm Tool



TE Part # 2399600-2
SDE DT Highspeed Ferrule 0.50 mm Die Set



TE Part # CAT-AI5-DHCS
DT Highspeed Connector Shielding



Also in the Series

DEUTSCH DT Highspeed

Automotive Connector EMC Shielding(5)	Automotive Headers(3)	Automotive Housings(2)	Infotainment & Multimedia Cable Assemblies(15)
Other Automotive Connector Accessories(6)	PCB Headers & Receptacles(3)	Wire-to-Board Headers & Receptacles(1)	

Customers Also Bought

TE Part #9-2367345-1 SOC CONN CVR ASSY,2POS,CSS SIZE 20,180	TE Part #9-2367346-1 SWS,HSD,CVTY DIA,RECTANGULAR	TE Part #9-2370714-1 CU ALLOY,SHIELD ASSY,CONN HSG, DATA DT	TE Part #1623929-2 CFR200 5% 100R
TE Part #7-1625892-1 3W SM M/OX 5% 820R	TE Part #6-1879664-5 H8 5K36 0.1% 15PPM	TE Part #1622521-1 LR1 1% 56R	TE Part #2292865-3 AS16,CAP BACKSHELL KIT,ST,12P, NC16
TE Part #9-2367337-1 2POS,CSS SIZE 20,SOC OUTER HSG ASSY,SLD	TE Part #282520-000 44A0311-18-0-US		



Documents

Product Drawings

CU ALLOY,OUTER FERRULE,DATA DT

English

CAD Files

Customer View Model

ENG_CVM_CVM_9-2370624-1_A1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_9-2370624-1_A1.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_9-2370624-1_A1.3d_igs.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English