




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Tab**

Wire Size: **.32 – .82 mm²**

Mating Tab Width: **2.8 mm [.11 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Industry Standards

Compatible With Agency/Standards Products	UL
---	----

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Other

Line	FASTON .110
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Packaging Features

Packaging Quantity	4000
--------------------	------



Packaging Method

Strip/Reel

Dimensions

Product Length	13.2 mm[.52 in]
Compatible Insulation Diameter Range	3 mm[.118 in]
Terminal Material Thickness	.4 mm[.015 in]
Wire Size	.32 – .82 mm²

Contact Features

Quick Disconnect Terminal Type	Tab
Mating Tab Width	2.8 mm[.11 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Unplated
Crimp Type	F-Crimp
Barrel Type	Open

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 42475-2 250 FASTON TAB 22-18 AWG TPBR	 TE Part # 42475-3 250 FASTON TAB 22-18 AWG BR	 TE Part # 4151105-1 OCEAN-2.0-APPLICATOR-S-080F136F-RSM	 TE Part # 42475-4 250 FASTON TAB 22-18 AWG TPBR
 TE Part # 42490-4 187 FASTON TAB 22-18 AWG BR	 TE Part # 1494210-2 110 FASTON,TAB,22-17 AWG, JIS C260	 TE Part # 63165-2 FASTON 110 AMPLIVAR TAB 23-19 MAG TPBR	 TE Part # 4151105-2 OCEAN-2.0-APPLICATOR-S-080F136F-RSA
 TE Part # 7-4151105-7 OCEAN_2.0_SPARE_PART_KIT-080F136F	 TE Part # 63535-1 TAB SPECIAL 025TPBR	 TE Part # 61281-3 250 FASTON TAB 14-12 AWG TPBR	 TE Part # 63932-1 110 FASTON TAB 22-18 AWG TPBR
 TE Part # 63138-1 110 FASTON REC 22-18 AWG TPBR	 TE Part # 1742753-1 FASTON 2MM TAB 18-22AWG TPBR	 TE Part # 42474-3 250 FASTON TAB 18-14 AWG BR	



Also in the Series | **FASTON 110**

Crimp Terminal Housings(13)	Insertion & Extraction Tools(1)	PCB Terminals(22)	Quick Disconnects(168)

Customers Also Bought

 TE Part #1494212-1 SIZE(2.8) AMPLIVAR FASTON RECP	 TE Part #1494209-1 FASTON 110 20-24AWG CUNI	 TE Part #1494218-1 110 FASTON,FLAG,TAB,18-22 AWG, BR	 TE Part #1494219-1 110 FASTON,REC.,18-22 AWG,BR
 ANVIL TE Part #1803591-1 ANVIL, WIRE F	 CRIMPER, INSUL O PREMIUM TE Part #2119784-3	 CRIMPER, WIRE .062 F PREMIUM TE Part #7-456403-0	 TE Part #1878643-3 M5031
 TE Part #2161282-1 AMP 3K/5K CPU BOARD ASSEMBLY	 TE Part #5-456403-8 CRIMPER, WIRE .062F PREMIUM		

Documents

Product Drawings
110 FASTON,TAB,22-17 AWG, JIS C260

English

CAD Files
3D PDF
3D



Customer View Model

[ENG_CVM_CVM_1494210-1_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1494210-1_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1494210-1_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Agency Approvals

[Agency Approval Document](#)

English