




Connectors > Connector Accessories > Connector Backshells



Connector Backshell Product Style: **Shielded**
Connector Backshell Product Type: **Backshell**
Primary Product Material: **Zinc**
Body Orientation: **Straight**
Compatible With Connector Shell Size: **4**

Features

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Dimensions

Compatible Insulation Diameter Range	4 – 13 mm[.197 – .433 in]
--------------------------------------	---------------------------

Mechanical Attachment

Thread Size	4-40
-------------	------

Packaging Features

Packaging Method	Bag
Packaging Quantity	100

Body Features

Cable Exit Angle	45°
Primary Product Material	Zinc
Primary Product Plating Material	Nickel

Product Type Features

Connector Backshell Product Style	Shielded
-----------------------------------	----------



Connector Backshell Product Type

Backshell

Housing Features

Body Orientation	Straight
Compatible With Connector Shape	D-Shaped

Operation/Application

Compatible With Connector Shell Size	4
--------------------------------------	---

Configuration Features

Number of Positions	37
---------------------	----

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 1534811-1
HD20 COVER KIT 37 POS WITH CABLE CLAMPS

TE Part # 3-2198618-7
Ni Pltd Plstic Backshell, 37 Way, 45 Deg

Customers Also Bought

TE Part #5746881-1
MALE SCREW RETAINER KIT

TE Part #1879663-4
H8 115R 0.1% 15PPM

TE Part #1879665-7
H8 14K3 0.1% 15PPM

TE Part #2174100-1
CAP HOUSING ASSEMBLY 130 POS 0.5 /1.0

TE Part #C795573001
44A0111-24-9CK0300

TE Part #CD61243001
44A0111-22-9CK0300

TE Part #CD61283001
44A0111-26-9CK0300

TE Part #CD61183001
44A0111-20-9CK0300

TE Part #E247363001
44A0111-24-9CK2000

TE Part #2174100-2
CAP HOUSING ASSEMBLY 130 POS 0.5 /1.0

Documents

Product Drawings

METAL BACKSHELL 37 WAY 45 DE

English

METAL BACKSHELL 37 WAY 45 DE

English

CAD Files



Customer View Model

[ENG_CVM_CVM_3-1478763-7_G.2d_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_3-1478763-7_G.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-1478763-7_G.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.