




PIDG

TE Internal #: 36151
Closed Ring Tongue Terminal, 22 – 16 AWG, #6 / M3.5 Stud, 3.68 mm [.145 in] Stud Diameter, Closed Barrel, Straight, Tin Plating, PIDG

[View on TE.com >](#)

Terminals & Splices > Ring Terminals > PIDG Ring Tongue Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: 509 – 3260 CMA

Stud Size: #6, M3.5

[All PIDG Ring Tongue Terminals \(410\)](#)

Features

Configuration Features

Number of Holes	1
-----------------	---

Body Features

Product Weight	.843 g
----------------	--------

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Electrical Characteristics

Voltage Rating	300 V
----------------	-------

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	1000
Packaging Method	Loose Piece

Product Type Features

--	--



Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	#6, M3.5
Sealable	No
Wire Insulation Support Retention Type	Insulation Support

Contact Features

Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Tin

Dimensions

Wire Size	509 – 3260 CMA
Stud Diameter	3.68 mm [.145 in]
Tongue Thickness	.79 mm [.031 in]
Product Length	20.24 mm [.797 in]
Compatible Insulation Diameter (Max)	3.18 mm [.125 in]
Compatible Insulation Diameter Range	2.03 – 3.18 mm [.08 – .125 in]

Usage Conditions

Insulation Option	Partially Insulated
-------------------	---------------------

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC



Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2392021-1 RED BATTERY DAHT KIT 110V (47689-4)	TE Part # 539691-2 ERGO DIE R.B.Y	TE Part # 169404 CERTI-LOK DIE	TE Part # 2063030-1 SDE DIESET, RBY, UL
TE Part # 2392021-2 RED BATTERY DAHT KIT 220V (47689-4)	TE Part # 47806-2 DIES PIDG 22-16 DIE SET	TE Part # 58423-1 DIE, RBY IS9252	TE Part # 47386 DAHT PG PIDG 26-16 ASSY
TE Part # 58433-3 PRO CR ASSY, RBY IS9252	TE Part # 47386-4 DAHT PG PIDG 26-16 ASSY	TE Part # 59300 T-HEAD PIDG PG 26-16 ASSY	TE Part # 525690 DAHT PG PIDG 20-18 ASSY



TE Part # 59824-1
TETRA-CRIMP PIDG PG FASTON 22-10 ASSY



TE Part # 169400
CERTI-LOK FRAME W/O DIES




TE Part # 59250
T-HEAD PIDG 26-14 ASSY

Also in the Series | PIDG



Compression Connectors(17)



Crimp Wire Pins, Tabs & Ferrules(41)



Hand Crimping Tools(2)




Knife Disconnects(11)



Quick Disconnects(38)



Ring Terminals(588)



Spade Terminals(228)



Special Purpose Terminals(1)



Splices(41)

Customers Also Bought



TE Part #644875-5
05P MTA100 HDR ASSY F/L,SP BND



TE Part #EK8084-000
ZH150-3/1.5-0-10M



TE Part #1-1337430-0
BNC Str Plg Hex 50Ohm Silver Pltd RG174A



TE Part #A55157-000
HX-SCE-38.1-50-S1-4





TE Part #E11046-000
55PC1121-16-2/6-9



TE Part #1-1609157-1
12HPEND1-HG=F8572

TE Part #2-1589678-8
NCG00711041PC2DC006 = CIRCULAR

TE Part #AAC6493-00
100P3307H3-15-20-1-B

TE Part #104113-E
ERMB 125 FS 1 EE * 3,70 A-E V-V ** 247

TE Part #52027-8-35PN
HERM RECP

Documents

Product Drawings

PIDG R 22-16 COMM 22-18 MIL 6

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_36151_T.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_36151_T.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_36151_T.3d_stp.zip

English

Customer View Model

ENG_CVM_36151_M.3d_igs.zip

English

Customer View Model

ENG_CVM_36151_M.3d_stp.zip

English

Customer View Model

ENG_CVM_36151_M.2d_dxf.zip

English

3D PDF

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages
PIDG TERMINALS & SPLICES Quick Reference Guide
English

Instruction Sheets
Instruction Sheet (U.S.)
English

Agency Approvals
UL Report
English