

6W isolated DC-DC converter in DIP package  
Ultra-wide input and regulated dual/single output



Patent Protection  
CE Report CB RoHS  
EN62368-1 IEC60950-1

## FEATURES

- Ultra-wide 4:1 input voltage range
- High efficiency up to 88%
- No-load power consumption as low as 0.12W
- I/O isolation test voltage 1.5k VDC
- Operating ambient temperature range: -40°C to +85°C
- Input under-voltage, output over-voltage, short-circuit, over-current protection
- Meets CISPR32/EN55032 CLASS A, without extra components
- Industry standard pin-out

*URA\_ZP-6WR3 & URB\_ZP-6WR3 series of Isolated 6W DC-DC converter products with an ultra-wide range of voltage input of 9-36VDC(24VDC input), 18-75VDC(48VDC input), input to output isolation is tested with 1500VDC, input under-voltage protection, output over-voltage, short-circuit, over-current protection. They meet CLASS A of CISPR32/EN55032 EMI standards without external components and they are widely used in fields such as industrial control, electric power, instruments, communication and railway applications.*

## Selection Guide

Certification	Part No.	Input Voltage (VDC)		Output		Full Load Efficiency <sup>②</sup> (%) Min./Typ.	Capacitive Load <sup>③</sup> (μF)Max.
		Nominal (Range)	Max. <sup>①</sup>	Voltage (VDC)	Current (mA) Max./Min.		
EN/IEC	URA2405ZP-6WR3	24 (9-36)	40	±5	±600/0	80/82	680
	URA2409ZP-6WR3			±9	±333/0	82/84	220
	URA2412ZP-6WR3			±12	±250/0	83/85	330
	URA2415ZP-6WR3			±15	±200/0	86/88	220
	URA2424ZP-6WR3			±24	±125/0	84/86	100
	URB2403ZP-6WR3			3.3	1500/0	75/77	1800
	URB2405ZP-6WR3			5	1200/0	80/82	1000
	URB2409ZP-6WR3			9	667/0	81/83	1000
	URB2412ZP-6WR3			12	500/0	83/85	470
	URB2415ZP-6WR3			15	400/0	84/86	220
	URB2424ZP-6WR3			24	250/0	84/86	100
EN/IEC	URA4805ZP-6WR3	48 (18-75)	80	±5	±600/0	81/83	680
	URA4812ZP-6WR3			±12	±250/0	85/87	330
	URA4815ZP-6WR3			±15	±200/0	86/88	220
	URB4803ZP-6WR3			3.3	1500/0	78/80	1800
	URB4805ZP-6WR3			5	1200/0	82/84	1000
	--			9	667/0	83/85	680
	URB4809ZP-6WR3			12	500/0	85/87	470
	URB4812ZP-6WR3			15	400/0	86/88	220
	URB4824ZP-6WR3			24	250/0	85/87	100

Notes:

①Exceeding the maximum input voltage may cause permanent damage;

②Efficiency is measured at nominal input voltage and rated output load;

③The specified maximum capacitive load for positive and negative output is identical.

## Input Specifications

Item	Operating Conditions	Min.	Typ.	Max.	Unit
Input Current (full load / no-load)	24VDC input	--	302/5	333/12	mA
	48VDC input	--	156/4	160/8	
Reflected Ripple Current		--	20	--	

Surge Voltage (1sec. max.)	24VDC input	-0.7	--	50	VDC
	48VDC input	-0.7	--	100	
Start-up Voltage	24VDC input	--	--	9	
	48VDC input	--	--	18	
Input Under-voltage Protection	24VDC input	5.5	6.5	--	
	48VDC input	12	15.5	--	
Input Filter			Pi filter		
Hot Plug			Unavailable		

### Output Specifications

Item	Operating Conditions		Min.	Typ.	Max.	Unit
Voltage Accuracy <sup>①</sup>	Vo1		--	$\pm 1$	$\pm 3$	%
	Vo2					
Balance Of Output Voltage	Dual output, balanced load		--	$\pm 0.5$	$\pm 1.5$	
Linear Regulation	Input voltage variation from low to high at full load	Vo1	--	$\pm 0.2$	$\pm 0.5$	
		Vo2	--	$\pm 0.5$	$\pm 1$	
Load Regulation <sup>②</sup>	5%-100% load	Vo1	--	$\pm 0.5$	$\pm 1$	
		Vo2	--	$\pm 0.5$	$\pm 1.5$	
Cross Regulation	Dual outputs, Vo1 load at 50%, Vo2 load at range of 10%-100%		--	--	$\pm 5$	
Transient Recovery Time	25% load step change		--	300	500	$\mu s$
Transient Response Deviation		3.3V, 5V, $\pm 5V$ output	--	$\pm 5$	$\pm 8$	%
		Others	--	$\pm 3$	$\pm 5$	
Temperature Coefficient	Full load		--	--	$\pm 0.03$	$^{\circ}C$
Ripple&Noise <sup>③</sup>	20MHz bandwidth		--	--	85	mVp-p
Over-voltage Protection	Input voltage range		110	--	160	%Vo
Over-current Protection			110	140	190	%Io
Short-circuit Protection			Continuous, self-recovery			

Note: ①Output voltage accuracy of  $\pm 5VDC/\pm 9VDC$  output converter for 0%-5% load is  $\pm 5\%$  max;

②Load regulation for 0%-100% load is  $\pm 5\%$ ;

③The "parallel cable" method is used for Ripple and Noise test, please refer to DC-DC Converter Application Notes for specific information.

### General Specifications

Item	Operating Conditions	Min.	Typ.	Max.	Unit
Isolation	Input-output Electric Strength Test for 1 minute with a leakage current of 1mA max.	1500	--	--	VDC
Insulation Resistance	Input-output resistance at 500VDC	1000	--	--	MΩ
Isolation Capacitance	Input-output capacitance at 100kHz/0.1V	--	1000	--	pF
Operating Temperature	Derating when operating temperature up to $71^{\circ}C$ (see Fig. 1)	-40	--	85	$^{\circ}C$
Storage Temperature		-55	--	125	
Storage Humidity	Non-condensing	5	--	95	%RH
Pin Soldering Resistance Temperature	Soldering spot is 1.5mm away from case for 10 seconds	--	--	300	$^{\circ}C$
Vibration		IEC/EN61373 - Category 1, Grade B			
Switching Frequency *	PWM mode	--	300	--	kHz
MTBF	MIL-HDBK-217F@ $25^{\circ}C$	1000	--	--	k hours

Note: \*Switching frequency is measured at full load. The module reduces the switching frequency for light load (below 50%) efficiency improvement.

### Mechanical Specifications

Case Material	Aluminum alloy
Dimensions	32.00 x 20.00 x 10.80mm
Weight	12.0g(Typ.)
Cooling Method	Free air convection

### Electromagnetic Compatibility (EMC)

Emissions	CE	CISPR32/EN55032 CLASS A (without extra components)/ CLASS B (see Fig.3-② for recommended circuit)		
	RE	CISPR32/EN55032 CLASS A (without extra components)/ CLASS B (see Fig.3-② for recommended circuit)		
Immunity	ESD	IEC/EN61000-4-2	Contact $\pm 4kV$	perf. Criteria B
	RS	IEC/EN61000-4-3	10V/m	perf. Criteria A
	EFT	IEC/EN61000-4-4	$\pm 2kV$ (see Fig.3-① for recommended circuit)	perf. Criteria B
	Surge	IEC/EN61000-4-5	$\pm 2kV$ (see Fig.3-① for recommended circuit)	perf. Criteria B
	CS	IEC/EN61000-4-6	3 Vr.m.s	perf. Criteria A
	Voltage dips, short interruptions and voltage variations immunity	IEC/EN61000-4-29	0-70%	perf. Criteria B

### Electromagnetic Compatibility (EMC) (EN50155)

Emissions	CE	EN50121-3-2	150kHz-500kHz	99dB $\mu$ V (see Fig.3-② for recommended circuit)
		EN55016-2-1	500kHz-30MHz	93dB $\mu$ V (see Fig.3-② for recommended circuit)
Immunity	RE	EN50121-3-2	30MHz-230MHz	40dB $\mu$ V/m at 10m (see Fig.3-② for recommended circuit)
		EN55016-2-1	230MHz-1GHz	47dB $\mu$ V/m at 10m (see Fig.3-② for recommended circuit)
	ESD	EN50121-3-2	Contact $\pm 6kV$ /Air $\pm 8kV$	perf. Criteria A
	RS	EN50121-3-2	20V/m	perf. Criteria A
	EFT	EN50121-3-2	$\pm 2kV$ 5/50ns 5kHz (see Fig.3-① for recommended circuit)	perf. Criteria A
	Surge	EN50121-3-2	line to line $\pm 1kV$ (42Ω, 0.5μF) (see Fig.3-① for recommended circuit)	perf. Criteria A
	CS	EN50121-3-2	0.15MHz-80MHz 10V r.m.s	perf. Criteria A

### Typical Characteristic Curves








Fig. 1






## Design Reference


### 1. Typical application

All the DC/DC converters of this series are tested before delivery using the recommended circuit shown in Fig. 2. Input and/or output ripple can be further reduced by appropriately increasing the input & output capacitor values  $C_{in}$  and  $C_{out}$  and/or by selecting capacitors with a low ESR (equivalent series resistance). Also make sure that the capacitance is not exceeding the specified max. capacitive load value of the product.



### 2. EMC compliance circuit

Dual output:



Single output:




Fig. 3

Notes: For EMC tests we use Part ① in Fig. 3 for immunity and part ② for emissions test. Selecting based on needs.

3. The products do not support parallel connection of their output


4. For additional information please refer to DC-DC converter application notes on  
[www.mornsun-power.com](http://www.mornsun-power.com)

Vin(VDC)	Cin	Vo(VDC)	Cout
24	100μF/50V	3.3/5/9/±5/±9	10μF/16V
		12/15/±12/±15	10μF/25V
		24/±24	10μF/50V
48	10μF/100V~47μF/100V	3.3/5/9/±5	10μF/16V
		12/15/±12/±15	10μF/25V
		24	10μF/50V

Parameter description:

Model	Vin:24VDC	Vin:48VDC
FUSE	Choose according to actual input current	
C0/C3	330μF/50V	330μF/100V
C1	1μF/50V	1μF/100V
C2	Refer to the Cout in Fig.2	
LDM1		4.7μH
CY1/CY2		1nF/2kV

Dimensions and Recommended Layout



Notes:

- For additional information on Product Packaging please refer to [www.mornsun-power.com](http://www.mornsun-power.com). Packaging bag number: 58210008;
- It is recommended that the load imbalance of the dual output is  $\leq \pm 5\%$ . If it exceeds  $\pm 5\%$ , the performance of the product cannot be guaranteed to meet as datasheet marked. For details, please contact our technical staff;
- The maximum capacitive load offered were tested at input voltage range and full load;
- Unless otherwise specified, parameters in this datasheet were measured under the conditions of  $T_a=25^\circ C$ , humidity  $< 75\%RH$  with nominal input voltage and rated output load;
- All index testing methods in this datasheet are based on company corporate standards;
- The performance indexes of the product models listed in this datasheet are as above, but some indexes of non-standard model products will exceed the above-mentioned requirements, and please directly contact our technicians for specific information;
- We can provide product customization service;
- Products are related to laws and regulations: see "Features" and "EMC";
- Our products shall be classified according to ISO14001 and related environmental laws and regulations, and shall be handled by qualified units.

**Mornsun Guangzhou Science & Technology Co., Ltd.**

Address: No. 8, Nanyun 4th Road, Huangpu District, Guangzhou, China

Tel: 86-20-38601850

Fax: 86-20-38601272

E-mail: [info@mornsun.cn](mailto:info@mornsun.cn)

[www.mornsun-power.com](http://www.mornsun-power.com)