MORNSUN®

Intelligent four-channel CAN bridge

RoHS

FEATURES

- With 4-channel CAN interface, isolation between two pairs of 2500VDC
- The baud rate can be configured in the range of 40k-1Mbps
- CAN message filtering function, effectively avoiding unwanted messages from being forwarded
- The destination port for message forwarding can be set arbitrarily
- Port data throughput up to 6000fps
- Comply with CAN2.0B specification and ISO/DIS 11898 specification
- Working voltage: 9V 36V DC (automatically change direction)
- Operating ambient temperature range: -40 $^\circ$ C to +85 $^\circ$ C
- The same network can support 110 nodes
- Set isolation and ESD bus protection in one
- CAN ports are equipped with shielded wire ground interface
- Preset 120 Ω terminal matching resistance
- With indicator lights for power supply, device status, bus activity, error indicator

TB24UCAN-4 can realize the transparent connection of multiple CAN networks, and can realize the multi-point connection of complex structure at the bus level. TB24UCAN-4 makes the backbone network have no branch line length limitation, and any two nodes in the network can reach the protocol distance. The device has 4 communication ports, and each port has an independent CAN transceiver, which can quadruple the number of nodes. Therefore, while providing free wiring, it also lifts the maximum number of CAN transceivers on the system bus.

Each port of TB24UCAN-4 has indicator lights for detecting bus activity and bus failure, which is convenient for observing the working status of CAN bus network. TB24UCAN-4 can be used in CAN networks with a baud rate of up to 1Mbps, and all channels can work at different baud rates. TB24UCAN-4 complies with CAN specification 2.0A (11-bit CAN identifier) and 2.0B (29-bit CAN identifier). It supports transparent and protocol-independent CAN message transmission, making it suitable for a variety of applications. In addition, it can be used for various high-level CAN protocols (CANOpen, SDS, J1939, DeviceNet or other customized protocols).

TB24UCAN-4 can be configured with the corresponding CAN message filter, which can ensure that only the required data is transmitted to other CAN networks through the repeater. At the same time, it also has a data routing function, which can selectively forward CAN messages received from one channel to another channel. Therefore, the device can effectively reduce the load on the network. TB24UCAN-4 can be configured by connecting to a PC through an asynchronous serial communication interface; it provides configuration software based on Windows system, which is simple to use and supports immediate configuration effect. After the device is configured, it can be put into work without any operation.

Selection G	Jide					
Certification	Part No.	Power input (VDC)	Baud rate (kbps)	Static power consumption(W)	Dynamic power consumption(W)	Number of single-channel Nodes
	TB24UCAN-4	9-36	40 -1000	1	1.2	110

Power Supply Specific	ations				
Item	Operating Conditions	Min.	Тур.	Max.	Unit
Power Supply Input Voltage		9	24	36	VDC
Consumption	Static power consumption		0.7	1.0	W
	Dynamic power consumption		1.0	1.2	W
Protection characteristics	40V overvoltage protection; automatic	power reversal;			
Note: *Both JP2 and JP3 are powe	er connectors, only connect one of them.				

Transmission Specifications					
Item	Operating Conditions	Min.	Тур.	Max.	Unit
Transmission delay			20	200	US

MORNSUN[®]

MORNSUN Guangzhou Science & Technology Co., Ltd.

2021.11.20- A/0

Page 1 of 8

[•] With indice N-4 can realize the transparent connect of complex structure at the bus level. TB24U d any two nodes in the network can reac ort has an independent CAN transceiver e wiring, it also lifts the maximum number or ort of TB24UCAN-4 has indicator lights for e working status of CAN bus network. TB24 all channels can work at different baud rat d 2.0B (29-bit CAN identifier). It supports traitable for a variety of applications. In or SDS, J1939, DeviceNet or other customized

MORNSUN®

POWER indicator (red)	Light up, the power status is OK; Light off, the power is not connected or the power is abnormal
SYSTEM indicator (green)	Flashing frequency 0.5HZ, the system is working normally; Light off, the system is not working; flashing irregularly, insufficient power or abnormal interference
ACTIVE indicator (green)	Flashing, the corresponding channel bus has data forwarding;Light off, the corresponding channel bus has no data forwarding
FAULT indicator (red)	Light up, the corresponding channel bus has an error; Light off, the corresponding channel bus has no error

CAN Interface Specifications

Item Operating (Conditions Min.	Turo		
operating		Тур.	Max.	Unit
Differential Dominant Level (Logic 0) Vdiff(d)	1.5	2	3	
Level Recessive Level (Logic 1) Vdiff()	-0.05	0	0.05	VDC
Bus Pin Maximum Withstand Voltage Vx	-30		+30	
Load Resistance Differential RL	45	60	65	Ω
Input Impedance Differential Rdiff	15		40	kΩ
Baud Rate	40		1000	kbps
CAN Bus Interface Meets ISO/	DIS 11898-2 standard Twisted-pair output			

General Specificatio	ns	
Item	Operating Conditions	Value
Isolation Test	Electric Strength Test for 1 minute, leakage current <1mA	2500VDC(Between the one CAN interface and the other)
Insulation Resistance	At 500VDC	$1000M\Omega(\text{Between the one CAN interface and the other)}$
Operating Temperature		-40 ℃ to +85℃
Transportation and Storage Temperature		-40℃ to +8505℃
Operating Humidity	Non-condensing	10% - 90%

Mechanical Specif	fications
Case Material	Metal (SPCC, surface paint process)
Dimensions	118 x 72.0 x 23mm
Weight	300g(Typ.)
Cooling Method	Free air convection

Electro	magnetic Con	npatibility (EMC)	
	ESD	IEC/EN 61000-4-2 Contact \pm 4kV (Bus port, FG pin is not connected to the ground)	Perf. Criteria A
lasas with a	ESD	IEC/EN 61000-4-2 Contact \pm 8kV (Bus port, FG pin is connected to the ground)	Perf. Criteria A
Immunity	EFT	IEC/EN 61000-4-4 ±2kV (Bus port, without external components)	Perf. Criteria B
	Surge	IEC/EN 61000-4-5 ±2kV (Bus port, common mode, without external components)	Perf. Criteria B

Application Precautions

1. Carefully read and follow the instructions before use; contact our technical support if you have any question;

- 2. Do not use the product in hazardous areas;
- 3. It is strictly forbidden to disassemble the product privately in order to avoid product failure or malfunction.

After-sales service

- 1. Factory inspection and quality control are strictly enforced before shipping any product; please contact your local representative or our technical support if you experience any abnormal operation or possible failure of the module;
- 2. The products have a 3-year warranty period, from the date of shipment. The product will be repaired or exchanged free of charge within the warranty period for any quality problem that occurs under normal use.



MORNSUN Guangzhou Science & Technology Co., Ltd. 2021.11.20- A/0 Page 2 of 8



Design Reference

1. Typical application circuit

The typical application of TB24UCAN-4 is shown in Figure 1. There are 4 CAN channels in total, and each CAN channel can be connected to a CAN network or a device with CAN interface.



Figure 1. Typical application circuit

The pin functions of the terminal block are as follows:

Table 1.CAN bus terminal function description

Port name	Function Description
CANL	CANL signal line
R+	Terminal resistance (short-circuit with R- to obtain 120 ${}^\Omega$ terminal matching resistance)
R-	Terminal resistance (short-circuit with R+ to obtain 120 ${}^{\Omega}$ terminal matching resistance)
FG	Shield ground wire (not necessarily connected)
CANH	CANH signal line

According to the ISO 11898 specification, in order to reduce the signal reflection on the CAN bus and enhance the reliability of communication, terminal matching resistors are usually added to the two end points of the bus. The size of the terminal matching resistance is determined by the characteristic impedance of the transmission cable. For example, if the characteristic impedance of a twisted pair is 120Ω , the two terminals on the bus should also be connected to a 120Ω terminal resistance.

The TB24UCAN-4 converter itself comes with a 120 ohm terminal resistor, and each port provides terminals R+ and R- connecting the terminal resistor. When TB24UCAN-4 is at the end of the bus, you can use a wire to short-circuit the "R-" and "R+" pins, then a 120 ohm terminal resistor is connected, as shown in Figure 2:



Figure 2. Built in $120 \,\Omega$ terminal resistor

If users use cables with impedance characteristics other than 120Ω , they can choose appropriate terminal resistance to connect to ports A and B, as shown in Figure 3:



Figure 3. External terminal resistor



MORNSUN Guangzhou Science & Technology Co., Ltd.

MORNSUN®

TB24UCAN-4 is connected to the PC through the RS232 interface to achieve the purpose of configuring or reading the bus status. Connect the TB24UCAN-4 to the PC through the RS232 cable. The setting is completed by the special configuration program running on the PC, without any hardware jumpers or switch configuration, and the configuration will take effect immediately after the completion. This port uses a DB-9 female connector. Before connecting with the PC, use an RS232 extension cable to connect the TB24UCAN-4 with the PC's serial port. If you use a crossover cable, you cannot communicate. The RS232 interface on TB24UCAN-4 is shown in Figure 4:



Figure 4. RS232 interface

Table 2. 232 Terminal function description

Port number	Function Description	Function description	
2	TXD	Send data	
3	RXD	Receive data	
5	GND	Ground	
1,4,6,7,8,9	NC	Invalid	

2. Function configuration

2.1 Basic Information

The first tab is basic information. The general settings include some basic information of the TB24UCAN-4 communication port and equipment. The operations of downloading all user-modified configurations to the device, or obtaining the current configuration and device information of the device are performed on this interface.

File (F) View (V) Tool (T) Lan Device Type 🕴 🗸	nguage (L) Help (H) TB24UCAN-4 ×
Jevice Type ♥ ¥ × ⊡ CANStudio I T824UCAN-4 T824CFA-2	BaudRate Router Filter Status Connect COM: Connect Con

Figure 5. Basic Information

Connection port: select the communication port between the host computer and TB24UCAN-4. The serial communication ports available in the system will be listed in the drop-down list of the combo box;

Read configuration: read configuration from TB24UCAN-4 (including configuration of other option cards);

Write configuration: write all configurations (including the configuration of other option cards) to the TB24UCAN-4 device.



 MORNSUN Guangzhou Science & Technology Co., Ltd.

 2021.11.20- A/0
 Page 4 of 8

 MORNSUN Guangzhou Science & Technology Co., Ltd. reserves the copyright and right of final interpretation



2.2 Baud rate

The second tab is the baud rate setting. The user selects the baud rate of the corresponding port in this tab. If you select "Custom" in the list below, you can enter the baud rate calculated by the user in the edit box below. To calculate the baud rate of non-standard value, click "Baud rate calculation".

TB24UCAN-4	BasicInfo BaudRate Router Filter Sta	atus		
TB24CFA-2	CAN1 Connect	Config		
	Auto Detect Detect Timeout: 1 s	Save Config		
		CAN4		
	CAN3	CAN4		
	CAN3 BaudRate:	CAN4 BaudRate:		

Figure 6. Baud rate

2.3 Routing function

TB24UCAN-4 has a simple message routing function, which can selectively forward CAN messages received by one channel to another channel. These operations are done in the "Routing" tab. Select the radio button of the corresponding channel to forward the message to that channel.

CANConfigStudio_1.0.0.0								
File (F) View (V) Tool (T) Lar	nguage (L) Help (H)							
Device Type 📮 🗴	TB24UCAN-4 ×							
CANStudio TB24UCAN-4	BasicInfo BaudRate Router Filter Status							
TB24CFA-2	CAN1 CA	1N2						
	CAN2	CAN1						
	CAN3	CAN3						
	CAN4	CAN4						
	CAN3 CA	1N4						
	CAN1	CAN1						
	CAN2	CAN2						
	CAN4	CAN3						
	₩.	V						
	<u>. </u>	Select All						
Ready								

Figure 7. Routing function

MORNSUN®

MORNSUN Guangzhou Science & Technology Co., Ltd.2021.11.20- A/0Page 5 of 8

MORNSUN Guangzhou Science & Technology Co., Ltd. reserves the copyright and right of final interpretation

MORNSUN®

2.4 Filter function

TB24UCAN-4 has a powerful message filter. The filter has 56 units, which can accommodate 56 standard identifiers or 56 extended identifiers or a mixture of two types of identifiers. The 56 filters are evenly distributed to 4 CAN bus ports within the product, with each port at most It can support 14 filters. In the "Filter" tab, there are two types of filters: standard single frame format and extended single frame format. Click the corresponding button on the configuration program interface, the detailed information of the corresponding filter can be displayed in the list box below, and the content of the filter can be changed at the same time.

TB24UCAN-4 TB24CFA-2	BasicInfo BaudRate Router Filter Statu Filter	IS
	Filter Setting	
	Frame Format Start ID 00000001	Channel - End ID 00000001 (*

Figure 8. Filter functionn

1) Click "Frame Format" and select "Standard Single Frame Format" or "Extended Frame Single Frame Format";

2) Click the "Channel" column of the newly added filter, and select the port corresponding to the filter in the pop-up drop-down list;
3) Enter the identifier of the filter in the "Start ID" edit box. Such as: 00000001 (hexadecimal). Note: The standard frame identifier range is 0~2047, and the extended frame identifier range is 0~536870911;

4) Click "Add Filter" with the mouse to complete the steps of adding a new filter;

5) Repeat the above operation to add other filters;

6) Delete one or several filters: click the filter or filters you want to delete in the "Filter Table", and then click "Delete Filter" to complete;

7) After finishing adding the filter table, note that the filter operation in the filter table will take effect after configuration after the radio button before "Enable" is selected, otherwise the filter operation will not be performed.

2.5 State refresh

The status of each channel of the TB24UCAN-4 can be monitored in real time through the configuration program. Click the "Refresh" button under the "Status" tab, and the software interface can display the working conditions of each channel of the device. The meaning of the status code is listed below the status indicator for comparison and reference.

evice Type 🛛 🕴	× TB24UCA	N-4 ×									
- CANStudio 	BasicInfo	Baud	Rate	Router	Filter	Status					
TB24CFA-2	Channel	000	001	010	011	100	101	110	111	TxErr	RxErr
	CAN1			•		٠		•		0	0
	CAN2	•		•		•		•	•	0	0
	CAN3	•	•	٠	•	•	•	•	•	0	0
	CAN4	•	•	•	•	•	•	•	•	0	0
	Meaning	Meaning of Status Code (1 indicates an error , 0 indicates no error) :								1	
	000 : No	error	001	: Stuff er	ror	010 : Form	error	011 : /	ACK erro	r	
	100 : Bit error	ecessive	101 erro	. : <mark>Bit don</mark> or	ninant	110 : CRC	error	111 : Softwa			0
											Update

Figure 9. State refresh



MORNSUN Guangzhou Science & Technology Co., Ltd.

3. Indicator light

There are 10 LED indicators on the top panel of TB24UCAN-4. The detailed functions are described in Table 3 below:

Name	Color	Status	Meaning
POWER	Red	Light up	Power status OK
	Kea	Light off	The power is not connected or the power supply is abnormal
		0.5HZ frequency flashing	The system is working
SYSTEM	Green	Light off	The system is not working
		Flicker irregularly	Insufficient power or interference causes anomalies
	ACTIVE(1-4) Green	Light up/Flashing	The corresponding CAN channel bus is in data forwarding
ACTIVE(1-4)		Light off	The corresponding CAN channel bus is not in data forwarding
	Red	Light up/Flashing	Error occurred on the corresponding CAN channel bus
FAULT(1-4)		Light off	No error occurred on the corresponding CAN channel bus

Table 3. LED instructions

4. Precautions

1)TB24UCAN-4 has 4 CAN ports in total, and the ports can work at different baud rates at the same time. When the receiving port rate is high and the forwarding port rate is low, it is necessary to pay attention to whether the port cache is sufficient.

Each port of TB24UCAN-4 has a buffer of 512 frames, which supports high-rate reception and low-rate forwarding. But when this buffer size is overflowed, the data will be overwritten.



 MORNSUN Guangzhou Science & Technology Co., Ltd.

 2021.11.20- A/0
 Page 7 of 8

 MORNSUN Guangzhou Science & Technology Co., Ltd. reserves the copyright and right of final interpretation

Dimensions and Recommended Layout

THIRD ANGLE PROJECTION 🛞 🧲

MORNSU



Notes:

- 1. For additional information on Product Packaging please refer to www.mornsun-power.com. Packaging bag number: 58240027;
- 2. Unless otherwise specified, parameters in this datasheet were measured under the conditions of Ta=25°C, humidity<75%RH with nominal input voltage and rated output load;
- 3. All index testing methods in this datasheet are based on company corporate standards;
- 4. The performance indexes of the product models listed in this datasheet are as above, but some indexes of non-standard model products will exceed the above-mentioned requirements, and please directly contact our technician for specific information;
- 5. We can provide product customization service, please contact our technicians directly for specific information;
- 6. Products are related to laws and regulations: see "Features" and "EMC";
- 7. Our products shall be classified according to ISO14001 and related environmental laws and regulations, and shall be handled by qualified units.

MORNSUN Guangzhou Science & Technology Co., Ltd.

 Address: No. 5, Kehui St. 1, Kehui Development Center, Science Ave., Guangzhou Science City, Huangpu District, Guangzhou, P. R. China

 Tel: 86-20-38601850
 Fax: 86-20-38601272

 E-mail: info@mornsun.cn
 www.mornsun-power.com

MORNSUN[®]

MORNSUN Guangzhou Science & Technology Co., Ltd.