



1

2



3

4

A



B



A

B

C

Technical requirements:

1、Unit: mm

2、Line diameter: 0.4

3、Material: stainless steel with nicked plated-meet ROHS

4、Style: straight cylinder inside parallel pin

5、Technics: high temperature of the 260℃ heat treatment

6、No be marked sizes is $\pm 0.25\text{mm}$ tolerances

7、No dirty surface, no bad material

8、Contact number: 13459252012、0592-5216722

9、Mode: F6-12-0.4NH

10、Salt spray test:

five precent salt spray test was met for 24hours

11、Packaging method: in bags-the minimum package is 1000pcs

C

D

D

E

E

F

F

						碳钢线					厦门市芯网电子科技有限公司		
标记	处数	分区	更改文件号	签名	年 月 日	阶 段 标 记		重量	比例				
设计						s							3:1
校核													
批准													

1

2

3

4