


# FMC 0,5/ 4-ST-2,54 C2 - PCB connector



1706241

<https://www.phoenixcontact.com/us/products/1706241>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PCB connector, nominal cross section: 0.5 mm<sup>2</sup>, color: black, nominal current: 6 A, rated voltage (III/2): 160 V, contact surface: Au, contact connection type: Socket, number of potentials: 4, number of rows: 1, number of positions: 4, number of connections: 4, product range: FMC 0,5/...-ST, pitch: 2.54 mm, connection method: Push-in spring connection, conductor/PCB connection direction: 0 °, plug-in system: COMBICON FMC 0,5, locking: without, mounting method: without, type of packaging: packed in cardboard, Fixed coding of last position; can be combined with MC(V) 0,5/...-G-2,54...C2 headers

## Your advantages

- Gold-plated contacts ensure transfer quality remains stable over the long term
- Time saving push-in connection, tools not required
- Defined contact force ensures that contact remains stable over the long term
- Intuitive operation due to color-coded actuating push button
- Optimized for tight installation situations: operation and conductor connection from one direction

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1706241                        |
| Packing unit                         | 200 pc                         |
| Minimum order quantity               | 200 pc                         |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | AA01                           |
| Product key                          | AAFAA                          |
| Catalog page                         | Page 175 (C-1-2013)            |
| GTIN                                 | 4046356841276                  |
| Weight per piece (including packing) | 1.06 g                         |
| Weight per piece (excluding packing) | 1.055 g                        |
| Customs tariff number                | 85366990                       |
| Country of origin                    | PL                             |

# FMC 0,5/ 4-ST-2,54 C2 - PCB connector



1706241

<https://www.phoenixcontact.com/us/products/1706241>

## Technical data

### Product properties

|                       |                        |
|-----------------------|------------------------|
| Product type          | PCB connector          |
| Product family        | FMC 0,5/...-ST         |
| Product line          | COMBICON Connectors XS |
| Type                  | Standard               |
| Number of positions   | 4                      |
| Pitch                 | 2.54 mm                |
| Number of connections | 4                      |
| Number of rows        | 1                      |
| Number of potentials  | 4                      |
| Mounting flange       | without                |

### Electrical properties

|                             |        |
|-----------------------------|--------|
| Nominal current $I_N$       | 6 A    |
| Nominal voltage $U_N$       | 160 V  |
| Contact resistance          | 2.7 mΩ |
| Rated voltage (III/3)       | 32 V   |
| Rated surge voltage (III/3) | 0.8 kV |
| Rated voltage (III/2)       | 160 V  |
| Rated surge voltage (III/2) | 2.5 kV |
| Rated voltage (II/2)        | 160 V  |
| Rated surge voltage (II/2)  | 1.5 kV |

### Connection data

#### Connection technology

|                         |                     |
|-------------------------|---------------------|
| Type                    | Standard            |
| Connector system        | COMBICON FMC 0,5    |
| Nominal cross section   | 0.5 mm <sup>2</sup> |
| Contact connection type | Socket              |

#### Interlock

|                 |         |
|-----------------|---------|
| Locking type    | without |
| Mounting flange | without |

#### Conductor connection

|                                                                       |                                               |
|-----------------------------------------------------------------------|-----------------------------------------------|
| Connection method                                                     | Push-in spring connection                     |
| Conductor/PCB connection direction                                    | 0 °                                           |
| Conductor cross section rigid                                         | 0.14 mm <sup>2</sup> ... 0.5 mm <sup>2</sup>  |
| Conductor cross section flexible                                      | 0.14 mm <sup>2</sup> ... 0.5 mm <sup>2</sup>  |
| Conductor cross section AWG                                           | 26 ... 20                                     |
| Conductor cross section flexible, with ferrule without plastic sleeve | 0.25 mm <sup>2</sup> ... 0.34 mm <sup>2</sup> |

# FMC 0,5/ 4-ST-2,54 C2 - PCB connector



1706241

<https://www.phoenixcontact.com/us/products/1706241>

|                                                                      |                                               |
|----------------------------------------------------------------------|-----------------------------------------------|
| Conductor cross section, flexible, with ferrule, with plastic sleeve | 0.14 mm <sup>2</sup> ... 0.25 mm <sup>2</sup> |
| Cylindrical gauge a x b / diameter                                   | - / 1.0 mm                                    |
| Stripping length                                                     | 7 mm                                          |

## Specifications for ferrules without insulating collar

|                           |                    |
|---------------------------|--------------------|
| recommended crimping tool | 1212034 CRIMPFOX 6 |
|---------------------------|--------------------|

## Specifications for ferrules with insulating collar

|                           |                    |
|---------------------------|--------------------|
| recommended crimping tool | 1212034 CRIMPFOX 6 |
|---------------------------|--------------------|

## Material specifications

### Material data - contact

|                                             |                                                                                  |
|---------------------------------------------|----------------------------------------------------------------------------------|
| Note                                        | WEEE/RoHS-compliant, free of whiskers according to IEC 60068-2-82/JEDEC JESD 201 |
| Contact material                            | Cu alloy                                                                         |
| Surface characteristics                     | partially gold-plated                                                            |
| Metal surface terminal point (top layer)    | Tin (5 - 7 µm Sn)                                                                |
| Metal surface terminal point (middle layer) | Nickel (2 - 3 µm Ni)                                                             |
| Metal surface contact area (top layer)      | Gold (0.25 Au)                                                                   |
| Metal surface contact area (middle layer)   | Nickel (2 - 3 µm Ni)                                                             |


### Material data - housing

|                                        |              |
|----------------------------------------|--------------|
| Color (Housing)                        | black (9005) |
| Insulating material                    | LCP          |
| Insulating material group              | IIIa         |
| CTI according to IEC 60112             | 175          |
| Flammability rating according to UL 94 | V0           |

### Material data – actuating element

|                                        |               |
|----------------------------------------|---------------|
| Color (Actuating element)              | orange (2003) |
| Insulating material                    | LCP           |
| Insulating material group              | IIIa          |
| CTI according to IEC 60112             | 175           |
| Flammability rating according to UL 94 | V0            |

## Dimensions

|                     |                                                                                      |
|---------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing |  |
| Pitch               | 2.54 mm                                                                              |
| Width [w]           | 10.66 mm                                                                             |
| Height [h]          | 5.35 mm                                                                              |
| Length [l]          | 14 mm                                                                                |

# FMC 0,5/ 4-ST-2,54 C2 - PCB connector



1706241

<https://www.phoenixcontact.com/us/products/1706241>

## Mechanical tests

### Conductor connection

|               |                     |
|---------------|---------------------|
| Specification | IEC 60999-1:1999-11 |
| Result        | Test passed         |

### Test for conductor damage and slackening

|               |                     |
|---------------|---------------------|
| Specification | IEC 60999-1:1999-11 |
| Result        | Test passed         |

### Repeated connection and disconnection

|               |                     |
|---------------|---------------------|
| Specification | IEC 60999-1:1999-11 |
| Result        | Test passed         |

### Pull-out test

|                                                                                |                                          |
|--------------------------------------------------------------------------------|------------------------------------------|
| Specification                                                                  | IEC 60999-1:1999-11                      |
| Conductor cross section/conductor type/tractive force<br>setpoint/actual value | 0.14 mm <sup>2</sup> / solid / > 10 N    |
|                                                                                | 0.14 mm <sup>2</sup> / flexible / > 10 N |
|                                                                                | 0.5 mm <sup>2</sup> / solid / > 20 N     |
|                                                                                | 0.5 mm <sup>2</sup> / flexible / > 20 N  |

### Insertion and withdrawal forces

|                                     |                        |
|-------------------------------------|------------------------|
| Specification                       | IEC 60512-13-2:2006-02 |
| Result                              | Test passed            |
| No. of cycles                       | 100                    |
| Insertion strength per pos. approx. | 2 N                    |
| Withdraw strength per pos. approx.  | 2 N                    |

### Resistance of inscriptions

|               |                        |
|---------------|------------------------|
| Specification | IEC 60068-2-70:1995-12 |
| Result        | Test passed            |

### Polarization and coding

|               |                        |
|---------------|------------------------|
| Specification | IEC 60512-13-5:2006-02 |
| Result        | Test passed            |

### Visual inspection

|               |                       |
|---------------|-----------------------|
| Specification | IEC 60512-1-1:2002-02 |
| Result        | Test passed           |

### Dimension check

|               |                       |
|---------------|-----------------------|
| Specification | IEC 60512-1-2:2002-02 |
| Result        | Test passed           |

## Environmental and real-life conditions

### Vibration test

|               |                       |
|---------------|-----------------------|
| Specification | IEC 60068-2-6:2007-12 |
|---------------|-----------------------|

# FMC 0,5/ 4-ST-2,54 C2 - PCB connector



1706241

<https://www.phoenixcontact.com/us/products/1706241>

|                        |                                   |
|------------------------|-----------------------------------|
| Frequency              | 10 - 500 - 10 Hz                  |
| Sweep speed            | 1 octave/min                      |
| Amplitude              | 0.35 mm (10 Hz ... 60.1 Hz)       |
| Acceleration           | 5g (60.1 Hz ... 500 Hz)           |
| Test duration per axis | 2 h                               |
| Test directions        | X-, Y- and Z-axis (pos. and neg.) |

## Durability test

|                                              |                       |
|----------------------------------------------|-----------------------|
| Specification                                | IEC 60512-9-1:2010-03 |
| Impulse withstand voltage at sea level       | 2.95 kV               |
| Contact resistance R <sub>1</sub>            | 2.7 mΩ                |
| Contact resistance R <sub>2</sub>            | 2.6 mΩ                |
| Insertion/withdrawal cycles                  | 100                   |
| Insulation resistance, neighboring positions | > 5 MΩ                |

## Climatic test

|                                   |                                                                            |
|-----------------------------------|----------------------------------------------------------------------------|
| Specification                     | DIN 50018:2013-05                                                          |
| Corrosive stress                  | 1.0 dm <sup>3</sup> SO <sub>2</sub> on 300 dm <sup>3</sup> /40 °C/3 cycles |
| Thermal stress                    | 100 °C/168 h                                                               |
| Power-frequency withstand voltage | 1.39 kV                                                                    |

## Ambient conditions

|                                         |                                                     |
|-----------------------------------------|-----------------------------------------------------|
| Ambient temperature (operation)         | -40 °C ... 100 °C (dependent on the derating curve) |
| Ambient temperature (storage/transport) | -40 °C ... 70 °C                                    |
| Relative humidity (storage/transport)   | 30 % ... 70 %                                       |
| Ambient temperature (assembly)          | -5 °C ... 100 °C                                    |

## Electrical tests

### Thermal test | Test group C

|                            |                       |
|----------------------------|-----------------------|
| Specification              | IEC 60512-5-1:2002-02 |
| Tested number of positions | 16                    |

### Insulation resistance

|                                              |                       |
|----------------------------------------------|-----------------------|
| Specification                                | IEC 60512-3-1:2002-02 |
| Insulation resistance, neighboring positions | > 5 MΩ                |

### Temperature cycles

|               |                     |
|---------------|---------------------|
| Specification | IEC 60999-1:1999-11 |
| Result        | Test passed         |

### Air clearances and creepage distances |

|                                        |                     |
|----------------------------------------|---------------------|
| Specification                          | IEC 60664-1:2007-04 |
| Insulating material group              | IIIa                |
| Comparative tracking index (IEC 60112) | CTI 175             |
| Rated insulation voltage (III/3)       | 32 V                |
| Rated surge voltage (III/3)            | 0.8 kV              |

# FMC 0,5/ 4-ST-2,54 C2 - PCB connector



1706241


<https://www.phoenixcontact.com/us/products/1706241>

|                                                        |        |
|--------------------------------------------------------|--------|
| minimum clearance value - non-homogenous field (III/3) | 0.8 mm |
| minimum creepage distance (III/3)                      | 1.3 mm |
| Rated insulation voltage (III/2)                       | 160 V  |
| Rated surge voltage (III/2)                            | 2.5 kV |
| minimum clearance value - non-homogenous field (III/2) | 1.5 mm |
| minimum creepage distance (III/2)                      | 1.6 mm |
| Rated insulation voltage (II/2)                        | 160 V  |
| Rated surge voltage (II/2)                             | 1.5 kV |
| minimum clearance value - non-homogenous field (II/2)  | 0.5 mm |
| minimum creepage distance (II/2)                       | 1.6 mm |


## Packaging specifications

|                   |                     |
|-------------------|---------------------|
| Type of packaging | packed in cardboard |
|-------------------|---------------------|


## Drawings




Type: FMC 0,5/...-ST-2,54 with MC 0,5/...-G-2,54 SMD R..



Type FMC 0,5/...-ST-2,54 with MCV 0,5/...-G-2,54 SMD R..



Type: FMC 0,5/...-ST-2,54 with MCV 0,5/...-G-2,54 P20 THR R..



Type: FMC 0,5/...-ST-2,54 with MC 0,5/...-G-2,54 P20 THR R..

# FMC 0,5/ 4-ST-2,54 C2 - PCB connector



1706241

<https://www.phoenixcontact.com/us/products/1706241>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1706241>

|  <b>cULus Recognized</b><br>Approval ID: E60425-19920306 |                       |                       |                   |                             |
|-------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                                                                                                           | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| Use group B                                                                                                                               |                       |                       |                   |                             |
| Field wiring                                                                                                                              | 150 V                 | 5 A                   | 26 - 20           | -                           |
| Factory wiring                                                                                                                            | 150 V                 | 6 A                   | 26 - 20           | -                           |
| Use group C                                                                                                                               |                       |                       |                   |                             |
| Factory wiring                                                                                                                            | 50 V                  | 6 A                   | 26 - 20           | -                           |
| Use group F                                                                                                                               |                       |                       |                   |                             |
| Field wiring                                                                                                                              | 160 V                 | 5 A                   | 26 - 20           | -                           |

|  <b>VDE report with production monitoring</b><br>Approval ID: 40042258 |                       |                       |                   |                             |
|----------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                                                                                                                          | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|                                                                                                                                                          | 160 V                 | 6 A                   | -                 | 0.14 - 0.5                  |

# FMC 0,5/ 4-ST-2,54 C2 - PCB connector



1706241

<https://www.phoenixcontact.com/us/products/1706241>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-11.0 | 27460202 |
| ECLASS-12.0 | 27460202 |
| ECLASS-13.0 | 27460202 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002638 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# FMC 0,5/ 4-ST-2,54 C2 - PCB connector



1706241

<https://www.phoenixcontact.com/us/products/1706241>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)