

# HC-B-G-M40-EC-AL - Cable gland

1411441

<https://www.phoenixcontact.com/us/products/1411441>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

EVO EMC cable gland with bayonet locking, B series, size M40, cable diameter: 19 ... 27 mm



## Commercial data

Item number	1411441
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF57
Product key	BF7APM
Catalog page	Page 605 (C-2-2019)
GTIN	4046356932400
Weight per piece (including packing)	142.6 g
Weight per piece (excluding packing)	135 g
Customs tariff number	85389099
Country of origin	DE

# HC-B-G-M40-EC-AL - Cable gland

1411441

<https://www.phoenixcontact.com/us/products/1411441>



## Technical data

### Product properties

Product type	Cable gland with bayonet locking
Application	EMC
No. of conductors	1
Type of the screw connection	M40
Shielded	yes
Execution of the strain relief	B

### Dimensions

Dimensional drawing	
Width	54.2 mm
Height	722.4 mm
Depth	62 mm
Wrench size, union nut	43 mm
Thread pitch	1.5 mm

### Material specifications

Color	Aluminum color
Material Pressure screw	Brass, nickel-plated
Seal material	NBR
Seal material Cable seal	NBR
Housing material	Die-cast aluminum, corrosion resistant
Material for screw connection	Aluminum

### Cable/line

External cable diameter Cable 1	19 mm ... 27 mm
---------------------------------	-----------------

### Mechanical properties

Mechanical data	
Type of the screw connection	M40

### Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP66
	IP67
Enclosure rating (NEMA)	4 (UL 50e)
	4X (UL 50e)

# HC-B-G-M40-EC-AL - Cable gland

1411441

<https://www.phoenixcontact.com/us/products/1411441>



Ambient temperature (operation)	12 (UL 50e) -40 °C ... 125 °C (static)
---------------------------------	---

# HC-B-G-M40-EC-AL - Cable gland


1411441

<https://www.phoenixcontact.com/us/products/1411441>



## Drawings

Dimensional drawing



Dimensional drawing

# HC-B-G-M40-EC-AL - Cable gland

1411441

<https://www.phoenixcontact.com/us/products/1411441>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1411441>



**cUL Recognized**

Approval ID: E255026



**UL Recognized**

Approval ID: E255026



**EAC**

Approval ID: RU C-DE.AI30.B.01102



**EAC-RoHS**

Approval ID: RU D-DE.HB35.B.00387

**cULus Recognized**

# HC-B-G-M40-EC-AL - Cable gland

1411441

<https://www.phoenixcontact.com/us/products/1411441>



## Classifications

### ECLASS

ECLASS-11.0	27144432
ECLASS-12.0	27140801
ECLASS-13.0	27140801

### ETIM

ETIM 9.0	EC000441
----------	----------

### UNSPSC

UNSPSC 21.0	39121300
-------------	----------

# HC-B-G-M40-EC-AL - Cable gland

1411441

<https://www.phoenixcontact.com/us/products/1411441>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	c7aecd5a-a5f8-43a5-a8cd-e9094a490738

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

### Phoenix Contact USA

586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)