







REV.	ECN. NO.	APPD.
A	BC-10-0048062	Adward
B	BC-10-0152044	Adward
C	BC-11-0088036	Adward



SPECIFICATIONS :

- 1. PERFORMANCE :
 - 1-1. ELECTRICAL CHARACTERISTICS :
 - 1-1-1. CONTACT CURRENT RATING : 1.5AMPERE
 - 1-1-2. CONTACT RESISTANCE : 30 MILLIOHMS MAX.
 - 1-1-3. DIELECTRIC WITHSTANDING VOLTAGE : 500 VAC MIN.
 - 1-1-4. INSULATION RESISTANCE : 1000 MEGOHMS MIN.
 - 1-2. MECHANICAL CHARACTERISTICS :
 - 1-2-1. CONNECTOR ENGAGEMENT FORCE : 35N(3.5 Kgf) MAX.
 - 1-2-2. CONNECTOR SEPARATION FORCE : 10~35N(1.0~3.5 Kgf).
 - 1-2-3. DURABILITY: 1500 CYCLES.
 - 1-2-4. OPERATING TEMPERATURE : -55 TO +85°C

UB 1 1 1 2 * - 8FDE - 4 F

SERIES PERFIX
USB A TYPE

TERMINATION TYPE
1= RIGHT ANGLE

CONTACT TYPE
1= FEMALE

NO. OF POS
1 = 4 POS

PROFILE HEIGHT
2=4 1.3 MM


LEAD FREE CODE
F= LEAD FREE

—PACKAGE CODE
4= SOFT TRAY

— EXTEND CODE

— CONTACT AREA PLATED

1= 1u" MIN GOLD PLATED
C= 30 u" Pd/Ni,GOLD FLASH PLATED
3= 30 u" GOLD PLATED
7= 15 u" GOLD PLATED

5	REAR SHELL	1	STEEL	NICKEL PLATED					
4	FINGER	1	STAINLESS STEEL	CLEAN					
3	CONTACT	8	COPPER ALLOY	GOLD PLATED AT CONTACT AREA, LEAD FREE TIN ALLOY AT SOLDER TAIL, NICKEL PLATED OVER ALL.	FOR UB1112*-8FDE-4F				
2	INSULATOR	1	THERMOPLASTIC UL 94V-0	BLACK PA66					
1	FRONT SHELL	1	STAINLESS STEEL	NICKEL PLATED OVERALL, BUT KINK WITH LEAD FREE TIN ALLOY					
ITEM	DESCRIPTION	QTY	MATERIAL	FINISH	REMARK				
×.±	×°.±	UNITS	mm [INCH]	NAME(INTENDED USE)	FOXCONN HON HAI PRECISION IND. CO.,LTD TAIPEI, TAIWAN, R.O.C.				
.×±	.×°±	MAT'L		CUSTOMER					
.××± 0.25 [.010]	.××°±	N/A		PART NO.(INTENDED USE) UB1112*-8FDE-4F	TITLE: STACKED USB A TYPE RECEPTACLE				
.XXX±	.XXX°±	FINISH		APPD: Jesse Wang 8/1'11	DWG NO.: 327-0000-2172				
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF HON HAI PRECISION IND. CO., LTD. AND SHALL NOT BE REPRODUCED. COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF HON HAI PRECISION IND. CO., LTD.			N/A	CHKD: F.H Shu 8/1'11					
			Q'TY			DR: C.Y Zhai 8/1'11	SCALE	SHEET	REV
			N/A				N/A	1/1	C