

Passive Components > Resistors > Through-Hole Resistors

Resistor Type: **General Purpose Resistor**Element Type: **Metal Oxide Film**Power Rating: **.5 W**Resistance Class: **1k Ω – 1M Ω** Resistance Value: **1.2K Ω**

Features

Usage Conditions

Operating Temperature Range	-55 – 155 $^{\circ}$ C
Temperature Coefficient	± 350 ppm/ $^{\circ}$ C

Electrical Characteristics

Operating Voltage	250 V
Power Rating	.5 W
Resistance Class	1k Ω – 1M Ω
Resistance Value	1.2K Ω
Passive Component Tolerance	5 %

Product Type Features

Resistor Type	General Purpose Resistor
Element Type	Metal Oxide Film

Configuration Features

Number of Resistors	1
---------------------	---

Body Features

Lead Type	Axial-Leaded
-----------	--------------

Termination Features

Termination Area Base Material	Copper
Number of Terminations	2

Dimensions

Passive Component Dimensions	7.2 x 2.5 mm
------------------------------	--------------

Packaging Features

Packaging Method	Ammo Packed
------------------	-------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com/compliance)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1625881-2
1W STD M/OX 2% 220RTE Part # 2-1625892-1
3W SM M/OX 5% 1K0TE Part # 6-1676123-7
1/2W SM M/OX 5% 470RTE Part # 4-1625886-1
1W SM M/OX 5% 820KTE Part # 1625893-5
5W SM M/OX 5% 47K



Also in the Series | Neohm ROX



Through-Hole Resistors(783)

Customers Also Bought

TE Part #CV7360-000
202K121-25L-0TE Part #5-1415036-1
PTML0024TE Part #6-2176414-3
7W STD M/OX 5% 7K5TE Part #2176163-5
UPF50 0.1% 5PPM 120R

TE Part #2820463016
44A0111-24-6TE Part #9675813001
100G0111-0.50-6TE Part #9-2176614-7
EP 10W (SS) 10K 5% BULK BOXTE Part #AAB1892-00
91H1-15-10-1-B-HE200TE Part #047688-000
ENC-22/ADH-0TE Part #223762-000
ENC-33/ADH-0

Documents

Product Drawings

1/2W SM M/OX 5% 1K2

English

Datasheets & Catalog Pages

Flame Proof Power Metal Oxide Film Resistors - Type ROX Series - Tyco Electronics Passives

English