







RoHS



SECTION A-A



适用线路板 (PCB LAYOUT)

Model No.	Pin	A	B	C	D
WAFER-PH2.0-2PZZ-W	2	2.00	6.00	1.00	5.00
WAFER-PH2.0-3PZZ-W	3	4.00	8.00	2.00	7.00
WAFER-PH2.0-4PZZ-W	4	6.00	10.00	4.00	9.00
WAFER-PH2.0-5PZZ-W	5	8.00	12.00	6.00	11.00
WAFER-PH2.0-6PZZ-W	6	10.00	14.00	8.00	13.00
WAFER-PH2.0-7PZZ-W	7	12.00	16.00	10.00	15.00
WAFER-PH2.0-8PZZ-W	8	14.00	18.00	12.00	17.00
WAFER-PH2.0-9PZZ-W	9	16.00	20.00	14.00	19.00
WAFER-PH2.0-10PZZ-W	10	18.00	22.00	16.00	21.00
WAFER-PH2.0-11PZZ-W	11	20.00	24.00	18.00	23.00
WAFER-PH2.0-12PZZ-W	12	22.00	26.00	20.00	25.00
WAFER-PH2.0-13PZZ-W	13	24.00	28.00	22.00	27.00
WAFER-PH2.0-14PZZ-W	14	26.00	30.00	24.00	29.00
WAFER-PH2.0-15PZZ-W	15	28.00	32.00	26.00	31.00
WAFER-PH2.0-16PZZ-W	16	30.00	34.00	28.00	33.00
WAFER-PH2.0-17PZZ-W	17	32.00	36.00	30.00	35.00
WAFER-PH2.0-18PZZ-W	18	34.00	38.00	32.00	37.00
WAFER-PH2.0-19PZZ-W	19	36.00	40.00	34.00	39.00
WAFER-PH2.0-20PZZ-W	20	38.00	42.00	36.00	41.00

Specifications/技术规格:

- 1.Poles/线数: 2~20P
- 2.Wire range/适用线规: AGW 30#~24#
- 3.Applicable PC board thickness/适用PC板厚度: 0.8~1.6mm
- 4.Current rating/额定电流: 2.0A
- 5.Voltage rating/额定电压: 100V DC/AC
- 6.Insulation Resistance/绝缘电阻: 1000MΩ Min
- 7.Dielectric Withstanding/ 耐电压: 800V AC/minute
- 8.Contact Resistance/ 接触电阻: 20mΩ Max
- 9.Operating Temperature/ 工作温度: -25℃ to +85℃

⑧	Terminal			Brass	Plating Sn
⑨	Housing		1	PA66	White
NO.	Name	Number	Qty	Materil	Remarks

YUANDI® Yuandi Electronics Co.,Ltd

design	date	name	WAVER CONNECTOR
Review	date		
Approved	date	model	WAFER-PH2.0-□□PZZ-W

Drawing number: Proportion 1:1 unit mm gage number A4

modify Review Approved

angle ±2°
10~30 ±0.30
5~10 ±0.20
~ 5 ±0.10

Tolerance not specified