






REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



PIN ASSIGNMENTS

A5	CC1	B12	GND
A9	VBUS	B9	VBUS
A12	GND	B5	CC2
PIN	SIGNAL NAME	PIN	SIGNAL NAME



RECOMMENDED PCB LAYOUT
 GENERAL TOLERANCE ± 0.05

备注(NOTE): 1 材质:

1.1 胶芯: LCP UL94 V-0

1.2 端子: (C2680, 镍底, 镀金0.5U

1.3 外壳: 不锈钢304—表面镀镍50U

2. 电气特性:

2.1 接触区: 接触电阻30mQMax,
允许10mΩ变化量,

测试条件: 20mv, 100mA下测量,

2.2 额定电流: 最大3A

2.3 额定电压: 5V.

2.4 耐电压: 100VAC.

2.5 绝缘电阻: 至少100兆欧

3. 机械性能:


3.1 插入力: 0.5—2.0Kg

3.2 拔出力: 0.8—2.0Kg

3.3 插拔次数: 5000+.

4. 工作环境: -20℃to +85℃

4.1 盐雾测试: 24H

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.X: ± 0.30	X.X': $\pm 3^\circ$	PART NO. TYPE-C-01A-6P	TITLE: TYPE-C 6P SMT 四脚插板	
X.XX: ± 0.20	X.XX': $\pm 2^\circ$			
X.XXX: ± 0.10		DESIGN: Ethan	MANUFACTURE DWG	
UNITS	mm	CHED: Olvia		
MATERILA	— — —	APPD: Ava	 SCALE N:A	SHEET 1/1
FINISH	— — —			