



Connectors > Connector Accessories > Connector Strain Relief > Cable Clamp for Size 4-5 STD/5QL Shell



Strain Relief Accessory Type: **Cable Clamp Kit**

Primary Product Material: **Zinc**

Compatible With Connector Shell Size: **5**

Shielded: **Yes**

Operating Temperature Range: **-40 – 90 °C [ -40 – 194 °F ]**

[All Cable Clamp for Size 4-5 STD/5QL Shell \(6\)](#)

Features

Housing Features

Compatible With Connector Shape	D-Shaped
Body Orientation	Straight

Body Features

Cable Exit Angle	180°
Primary Product Material	Zinc

Product Type Features

Strain Relief Accessory Type	Cable Clamp Kit
------------------------------	-----------------

Operation/Application

Compatible With Connector Shell Size	5
Shielded	Yes

Usage Conditions

Operating Temperature Range	-40 – 90 °C[-40 – 194 °F]
-----------------------------	---------------------------

Other



EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | Rail D-Sub Backshells




Connector Contacts(5)



Connector Hardware(19)



Connector Strain Relief(67)



D-Sub Backshells & Clamps(55)

Customers Also Bought



TE Part #1658640-1  
HDP-20,RCPT,SIZE 5, 50 POSN



TE Part #CAT-R131-Q15A  
Quick Lock Pins for D-Sub with  
Threaded Inserts



TE Part #CAT-R131-D1C  
D-SUB BACKSHELL SIZE 4



TE Part #1-2308290-1  
QL-SET FOR VARIAN C VW REAR  
WALL MOUNTG



TE Part #1-2308338-1  
QL-FULL METAL HOODS SIZE 5 (1  
CABLE CLP)



TE Part #167296-1  
50P.HDP20 PLUG ASSY



TE Part #EC0784-000  
06171101



TE Part #EC0831-000  
06171909

Documents

Product Drawings

CABLE CLAMP7 (CASE RAW)

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_1-2308272-7\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_1-2308272-7\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_1-2308272-7\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



---

[Datasheets & Catalog Pages](#)

[Rail D-Sub Backshells Flyer](#)

English