






REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



PIN ASSIGNMENTS

A5	CC1	B12	GND
A9	VBUS	B9	VBUS
A12	GND	B5	CC2
PIN	SIGNAL NAME	PIN	SIGNAL NAME



RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ± 0.05

备注(NOTE):1材质:

1.1胶芯:LCP UL94 V-0

1.2端子:(C2680,镍底,镀金0.5U

1.3外壳:不锈钢304—表面镀镍50U

2.电气特性:

2.1.接触区:接触电阻30mQMax,
允许10m Ω 变化量,

测试条件:20mv,100mA下测量,

2.2.额定电流:最大3A

2.3.额定电压:5V.

2.4.耐电压:100VAC.

2.5.绝缘电阻:至少100兆欧

3.机械性能:

3.1.插入力:0.5—2.0Kg

3.2.拔出力:0.8—2.0Kg

3.3.插拔次数:5000+.

4.工作环境:-20℃to +85℃

4.1.盐雾测试:24H

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.X:±0.30	X.X':±3°	PART NO. TYPE-C-010C-6P	TITLE: TYPE-C 6P SMT 四脚插板	
X.XX:±0.20	X.XX':±2°			
X.XXX:±0.10				
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG	
MATERILA	— — —	CHED: Olvia		
FINISH	— — —	APPD: Ava		
			SCALE	SHEET
			N:A	1/1