



Product Features

- Excellent Insertion Loss and Isolation performance
- High Linearity
- GPIO Control Interface
- Broadband frequency range: 0.7 to 2.7 GHz
- Small package: QFN-10 1.1mm x 1.5mm x 0.45mm
- No DC blocking capacitors required
- 1kV HBM ESD Protection on all pins

Product Applications

- Band Selecting
- Antenna Tuning

Product Description

The LX8545 is a Silicon On Insulator (SOI) Single Pole, Four Throw (SP4T) antenna tuner which require very low insertion loss, high isolation and high linearity performance.

The high linearity performance and low insertion loss for 5G and 4G LTE applications.

The LX8545 is manufactured in a compact 1.1mm x 1.5mm x 0.45mm, 10-pin surface mount Quad Flat No-Lead (QFN) package.




Figure 1 Functional Block Diagram

Absolute Maximum Conditions

Parameters	Symbol	Minimum	Maximum	Units
Supply voltage	V _{DD}		4.8	V
Control voltage	VCTL		3.3	V
RF input power	P _{in}		+43	dBm
Storage temperature	T _{STG}	-55	+150	°C
Operating temperature	T _{OP}	-40	+90	°C
Human Body Model, Class 1C	ESD	1000		V

1: Test condition 50% duty cycle, VSWR=1:1, +25 °C

Note: Exposure to maximum rating conditions for extended periods may reduce device reliability. There is no damage to device with only one parameter set at the limit and all other parameters set at or below their nominal value. Exceeding any of the limits listed here may result in permanent damage to the device.

General Electrical Specifications

Parameters	Symbol	Test Condition	Min.	Typ.	Max.	Units
Supply voltage	V _{DD}		2.5	2.8	3.6	V
Supply current, active mode	I _{DD}			100	120	μA
Control signal: High Low	VCT		1.35	1.8	2.70 0.35	V
RF Operating Voltage (ANT to RF1/2/3/4)	V _P			60		V
Turn-on time (PIN = +27 dBm)	T _{ON}	Measured from 50% of final VDD supply voltage to 90% of RF power		3	5	μs
Switching time (PIN = +27 dBm)	T _{SW}	Measured from 50% of final VDD supply voltage to 90% of RF power		3	5	μs

(VDD = 2.85 V, VCT= 1.8 V, TOP = +25 °C, Characteristic Impedance [ZO] = 50 Ω, Unless Otherwise Noted)

RF Specifications

Parameters	Symbol	Test Condition	Min.	Typ.	Max.	Units
Operating frequency	f		0.7		2.7	GHz
Insertion loss	IL	Up to 0.9 GHz		0.28	0.40	dB
		Up to 1.9 GHz		0.42	0.50	
		Up to 2.7 GHz		0.50	0.80	
Isolation (ANT port to any receive port)	Iso	Up to 0.9 GHz	20	24		dB
		Up to 1.9 GHz	15	19		
		Up to 2.7 GHz	12	15		
Isolation (Active RF Ports to other inactive RF Ports)	Iso	Up to 0.9 GHz	23	25		dB
		Up to 1.9 GHz	17	20		
		Up to 2.7 GHz	14	17		
2nd Order harmonics	2fo	Pin = +26 dBm,900MHz	-73	-68		dBm
		Pin = +35 dBm,900MHz	-63	-60		
3rd Order harmonics	3fo	Pin = +26 dBm,900MHz	-78	-68		dBm
		Pin = +35 dBm,900MHz	-61	-59		
0.1 dB Compression Point 50% duty cycle, VSWR=1:1	P0.1dB	900M, 50Ω		+43		dBm
Ron		Path on		1.1	1.4	Ohm
Coff		Path off		140	160	fF

Truth Table

CTL1	CTL2	ANT-RFX
0	0	ANT-RF1 on
0	1	ANT-RF2 on
1	0	ANT-RF3 on
1	1	ANT-RF4 on

Pin-out Information




Figure 2 Pin-out Information

Table 1. Pin Description

Pin #	Name	Description	Pin #	Name	Description
1	RF1	RF Port 1	6	CTL2	Control voltage2
2	RF2	RF Port 2	7	GND	Ground
3	GND	Ground	8	RF4	RF Port 4
4	VDD	Supply voltage	9	RF3	RF Port 3
5	CTL1	Control voltage1	10	ANT	Antenna in

Application circuit




Figure 3 Application circuit

Evaluation Board






Figure 4 Evaluation Board Assembly Diagram


Package Outline Dimension



SYMBOL	MILLIMETER		
	MIN	NOM	MAX
A	0.40	0.45	0.50
A1	0.00	0.02	0.05
A2	0.127REF		
b	0.17	0.20	0.23
D	1.45	1.50	1.55
E	1.05	1.10	1.15
D1	0.950	1.00	1.050
E1	0.550	0.60	0.650
e	0.375	0.40	0.425
z	0.05REF		

Figure 5 Package Outline Dimension

Package Dimensions (5000pcs)



W	8.00 ± 0.05	T	0.20 ± 0.02	D1	0.80 ± 0.10
E	1.75 ± 0.10	F	3.50 ± 0.10	D0	1.60 ± 0.10
P0	4.00 ± 0.10	P1	4.00 ± 0.10	P2	2.00 ± 0.10
A0	1.25 ± 0.05	B0	1.88 ± 0.05	K0	0.75 ± 0.05

Figure 6 Tape and Reel Dimensions


Declaration of No Harmful Substances

This part is compliant with 2005/20/EC packaging directive, 1907/2006/EC REACH directive and the 2011/65/EU RoHS directive (Restrictions on the Use of Certain Hazardous Substances in Electrical and Electronic Equipment), as amended by Directive 2015/863/EU.

This product also has the following attributes:

- Lead free
- Halogen Free (Chlorine, Bromine)
- SVHC Free

Reflow Chart



NOTE: Reflow Profile with 240°C peak also acceptable.