



**Part Number :** [887328702](#)


**Product Description :** USB On-The-Go (OTG) Shielded I/O Cable Assembly, USB A-to-Mini B, USB 2.0, 1.50m Length, Black

**Series Number :** 68768

**Status :** New Business Not Supported

**Product Category :** I/O Cable Assemblies

**Engineering Number :** 887-3287-02



---

## Documents & Resources

---

### Product Environment Compliance

#### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

#### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

#### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### EU RoHS Certificate of Compliance

---

### Part Details

## General

Status	New Business Not Supported
Category	I/O Cable Assemblies
Series	68768
Description	USB On-The-Go (OTG) Shielded I/O Cable Assembly, USB A-to-Mini B, USB 2.0, 1.50m Length, Black
Assembly Configuration	Dual Ended Connectors
Connector to Connector	USB Type A-to-Mini-B
Product Name	USB
UPC	800756208404

## Electrical

Current - Maximum per Contact	1.0A
Shielded	Yes
Voltage - Maximum	30V

## Physical

Cable Length	1.50m
Circuits (Loaded)	5
Circuits (maximum)	5
Color - Resin	Black
Gender	Male-Male
Lock to Mating Part	Yes
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	55.200/g
Packaging Type	Bag
Plating min - Mating	0.762µm
Plating min - Termination	4.064µm
Single Ended	No
Wire/Cable Type	Round
Wire Insulation Diameter	N/A
Wire Size (AWG)	28

## Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

---

This document was generated on Jan 21, 2025