

1318620-1


✓ ACTIVE

AMP | 0.64/025 Connector System

TE Internal #: 1318620-1

4 Position Housing, Housing for Female Terminals, Wire-to-Board /
Wire-to-Device, 2 mm [.079 in] Centerline, Blue, Signal, 0.64/025
Connector System[View on TE.com >](#)

Connectors > Automotive Connectors > Automotive Housings > TH/.025 CONNECTOR SYSTEM, HOUSING

Number of Positions: **4**Connector & Housing Type: **Housing for Female Terminals**Mating Tab Width: **.64 mm [.025 in]**Connector System: **Wire-to-Board, Wire-to-Device**Centerline (Pitch): **2 mm [.079 in]**[All TH/.025 CONNECTOR SYSTEM, HOUSING \(177\)](#)

Features

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Dimensions

Product Width	8.6 mm[.339 in]
Product Length	19 mm[.748 in]
Connector Height	9 mm[.354 in]

Packaging Features

Packaging Quantity	100
Packaging Method	Bag

Mechanical Attachment

Strain Relief	Without
Terminal Position Assurance	Yes
Mating Alignment Type	Polarized
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Other

Serviceable	Yes
-------------	-----

Connector Position Assurance Capable	No
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Electrical Characteristics

Operating Voltage	12 VDC
Nominal Voltage Architecture	12 V

Body Features

Cable Exit Angle	180°
Primary Product Color	Blue

Housing Features

Housing Material	PBT
Centerline (Pitch)	2 mm [.079 in]

Contact Features

Contact Size	.63mm
Contact Type	Receptacle
Mating Tab Width	.64 mm [.025 in]

Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Rectangular
Connector & Housing Type	Housing for Female Terminals
Connector System	Wire-to-Board, Wire-to-Device
Sealable	No
Primary Locking Feature	On the Terminal

Configuration Features

Number of Positions	4
Number of Rows	1

Usage Conditions

Operating Temperature (Max)	80 °C, 100 °C, 90 °C, 85 °C, 75 °C, 70 °C [167 °F][158 °F][176 °F][194 °F][185 °F][212 °F]
Operating Temperature Range	-30 – 100 °C [-22 – 212 °F]

Operation/Application

Circuit Application

Signal

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 1376515-1
025 4P V CAP HSG ASSY

TE Part # CAT-T319-T273
TH/025 CONNECTOR SYSTEM,
RECPT AND TAB

Also in the Series | [0.64/025 Connector System](#)



Customers Also Bought





Documents

Product Drawings

025 ANCHOR HEIGHT SENSOR 4POS PLUG HSG

Japanese

CAD Files

3D PDF

English

Customer View Model

[ENG_CVM_1318620-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_1318620-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_1318620-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Crimping of 025 Receptacle Contact

Japanese

Application Specification

Japanese

Instruction Sheets

Instruction Sheet (non U.S.)

Japanese

Instruction Sheet (non U.S.)

Japanese