

Han-Modular coax M-contact 50Ohm (RG174)



Image is for illustration purposes only. Please refer to product description.

Identification

| | |
|----------------------------|------------------------------------|
| Category | Contacts |
| Series | DIN 41626 |
| Type of contact | Coaxial contact |
| Description of the contact | for cables RG 174 U, 188 AU, 316 U |

Version

| | |
|-----------------------|--------------------------|
| Termination method | Solder termination |
| Termination method | Solder/crimp termination |
| Gender | Male |
| Manufacturing process | Turned contacts |

Technical characteristics

| | |
|--------------------|--------|
| Rated current | ≤1.5 A |
| Contact resistance | ≤10 mΩ |
| Impedance | 50 Ω |

Material properties

| | |
|---------------------|--|
| Material (contacts) | Copper alloy |
| Surface (contacts) | Gold plated |
| RoHS | compliant with exemption |
| RoHS exemptions | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status | compliant with exemption |
| China RoHS | 50 |

Material properties

| | |
|--------------------------------------|--------------------------------------|
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Yes |
| REACH SVHC substances | Lead |
| ECHA SCIP number | b51e5b97-eeb5-438b-8538-f1771d43c17d |
| California Proposition 65 substances | Yes |
| California Proposition 65 substances | Lead Nickel |

Specifications and approvals

| | |
|----------------|--------------------------|
| Specifications | IEC 60664-1 IEC 61984 |
|----------------|--------------------------|

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 10 |
| Net weight | 2.14 g |
| Country of origin | Germany |
| European customs tariff number | 85366990 |
| GTIN | 5713140018235 |
| ETIM | EC000796 |
| eCl@ss | 27440204 Contact for industrial connectors |