




Over Voltage and Over Current Protection IC

General Description

The LP5314 is an Over-Voltage-Protection (OVP) and Over-Current-Protection (OCP) device. The device will switch off internal MOSFET to disconnect VIN to VOUT to protect load when any of input voltage, input current over the threshold. The Over temperature protection (OTP) function monitors chip temperature to protect the device.

The LP5314 is available in SOT-23-6 package. Standard products are Pb-free and Halogen-free.


Order Information



Features

- ◆ Input Voltage Range: 3.5V to 36V
- ◆ Typical Output Power on Time: 9ms
- ◆ OVP Threshold: 6.1V
- ◆ OVP Threshold Time Less Than 1 μ s
- ◆ Over Current Protection: 2.1A(MIN)
- ◆ Low $R_{DS(ON)}$ Internal Switches:130m Ω @ 5V /1A
- ◆ Output Discharge
- ◆ Thermal Fault Protection
- ◆ SOT23-6 Package
- ◆ RoHS Compliant and 100% Lead (Pb)-Free

Typical Application Circuit



Applications


- ✧ GPS
- ✧ PMP
- ✧ PAD
- ✧ MID
- ✧ Digital cameras, Digital Videos

Marking Information

Device	Marking	Package	Shipping
LP5314B6F	LP5314 YWX	SOT23-6	3K/REEL
Marking indication: Y:Production year W:Production week X:Production batch			



Functional Pin Description




Pin Description

Pin	Name	Description
1/4	NC	No connection.
2/5	VIN	Input pin. A 1uF low ESR ceramic capacitor or larger must be connected as close as to this pin. It is recommended to use 50V capacitor or according to application.
3	VOUT	Output pin.
6	GND	Ground.



Function Diagram



Absolute Maximum Ratings ^{Note 1}

- ✧ Input Voltage to GND 36V
- ✧ Output Voltage to GND 6.5V
- ✧ Maximum Junction Temperature 150°C
- ✧ Maximum Soldering Temperature (at leads, 10 sec) 260°C

Note 1. Stresses beyond those listed under “Absolute Maximum Ratings” may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

Thermal Information

- ✧ Maximum Power Dissipation (SOT23-6, $P_D, T_A=25^\circ\text{C}$) 0.45W
- ✧ Thermal Resistance (SOT23-6, θ_{JA}) 250°C/W
- ✧ Maximum Power Dissipation (SOT89, $P_D, T_A=25^\circ\text{C}$) 0.7W
- ✧ Thermal Resistance (SOT89, θ_{JA}) 165°C/W

ESD Susceptibility

- ✧ HBM(Human Body Mode) 2KV
- ✧ MM(Machine Mode) 200V

Recommended Operating Conditions

- ✧ Operating Ambient Temperature Range (T_A) -20°C to 85°C
- ✧ Operation Junction Temperature Range -20°C to 125°C






Electrical Characteristics

$T_A=25^{\circ}\text{C}$, unless otherwise noted


Symbol	Parameter	Condition	Min	Typ	Max	Units
DC characteristics and Power-ON-Reset						
V_{IN}	Input Voltage		3.5		36	V
I_Q	Input quiescent current	$V_{IN}=5V, I_{OUT}=0A$		80		μA
R_{ON}	VIN-to-VOUT ON resistance	$V_{IN}=5V, I_{OUT}=1A$		130	145	m Ω
$R_{DISCHARGE}$	Output discharge resistance			3.6		K Ω
UVLO	Under voltage lock out threshold	V_{IN} increasing from 0~3V	2.6	2.8	3	V
$V_{HYS-UVLO}$	Under voltage lock out hysteresis	V_{IN} decreasing from 3~0V		150		mV
T_{ON}	Output power-on time	$V_{IN}=0 \rightarrow 5V$ to output ON		9		ms
Input Over-Voltage-Protection (OVP)						
V_{OVP}	OVP threshold	V_{IN} increasing from 5~7V	5.8	6.1	6.4	V
$V_{HYS-OVP}$	OVP hysteresis	V_{IN} decreasing from 7~5V		300		mV
T_{OVP}	OVP active time	$V_{IN}=5 \rightarrow 10V$			1	μs
$T_{ON(OVP)}$	OVP recovery time	$V_{IN}=10 \rightarrow 5V$ to output ON		9		ms
Input Over-Current-Protection (OCP)						
I_{OCP}	OCP threshold		2.1	2.5		A
t_{OCP}	OCP active time			30		ms
$t_{ON(OCP)}$	OCP recovery time			1		s
Over-Temperature-Protection (OTP)						
T_{OTP}	OTP threshold			150		$^{\circ}\text{C}$
T_{OTP_HYS}	OTP hysteresis			20		$^{\circ}\text{C}$



Typical Operating Characteristics



OVP waveform




VIN falling waveform



Packaging Information

SOT23-6



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	0.889	1.295	0.031	0.051
A1	0.000	0.152	0.000	0.006
B	1.397	1.803	0.055	0.071
b	0.250	0.560	0.010	0.022
C	2.591	2.997	0.102	0.118
D	2.692	3.099	0.106	0.122
e	0.838	1.041	0.033	0.041
H	0.080	0.254	0.003	0.010
L	0.300	0.610	0.012	0.024

SOT-23-6 Surface Mount Package