


TE Internal #: 6368011-4
RJ45 Connector, Multiple Ports, 2 x 1, Jack, Shielded, Cat 5,
Standard - Latch Down, 8 Position, Low Profile, Through Hole -
Solder, AMP-METRIMATE

[View on TE.com >](#)



Connectors > Modular Jacks & Plugs > RJ45 Connectors



Modular Jack & Plug Interface Type: **RJ45**
Port Configuration: **Multiple Ports**
Port Matrix Configuration: **2 x 1**
Modular Jacks & Plugs Products: **RJ Type Jacks & Plugs**
Connector Contact Density: **Standard**

Features

Packaging Features

Packaging Quantity	45
Packaging Method	Tray

Dimensions

PCB Thickness (Recommended)	1.57 mm[.062 in]
Connector Height	31.45 mm[1.23 in]

Mechanical Attachment

Panel Mount Feature	Without
Connector Mounting Type	Panel Mount, Board Mount

Contact Features

Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Current Rating (Max)	1.5 A, .2 A
Contact Mating Area Plating Material	Gold
Contact Base Material	Phosphor Bronze



Contact Mating Area Plating Material Thickness	1.27 µm[50 µin]
Body Features	
LED Color (Bottom Left)	Green/Orange
LED Color (Bottom Right)	Green/Orange
Grounding Tab Plating Material	Tin over Nickel
Shield Plating Material	Tin over Nickel
Shield Material	Copper Alloy
LED Color (Top Right)	Green/Orange
LED Color (Top Left)	Green/Orange
Modular Jack Latch Orientation	Standard - Latch Down
Connector Profile	Low
Industry Standards	
UL Flammability Rating	UL 94V-0
Performance Category	Cat 5
Operation/Application	
Indicator Type	LED
Shielded	Yes
Circuit Application	Signal
Configuration Features	
Number of PCB Ground Tabs	6
Multiple Port Configuration	Stacked
Port Configuration	Multiple Ports
Port Matrix Configuration	2 x 1
Connector Contact Density	Standard
Number of Positions	8
Number of Loaded Positions	8
PCB Mount Orientation	Right Angle
Product Type Features	
Connector Product Type	Connector Assembly
Modular Jack & Plug Interface Type	RJ45
Modular Jacks & Plugs Products	RJ Type Jacks & Plugs
Modular Connector Style	Jack



Grounding Options	PCB and Panel Ground
Connector & Contact Terminates To	Printed Circuit Board

Termination Features

Termination Method to PCB	Through Hole - Solder
Termination Post & Tail Length	2.85 mm[.112 in]

Housing Features

Mating Entry Location	Side
Centerline (Pitch)	1.02 mm[.04 in]
Housing Color	Black
Housing Material	PBT Polyester

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous



materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 188729-1
8P.COVER/SOLD.STOP

Also in the Series | AMP-METRIMATE

Card Edge Power Connectors(1)

Connector Hardware(1)

PCB Headers & Receptacles(8)

Rack & Panel Connectors(1)

Rectangular Power Connectors(2)

SO DIMM Sockets(12)

Wire-to-Board Headers & Receptacles (2)

Customers Also Bought

TE Part #6609117-5
6EGS1-1=F7863 S0

TE Part #5227161-7
RTANG JACK W/MTG PINS, BNC PCB

TE Part #2273011-1
M8 x 1.0 Angled socket Pigtail

TE Part #1648206-1
298-08-01100=SA CONN,SKT



TE Part #1050547-1
2001 5032 00



TE Part #1367147-3
SFP COVER, UNPL, NO LOGO



TE Part #1648384-1
708-73-01109=SA CONTACT,SKT



TE Part #1052552-1
2052 1352 02,SMA FM JACK RECPT



TE Part #6651205-1
CONN,SKT,POS30,MINI DRAWER



TE Part #1650156-2
701-15-02109=CONTACT,PIN,#12

Documents

Product Drawings

STK MJ,2X1,SHLD,G/O BI LEDS

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_6368011-4_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_6368011-4_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_6368011-4_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Application Specification

English

Agency Approvals

UL Report

English

6368011-4

RJ45 Connector, Multiple Ports, 2 x 1, Jack, Shielded, Cat 5, Standard - Latch Down, 8 Position, Low Profile, Through Hole - Solder, AMP-METRIMATE

