N-Ch and P-Ch Fast Switching MOSFETs

- ★ Super Low Gate Charge
- ★ 100% EAS Guaranteed
- ★ Green Device Available
- ★ Excellent CdV/dt effect decline
- ★ Advanced high cell density Trench technology

Product Summary

Green

BVDSS	RDSON	ID
100V	70mΩ	15.0A
-100V	180mΩ	-7.0A

PDFN5060-8L Pin Configuration





Description

The XR20G10F is the highest performance complementary N-ch and P-ch MOSFETs MOSFETs with extreme high cell density, which provide excellent RDSON and gate charge for most of the synchronous buck converter applications .

The XR20G10F meet the RoHS and Green Product requirement, 100% EAS guaranteed with full function reliability approved.

Absolute Maximum Ratings

Symbol	Parameter	Rating		Units
		N-Channel	P-Channel	
V_{DS}	Drain-Source Voltage	100	-100	V
V_{GS}	Gate-Source Voltage	±20	±20	V
I_D@T_A=25℃	Continuous Drain Current, V_{GS} @ 10V[1]	15.0	-7.0	A
I_D@T_A=70℃	Continuous Drain Current, V_{GS} @ 10V[1]	10.0	-4.5	A
I_{DM}	Pulsed Drain Current[2]	25	-9.5	A
EAS	Single Pulse Avalanche Energy[3]	22.5	35.3	mJ
I_{AS}	Avalanche Current	22.6	-26.6	A
P_D@T_A=25℃	Total Power Dissipation[4]	3.5	3.5	W
T_{STG}	Storage Temperature Range	-55 to 150	-55 to 150	℃
T_J	Operating Junction Temperature Range	-55 to 150	-55 to 150	℃

Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
$R_{\theta JA}$	Thermal Resistance Junction-Ambient [1]	---	75	℃/W
$R_{\theta JC}$	Thermal Resistance Junction-Case[1]	---	62.5	℃/W

Electrical Characteristics（T_J = 25°C, unless otherwise noted）

Parameter		Symbol	Test Conditions	Min.	Typ.	Max.	Unit
Static Characteristics							
Drain-Source Breakdown Voltage		$V_{(BR)DSS}$	V_{GS} = 0V, I_D = 250μA	100	-	-	V
Gate-body Leakage current		I_{GSS}	V_{DS} = 0V, V_{GS} = ±20V	-	-	±100	nA
Zero Gate Voltage Drain Current	T_J=25°C	I_{DSS}	V_{DS} =100V, V_{GS} = 0V	-	-	1	μA
	T_J=100°C			-	-	100	
Gate-Threshold Voltage		$V_{GS(th)}$	V_{DS} = V_{GS}, I_D = 250μA	1.2	-	2.5	V
Drain-Source on-Resistance[4]		$R_{DS(on)}$	V_{GS} = 10V, I_D = 5A	-	65	90	mΩ
			V_{GS} = 4.5V, I_D = 3A	-	75	105	
Forward Transconductance[4]		g_{fs}	V_{DS}=5V , I_D=5A	-	12	-	S
Dynamic Characteristics[5]							
Input Capacitance		C_{iss}	V_{DS} = 15V, V_{GS} =0V, f =1MHz	-	1220	-	pF
Output Capacitance		C_{oss}		-	53	-	
Reverse Transfer Capacitance		C_{rss}		-	42	-	
Gate Resistance		R_g	f =1MHz	-	1.3	-	Ω
Switching Characteristics[5]							
Total Gate Charge		Q_g	V_{GS} = 10V, V_{DS} = 50V, I_D=5A	-	20.6	-	nC
Gate-Source Charge		Q_{gs}		-	4	-	
Gate-Drain Charge		Q_{gd}		-	3.7	-	
Turn-On Delay Time		$t_{d(on)}$	V_{GS} =10V, V_{DD} =50V, R_G = 3Ω, I_D= 5A	-	4.7	-	ns
Rise Time		t_r		-	21	-	
Turn-Off Delay Time		$t_{d(off)}$		-	20	-	
Fall Time		t_f		-	16	-	
Drain-Source Body Diode Characteristics							
Diode Forward Voltage[4]		V_{SD}	I_S = 1A, V_{GS} = 0V	-	-	1.2	V
Continuous Source Current	T_C=25°C	I_S	-	-	-	15	A

Notes:

1. Repetitive rating, pulse width limited by junction temperature $T_{J(MAX)}$=150°C.

2.The data tested by pulsed , pulse width ≤ 300us , duty cycle ≤ 2%

3.The EAS data shows Max. rating . The test condition is V_{DD}=25V,V_{GS}=10V,L=0.1mH,I_{AS}=8A

4.The power dissipation is limited by 150°C junction temperature

5.The data is theoretically the same as I_D and I_{DM} , in real applications , should be limited by total power dissipation.

P-Channel Electrical Characteristics (T_J=25 ℃, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	V_{GS}=0V , I_D=-250uA	-100	---	---	V
$R_{DS(ON)}$	Static Drain-Source On-Resistance[2]	V_{GS}=-10V , I_D=-3A	---	180	220	mΩ
		V_{GS}=-4.5V , I_D=-2A	---	210	255	
$V_{GS(th)}$	Gate Threshold Voltage	V_{GS}=V_{DS} , I_D =-250uA	-1.2	---	-2.5	V
I_{DSS}	Drain-Source Leakage Current	V_{DS}=-80V , V_{GS}=0V , T_J=25℃	---	---	-1	uA
		V_{DS}=-80V , V_{GS}=0V , T_J=85℃	---	---	-30	
I_{GSS}	Gate-Source Leakage Current	V_{GS}=±20V , V_{DS}=0V	---	---	±100	nA
R_g	Gate Resistance	V_{DS}=0V , V_{GS}=0V , f=1MHz	---	13	---	Ω
Q_g	Total Gate Charge (-10V)	V_{DS}=-50V , V_{GS}=-10V , I_D=-2A	---	19	---	nC
Q_{gs}	Gate-Source Charge		---	3.4	---	
Q_{gd}	Gate-Drain Charge		---	2.9	---	
$T_{d(on)}$	Turn-On Delay Time	V_{DD}=-30V , V_{GS}=-10V , R_G=3.3Ω, I_D=-1A	---	9	---	ns
T_r	Rise Time		---	6	---	
$T_{d(off)}$	Turn-Off Delay Time		---	39	---	
T_f	Fall Time		---	33	---	
C_{iss}	Input Capacitance	V_{DS}=-30V , V_{GS}=0V , f=1MHz	---	1228	---	pF
C_{oss}	Output Capacitance		---	41	---	
C_{rss}	Reverse Transfer Capacitance		---	29	---	

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I_S	Continuous Source Current[1,5]	V_G=V_D=0V , Force Current	---	---	-7.0	A
V_{SD}	Diode Forward Voltage[2]	V_{GS}=0V , I_S=-1A , T_J=25℃	---	---	-1.2	V

Note :
1.The data tested by surface mounted on a 1 inch^2 FR-4 board with 2OZ copper.
2.The data tested by pulsed , pulse width ≦ 300us , duty cycle ≦ 2%
3.The EAS data shows Max. rating . The test condition is V_{DD}=-25V,V_{GS}=-10V,L=0.5mH,I_{AS}=-14A
4.The power dissipation is limited by 150℃ junction temperature
5.The data is theoretically the same as I_D and I_{DM} , in real applications , should be limited by total power dissipation.

Typical Characteristics



Figure 1. Output Characteristics



Figure 2. Transfer Characteristics



Figure 3. Forward Characteristics of Reverse



Figure 4. $R_{DS(ON)}$ vs. V_{GS}



Figure 5. $R_{DS(ON)}$ vs. I_D



Figure 6. Normalized $R_{DS(on)}$ vs. Temperature



Figure 7. Capacitance Characteristics



Figure 8. Gate Charge Characteristics



Figure 9. Power Dissipation



Figure10. Safe Operating Area



Figure 11. Normalized Maximum Transient Thermal Impedance

P-Channel Typical Characteristics



Fig.1 Typical Output Characteristics



Fig.2 On-Resistance vs G-S Voltage



Fig.3 Source Drain Forward Characteristics



Fig.4 Gate-Charge Characteristics



Fig.5 Normalized $V_{GS(th)}$ vs T_J



Fig.6 Normalized R_{DSON} vs T_J



Fig.7 Capacitance



Fig.8 Safe Operating Area



Fig.9 Normalized Maximum Transient Thermal Impedance



Fig.10 Switching Time Waveform



Fig.11 Unclamped Inductive Waveform

Package Mechanical Data- PDFN5060-8L



Top View



Bottom View



Side View

Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	0.900	1.000	0.035	0.039
A3	0.154REF.		0.006REF.	
D	4.944	5.096	0.195	0.201
E	5.974	6.126	0.235	0.241
D1	1.470	1.870	0.058	0.074
D2	0.470	0.870	0.019	0.034
E1	3.375	3.575	0.133	0.141
D3	4.824	4.976	0.190	0.196
E2	5.674	5.826	0.223	0.229
k	1.190	1.390	0.047	0.055
b	0.350	0.450	0.014	0.018
e	1.270TYP.		0.050TYP.	
L	0.559	0.711	0.022	0.028
L1	0.424	0.576	0.017	0.023
H	0.574	0.726	0.023	0.029
θ	10°	12°	10°	12°