

174552




NUMBER

三 角 法 (3rd ANGLE PROJECTION)

METRIC

単位: mm DIMENSIONS IN MM. DO NOT SCALE PRINT

PRINT DIST



基板穴あけ寸法 (参考)
(PCB LAYOUT (REF))

注 記

1. 嵌合相手プラグハウジング : P/N 1-480424-0
2. 適用製品規格 : 108-5155
3. 適用基板厚 : 1.6mm

NOTES

1. THE PARTY PLUG H.S.G. : P/N 1-480424-0
2. PRODUCT SPEC. : 108-5155
3. PCB THICK : 1.6mm
4. DIMENSION SHOWN REPRESENT PRODUCT IN DRY CONDITION. ADDITIONAL 2% GROWTH DUE TO END USE LOCATION MOISTURE ABSORPTION MAY OCCUR AND SHOULD BE ACCOUNTED FOR.

品番 (ITEM)	仕上り (FINISH)	材 料 (MATERIAL)	名 称 (NAME)	1	4	1	-1
③	ニッケル下地、錫めっき (Ni UNDER PLATE, FINISH Tin)	銅合金 (Cu ALLOY)	クランプ (CLAMP)	1	4	1	-1
②	ニッケル下地、錫めっき (Ni UNDER PLATE, FINISH Tin)	銅合金 (Cu ALLOY)	コンタクト (CONTACT)	1	4	1	-1
①	---	熱可塑性樹脂 (66-NYLON) UL94-V2	ハウジング (HEADER HSG)	1	4	1	-1
項目 (ITEM)	仕上り (FINISH)	材 料 (MATERIAL)	名 称 (NAME)	1	4	1	-1

TE Connectivity

包合電線断面積 (WIRE RANGE) mm ² (AWG -)	被覆外径 (INSULATION DIA.) mmφ	名称 (NAME) 4 極 コマーシャル メイテンロック ピンヘッダー 4 Pos. Com. M-N-L PIN HEADER (固定ベルト付) (WITH FIX BELT)
材料 (MATERIAL) 表参照	仕上 (FINISH)	一般公差 (GENERAL TOLERANCE) 10以下 : ±0.2 10を超え 30以下 : ±0.25 30を超え 100以下 : ±0.3 角 度 : ±3°
E2 REVISED PER ECR-21-117185 PJ VS 20OCT2021 E1 REVISED PER ECO-11-005294 RK HMR 07APR 11 LTR 変更 (REVISION RECORD) DR CHK DATE	DR. 28/MAR/00 Y. KATO CHK. I. HASEGAWA	DE. 22/MAR 00 APP. 22/MAR 00
A3 J C= 174552 尺 度 (SCALE) NOT REV. E2 SHEET 1 OF 1		

(CUSTOMER DRAWING) 参 考 図 面