







NOTES: 备注

- 1.Copper,nickel base,matte tin
黄铜H62, 镍底, 镀雾锡
- 2.Wire screw hole M4
压线螺孔M4
- 3.Current Rating: 60A
额定电流: 60A
- 4.Operating temperature: -40℃ ~ +125℃
工作温度: -40℃ ~ +125℃
- 5.There shall be no defects such as pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
- 6.Unmarked dimensions refer to tolerances
未标注的尺寸参考公差



Ordering Information

HC - * * * * - * * * * - 02

Type	Screw Thread	Welding Feet	T=Anti Twist	Series	D=Pin	Product No.	Material
M=Pull Teeth (抽牙)	S=M5 (螺牙)	1620-16x20mm	(防扭扭)	0808-8x8mm	S=MT	产品序号	默认=Copper (黄铜)
RS=Rivet Nut (铆螺母)	4=M4 (螺牙)	2-2个			FD=Flag Dip		默认=Copper (黄铜)
RG=Rivet Gasket (铆垫片)	S=M5 (螺牙)	4-4个					
	6=M6 (螺牙)	6-6个					
		8-8个					

			GENERAL TOLERANCE	制 图 DRAWING	02					 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD		
			DIM TOL	审 核 CHECK								
			5 or more ±0.35	批 准 APPROVAL	产品名称 TITLE		PCB 焊接端子 插板 铆垫片 M4 4焊脚 10x10.5x13.9mm 四脚防扭 壁0.8		版 本 REV.	A		
1	初版发行		2~5 ±0.25	比 例 SCALE	产品料号 PART NO.		HC-RG44T-1010-D070-02		单 位 UNITS	mm		
序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE	0~2 ±0.15	投 影 Projection			材 料 MATERIAL		页 次 SHEET	1/1		
			Angle ±3.0°									