








- NOTES:
备注
- 1.Copper,nickel base,matte tin
黄铜H62, 镍底, 镀雾锡
 - 2.Wire screw hole M5
压线螺孔M5
 - 3.Current Rating: 70A
额定电流: 70A
 - 4.Operating temperature: -40℃ ~ +125℃
工作温度: -40℃ ~ +125℃
 - 5.There shall be no defects such as pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
 - 6.Unmarked dimensions refer to tolerances
未标注的尺寸参考公差



Ordering Information

HC - * * * - * * * - * * * - 02

Type	Screw Thread	Welding Feet	Series	D-BIP	Product No.	Material
M-Pull Teeth (抽牙)	S-M5 (螺牙)	(焊脚)	0808-8x8mm	S-SMT	产品序号	默认=Copper (黄铜)
BN-Rivet Nut (铆螺母)	4-M4 (螺牙)	2-2个	163D-16x20mm	FD-Flag BIP		HC=Red Copper (紫铜)
RG-Rivet Gasket (铆垫片)	S-M5 (螺牙)	4-4个				
	6-M6 (螺牙)	6-6个				
		8-8个				

			GENE RL TOL E RANCE	制 图	02	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD		
			DIM TOL	审 核				
			5 or more ±0.35	批 准		产品名称	PCB 焊接端子 插板 抽牙 M5	版 本
			2~5 ±0.25	APPROVAL		TITLE	6焊脚 14.5x14.5x12mm	REV.
			0~2 ±0.15	比 例		产品料号	HC-M56-1414-D067-02	单 位
			Angle ±3.0°	SCALE		PART NO.		UNITS
1	初版发行			投 影		材料		页 次
序号	变更内容	日期		Projection		MATERIAL		SHEET
No.	MODIFY CONTENT	MODIFY DATE						