







参考安装方式

NOTES:

备注

1. Copper, nickel base, matte tin
黄铜H62, 镍底, 镀雾锡
2. Wire screw hole M4
压线螺孔M4
3. Current Rating: 70A
额定电流: 70A
4. Operating temperature: -40°C ~ +125°C
工作温度: -40°C ~ +125°C
5. There shall be no defects such as pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
6. Unmarked dimensions refer to tolerances
未标注的尺寸参考公差



Ordering Information

HC - * * * - * * * - * * * - 02

Type	Screw Thread	Welding Feet	Series	D-BIP	Product No.	Material
M-Pull Teeth (铆牙)	3-M5 (螺牙)	0808-8x8mm (焊脚)	0808-8x8mm 1620-16x20mm	S-SMT FD-Flag DIP	产品序号	默认=Copper (黄铜) HC=Red Copper (紫铜)
BN-Rivet Nut (铆螺母)	4-M4 (螺牙)	2~2个				
RG-Rivet Gasket (铆垫片)	5-M5 (螺牙)	4~4个				
	6-M6 (螺牙)	6~6个				
		8~8个				

			GENEAL TOLERANCE	制 图 DRAWING	02	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM TOL	审 核 CHECK		产品名称 TITLE	PCB 焊接端子 插板 铆垫片 M4 4焊脚 11.2x9.2x16mm	版 本 REV.	A
			5 or more ±0.35	批 准 APPROVAL		产品料号 PART NO.	HC-RG44-1109-D075-02	单 位 UNITS	mm
1	初版发行		2~5 ±0.25	比 例 SCALE		材 料 MATERIAL		页 次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE	Angle ±3.0°	投 影 Projection					