







NOTES:

备注

1. Copper, nickel base, matte tin
黄铜H62, 镍底, 镀雾锡
2. Wire screw hole M5
压线螺孔M5
3. Current Rating: 70A
额定电流: 70A
4. Operating temperature: -40°C ~ +125°C
工作温度: -40°C ~ +125°C
5. There shall be no defects such as pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
6. Unmarked dimensions refer to tolerances
未标注的尺寸参考公差



Ordering Information

HC - * * * - * * * - * * * - 02

Type	Screw Thread	Welding Feet	Series	D-BIP	Product No.	Material
M-Pull Teeth (抽牙)	S-M5 (螺牙)	(焊脚)	0808-8x8mm	S-SMT	产品序号	默认=Copper
BN-Rivet Nut (铆螺母)	4-M4 (螺牙)	2-2个	163D-16x20mm	FD-Flag		(黄铜)
RG-Rivet Gasket (铆垫片)	S-M5 (螺牙)	4-4个		Dip		HC=Red Copper (紫铜)
	6-M6 (螺牙)	6-6个				

			GENERAL TOLERANCE	制图 DRAWING	02	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM TOL	审核 CHECK		产品名称 TITLE	PCB 焊接端子 插板 抽牙 M5 4焊脚 12x12x13.4mm	版本 REV.	A
			5 or more ±0.35	批准 APPROVAL		产品料号 PART NO.	HC-M54-1212-D069-02	单位 UNITS	mm
1	初版发行		2~5 ±0.25	比例 SCALE		材料 MATERIAL		页次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	0~2 ±0.15	投影 Projection					
			Angle ±3.0°						