Product Summary

$V_{(BR)DSS}$	$R_{DS(on)TYP}$	I_D
80V	3.8mΩ@10V	130A

合肥矽普半导体
Siliup Semiconductor Technology Co.Ltd
技术 品质 服务
www.siliup.com

Feature

- Fast Switching
- Low Gate Charge and Rdson
- Advanced Split Gate Trench Technology
- 100% Single Pulse avalanche energy Test

Applications

- Power switching application
- DC-DC Converter
- Uninterruptible power supply

Package



TO-220-3L(1:G 2:D 3:S)

Circuit diagram



Marking



80N03BGH :Device Code
** :Week Code

Order Information

Device	Package	Unit/Tube
SP80N03BGHTQ	TO-220-3L	50

Absolute maximum ratings (Ta=25℃,unless otherwise noted)

Parameter	Symbol	Rating	Unit
Drain-Source Voltage	V_{DSS}	80	V
Gate-Source Voltage	V_{GSS}	±20	V
Continuous Drain Current (Tc=25°C)	I_D	130	A
Continuous Drain Current (Tc=100°C)	I_D	90	A
Pulse Drain Current Tested	I_{DM}	520	A
Single Pulse Avalanche Energy[1]	E_{AS}	576	mJ
Power Dissipation (Tc=25°C)	P_D	160	W
Thermal Resistance Junction-to-Case	$R_{\theta JC}$	0.78	°C/W
Maximum Junction Temperature	T_J	-55 to 150	°C
Storage Temperature Range	T_{STG}	-55 to 150	°C

Electrical characteristics (Ta=25℃, unless otherwise noted)

Characteristics	Symbol	Test Condition	Min	Typ	Max	Unit
Static Characteristics						
Drain-Source Breakdown Voltage	BV_{DSS}	I_D = 250μA, V_{GS} = 0V	80	-	-	V
Zero Gate Voltage Drain Current	I_{DSS}	V_{DS} = 64V, V_{GS} = 0V	-	-	1	uA
Gate Leakage Current	I_{GSS}	V_{GS} = ±20V, V_{DS} = 0V	-	-	±100	nA
Gate Threshold Voltage	$V_{GS(th)}$	V_{DS} = V_{GS}, I_D = 250μA	2.0	3.0	4.0	V
Drain-Source On-state Resistance	$R_{DS(ON)}$	V_{GS} = 10V, I_D = 20A	-	3.8	4.8	mΩ
Dynamic Characteristics						
Input Capacitance	C_{iss}	VGS=0V, VDS=40V,F=1MHz	-	4360	-	pF
Output Capacitance	C_{oss}		-	500	-	
Reverse Transfer Capacitance	C_{rss}		-	26	-	
Total Gate Charge	Q_g	VDS=40V, VGS=10V, ID=20A	-	42	-	nC
Gate-Source Charge	Q_{gs}		-	15	-	
Gate-Drain Charge	Q_{gd}		-	20	-	
Switching Characteristics						
Turn-On Delay Time	$t_{d(on)}$	VDD=40V, ID=20A, VGS=10V, R_G=3Ω	-	17	-	nS
Rise Time	t_r		-	39	-	
Turn-Off Delay Time	$t_{d(off)}$		-	64	-	
Fall Time	t_f		-	42	-	
Drain-Source Body Diode Characteristics						
Source-Drain Diode Forward Voltage	V_{SD}	VGS=0V , IS=1A , TJ=25℃	-	-	1.2	V
Maximum Body-Diode Continuous Current	I_S		-	-	130	A
Reverse Recovery Time	Trr	I_S=50 A,di/dt=100 A/μs, T_J=25℃	-	45	-	nS
Reverse Recovery Charge	Qrr		-	56	-	nC

Note :

1. The test condition is VDD=40V,VGS=10V,L=0.5mH,RG=25Ω

Typical Characteristics



Output Characteristics



Transfer Characteristics



Capacitance Characteristics



Gate Charge



Current dissipation



Power dissipation



RDS(on) VS Drain Current



Forward characteristics of reverse diode



Normalized breakdown voltage



Normalized Threshold voltage



Maximum Transient Thermal Impedance



Safe Operation Area

TO-220-3L Package Information



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	4.400	4.600	0.173	0.181
A1	2.250	2.550	0.089	0.100
b	0.710	0.910	0.028	0.036
b1	1.170	1.370	0.046	0.054
c	0.330	0.650	0.013	0.026
c1	1.200	1.400	0.047	0.055
D	9.910	10.250	0.390	0.404
E	8.950	9.750	0.352	0.384
E1	12.650	13.050	0.498	0.514
e	2.540 TYP.		0.100 TYP.	
e1	4.980	5.180	0.196	0.204
F	2.650	2.950	0.104	0.116
H	7.900	8.100	0.311	0.319
h	0.000	0.300	0.000	0.012
L	12.900	13.400	0.508	0.528
L1	2.850	3.250	0.112	0.128
V	6.900 REF.		0.276 REF.	
Φ	3.400	3.800	0.134	0.150