




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Tab**

Wire Size: **4 – 6 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Electrical Characteristics

Voltage Rating	250 V
----------------	-------

Mechanical Attachment

Locking Lance Height	1.5 mm
Wire Insulation Support	With
Mating Retention Type	Locking Lance

Packaging Features

Packaging Quantity	2500
--------------------	------



Packaging Method	Strip/Reel
------------------	------------

Dimensions

Product Length	30.1 mm[1.185 in]
Compatible Insulation Diameter Range	3.4 – 5.2 mm[.134 – .201 in]
Terminal Material Thickness	.41 mm[.016 in]
Wire Size	4 – 6 mm²

Product Type Features

Insertion Force	Normal
-----------------	--------

Contact Features

Quick Disconnect Terminal Type	Tab
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Pre-Tin
Crimp Type	F-Crimp
Barrel Type	Open

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC




Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 175040-1
FF 187 REC 0.5-1.25MM2 PTBR



TE Part # 7-2150459-7
OCEAN_2.0_SPARE_PART_KIT-160F210F




TE Part # 2150459-2
OCEAN_2.0_Applicator-E-160F210F-REA



TE Part # 151667-4
FF 375 REC TERMINAL 11-10 AWG PBR

Also in the Series | FASTIN-FASTON 250



Crimp Terminal Housings(207)



Insertion & Extraction Tools(2)




PCB Terminals(2)




Quick Disconnects(250)

Customers Also Bought



TE Part #480054-3
FF 250 REC HSG 1P NYLON NAT




TE Part #1-174933-1
070 MLC W-W CAP HSG 12P F/A



TE Part #CAT-M4595-T273
MCON Receptacle and Tab



TE Part #2318600-1
12POS,MCON 0.5,REC HSG ASSY,SLD, COD A



TE Part #917531-1
040 MLC T.F. PLUG HSG 14P NATU




TE Part #1-2350416-0
DYNAMIC 1100D TAB HSG 40P P/M GF33



TE Part #2399121-1
MATENET, FEMALE INSERT MODUL



TE Part #2322948-1
6POS,MQS,REC HSG,UNSLD



TE Part #2405580-1
12POS,MCON 0.5,REC HSG,UNSLD, COD A

Documents

Product Drawings

FF 250 TAB TERMINAL 11-10 AWG PTPB

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_280080-2_Z.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_280080-2_Z.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_280080-2_Z.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

Application Specification

280080-2

Quick Disconnect Tab, 11 – 10 AWG, 4 – 6 mm² Wire, 6.35 mm [.25 in] Tab Width,
Straight, Brass, Pre-Tin Plating, Strip/Reel, FASTIN-FASTON 250



English