



Sensors > Force Sensors > Force Sensor Elements > Compact Compression Load Cell



Force Sensor Type: OEM Compression Load Cells

Full Scale Range: 10 lbf

Operating Temperature Range: 0 – 50 °C [ 32 – 122 °F ]

Output Signal Type: 4V

EU RoHS Compliance: Compliant with Exemptions

[All Compact Compression Load Cell \(46\)](#)

Features

Other

|                    |                           |
|--------------------|---------------------------|
| Sensitivity Shift  | ±.05 % of FS              |
| Zero Shift in CTR  | ±.05 % of FS              |
| Force Direction    | Compression               |
| EU RoHS Compliance | Compliant with Exemptions |
| EU ELV Compliance  | Compliant                 |

Usage Conditions

|                             |                        |
|-----------------------------|------------------------|
| Accuracy                    | ±1 % of FS             |
| Operating Temperature Range | 0 – 50 °C[32 – 122 °F] |

Electrical Characteristics

|                      |        |
|----------------------|--------|
| Supply Voltage Range | 5 VDC  |
| Full Scale Range     | 10 lbf |

Product Type Features

|                   |                            |
|-------------------|----------------------------|
| Force Sensor Type | OEM Compression Load Cells |
|-------------------|----------------------------|

Operation/Application

|                    |    |
|--------------------|----|
| Output Signal Type | 4V |
|--------------------|----|



Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                                |
|-----------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant with Exemptions                                                                                                      |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                      |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold                                                                                           |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2024 (241)<br>Candidate List Declared Against: JAN 2024 (240)<br>Does not contain REACH SVHC |
| Halogen Content                               | Not Yet Reviewed for halogen content                                                                                           |
| Solder Process Capability                     | Not reviewed for solder process capability                                                                                     |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




Also in the Series | MEAS FX29



Force Sensor Elements(46)

Customers Also Bought



TE Part #2-5499206-9  
A/L UNIV HDR 40P VERT LG LAT B



TE Part #211903-1  
CMC DUST CAP ASSM SIZE 22



TE Part #1825910-3  
FSM2JAH=6MM TACT SWITCH, HIGH TEMP



TE Part #CAT-FSE0006  
Compact Compression Load Cell



TE Part #521210-5  
HSG,RAST 5,POSI LOCK MKIII,8P



TE Part #4-1879495-2  
CRGH0603 5% 680K 0.2W



TE Part #2108991-1  
Helical Antenna,PCB,SMT, For IoT



TE Part #1SNA290213R0400  
DR2.5/10.N.4L



TE Part #1SNA290219R1200  
DR2.5/10.P.4L

Documents

Datasheets & Catalog Pages  
FX29 COMPRESSION LOAD CELL

English