

Product Summary

$V_{(BR)DSS}$	$R_{DS(on)TYP}$	I_D
-20V	27mΩ@-4.5V	-5A
	36mΩ@-2.5V	



合肥矽普半导体

Siliup Semiconductor Technology Co., Ltd

技术 品质 服务

www.siliup.com


Feature

- High power and current handling capability
- Surface mount package
- ESD protected 2KV

Application


- Battery Switch
- DC/DC Converter

Package




SOT-23

Circuit diagram



Marking



Order Information

Device	Package	Unit/Tape
SP3415LKT2	SOT-23	3000


Absolute maximum ratings (Ta=25°C, unless otherwise noted)

Parameter	Symbol	Value	Unit
Drain-Source Voltage	V_{DS}	-20	V
Gate-Source Voltage	V_{GS}	± 10	V
Continuous Drain Current	I_D	-5	A
Pulse Drain Current Tested	I_{DM}	-20	A
Power Dissipation	P_D	0.9	W
Thermal Resistance Junction-to-Ambient	$R_{\theta JA}$	138.8	°C/W
Storage Temperature Range	T_{STG}	-55 to 150	°C
Operating Junction Temperature Range	T_J	-55 to 150	°C


Electrical characteristics (Ta=25°C, unless otherwise noted)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Static Characteristics						
Drain-Source Breakdown Voltage	BV _{DSS}	VGS=0V , ID=-250μA	-20	-	-	V
Drain-Source Leakage Current	IDSS	VDS=-16V , VGS=0V	-	-	-1	uA
Gate-Source Leakage Current	IGSS	VGS=±10V , VDS=0V	-	-	±5	uA
Gate Threshold Voltage	VGS(th)	VDS=VGS , ID=-250μA	-0.4	-0.65	-1.0	V
Static Drain-Source On-Resistance	RDS(ON)	VGS=-4.5V , ID =-4A	-	27	34	mΩ
		VGS=-2.5V , ID =-3A	-	36	48	
Dynamic characteristics						
Input Capacitance	Ciss	VDS=-10V , VGS=0V , f=1MHz	-	550	-	pF
Output Capacitance	Coss		-	125	-	
Reverse Transfer Capacitance	Crss		-	96	-	
Total Gate Charge	Qg	VDS=-10V , VGS=-4.5V , ID=-5A	-	14	-	nC
Gate-Source Charge	Qgs		-	2	-	
Gate-Drain Charge	Qgd		-	2.5	-	
Switching Characteristics						
Turn-On Delay Time	td(on)	VDD=-10V VGS=-4.5V , RG=3Ω , RL=2.5Ω	-	5	-	nS
Turn-On Rise Time	tr		-	46	-	
Turn-Off Delay Time	td(off)		-	55	-	
Turn-Off Fall Time	tf		-	67	-	
Source-Drain Diode characteristics						
Diode Forward Voltage	VSD	VGS=0V , IS=-1A , TJ=25℃	-	-	-1.2	V


Typical Characteristics




Output Characteristics




Transfer Characteristics




Capacitance Characteristics




Gate Charge




Current dissipation




Power dissipation




$R_{DS(on)}$ VS Drain Current




Forward characteristics of reverse diode




Normalized breakdown voltage



Normalized Threshold voltage




Maximum Transient Thermal Impedance



Safe Operation Area

SOT-23 Package Information



Symbol	Dimensions In Millimeters	
	Min.	Max.
A	0.90	1.15
A1	0.00	0.10
A2	0.90	1.05
b	0.30	0.50
c	0.08	0.15
D	2.80	3.00
E	1.20	1.40
E1	2.25	2.55
e	0.95 REF.	
e1	1.80	2.00
L	0.55 REF.	
L1	0.30	0.50
θ	0°	8°