


EMI & EMC Solutions > EMI Filters > Power Line Filters > DC Filters > DC Power Line Filters, Corcom DC Series



Current Rating: **15 A**

Operating Voltage: **80 VDC**

Input Termination Type: **Terminal Block**

Output Termination Type: **Terminal Block**

EU RoHS Compliance: **Compliant**

[All DC Power Line Filters, Corcom DC Series \(0\)](#)

Features

Mechanical Attachment

Panel Mount Feature Type	Flange
--------------------------	--------

Body Features

Product Orientation	Straight
---------------------	----------

Product Type Features

Filtering Requirements	Filtered
Input Termination Type	Terminal Block
Output Termination Type	Terminal Block

Electrical Characteristics

Current Rating	15 A
Operating Voltage	80 VDC

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series

Customers Also Bought



TE Part #420356-000
RMW-35/12-1200/ADH-0



TE Part #DT06-3S-E003
PLG, 3P, GRY, N, CAP



TE Part #YDTS26F13-98SNV001
PLUG ASSY



TE Part #160136
TERM, RING, PLASTI-GRIP, 16-14, M10




TE Part #1586314-1
VAL-U-LOK PIN BR TN 22-18 LP



TE Part #1622796-1
YR1 0.1% 100K



TE Part #770854-1
CONTACT, AMPSEAL SN/LP



TE Part #2-1617076-4
3SBH1227A2 = M39016/53-008M



TE Part #4-2176480-3
RA73F 1J 1K5 0.1% 5K RL

Documents

Product Drawings

15DCF10 J0=F7935

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1-6609074-1_O.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-6609074-1_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-6609074-1_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654001_Corcom_Product_Guide_DC_Series](#)

English

[Corcom Combined Selector Charts](#)

English

[1-1654250-1_CORCOM_EMI_RFI_QRG](#)

English