



TE Internal #: 1735284-5

SATA, Receptacle, Cable-to-Board, 22 Position, 7P + 15P, Standard Profile, Vertical, Surface Mount, 1 Row, 2 Port, Top, 1.27 mm [.05 in] Centerline

[View on TE.com >](#)

Connectors > Audio & Video Connectors > SATA & Micro SATA



SATA Connector Type: **SATA**

Connector & Housing Type: **Receptacle**

Connector System: **Cable-to-Board**

Number of Positions: **22**

Contact Configuration: **7P + 15P**

Features

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Tray, Box & Tray
Packaging Quantity	48

Housing Features

Housing Material	High Temperature Thermoplastic
Housing Color	Black
Centerline (Pitch)	1.27 mm[.05 in]

Mechanical Attachment

PCB Mount Retention Feature Length	.8 mm[.032 in]
Mating Alignment Type	Polarization
PCB Mount Retention Type	Solder Peg
PCB Mount Retention	With
PCB Mount Location	Top



Connector Mounting Type	Board Mount
Dimensions	
PCB Thickness (Recommended)	1.2 mm[.048 in]
Profile Height from PCB	8.15 mm[.32 in]
Contact Features	
Contact Mating Area Plating Material	Gold
Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material Thickness	.76 µm[30 µin]
Contact Configuration	7P + 15P
Contact Current Rating (Max)	1.5 A
Product Type Features	
SATA Connector Type	SATA
Connector & Housing Type	Receptacle
Connector System	Cable-to-Board
Connector & Contact Terminates To	Printed Circuit Board
Configuration Features	
Number of Positions	22
PCB Mount Orientation	Vertical
Number of Rows	1
Number of Ports	2
Body Features	
Connector Profile	Standard
Termination Features	
Termination Method to PCB	Surface Mount
Usage Conditions	
Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
Operation/Application	
Circuit Application	Power & Signal
Other	
EU RoHS Compliance	Compliant



EU ELV Compliance

Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought



TE Part #6418370001
TMS-SCE-1/8-2.0-4



TE Part #120953-5
UPM EXPANDED RCPT ASSEMBLY



TE Part #173081-2
EIS POST ASSY V 2P GOLD NATU.




TE Part #1241150-3
3P MOD II BREAK AWAY HDR,SMD, BLISTER



TE Part #171825-4
TYPE V EIS CONNECTOR 4P ASSY



TE Part #6469028-1
HM-ZD 2PR RECP 40P



TE Part #3-6318490-6
.5FHR04H,220,S,GIG,08/Sn,HT,NSYes



TE Part #6469025-1
HM-ZD 2PR HDR 40P 2.5MM



TE Part #5-2301994-6
RJ45 JACK INT.MAG. 1GB 1X1



TE Part #1-178314-2
DYNAMIC D3100 HDR 4P ASSY V K/X

Documents

Product Drawings

SATA BACKPLANE RECEPTACLE, VERTICAL, SMT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1735284-5_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1735284-5_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1735284-5_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



Product Specification

English

Agency Approvals

UL Report

English