



Passive Components > Resistors > Through-Hole Resistors



Resistor Type: **Power Resistor**
Element Type: **Metal Oxide Film**
Power Rating: **2 W**
Resistance Class: **Up to 1kΩ**
Resistance Value: **1.8 Ω**

Features

Usage Conditions

Operating Temperature Range	-55 – 235 °C
Temperature Coefficient	±350 ppm/°C

Product Type Features

Resistor Type	Power Resistor
Element Type	Metal Oxide Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Power Rating	2 W
Resistance Class	Up to 1kΩ
Resistance Value	1.8 Ω
Passive Component Tolerance	5 %

Body Features

Lead Type	Axial-Leaded
-----------	--------------

Termination Features

Termination Area Base Material	Copper
Number of Terminations	2



Dimensions

Passive Component Dimensions	5.5 x 16 mm
------------------------------	-------------

Packaging Features

Packaging Method	Ammo Packed
------------------	-------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

ROX2SJ1R8

Through-Hole Power Resistor, Metal Oxide Film, 2 W, 1.8 ohm, 5 %, ±350 ppm/°C, Axial-Leaded, Copper Termination, 5.5 x 16 mm, Ammo Packed, Neohm ROX



TE Part # 1625893-5
5W SM M/OX 5% 47K

TE Part # 4-1625886-1
1W SM M/OX 5% 820K

TE Part # 1625881-2
1W STD M/OX 2% 220R

TE Part # 2-1625892-1
3W SM M/OX 5% 1K0

TE Part # 6-1676123-7
1/2W SM M/OX 5% 470R

Also in the Series | **Neohm ROX**

[Through-Hole Resistors\(783\)](#)

Customers Also Bought

TE Part #1-2176045-5
EP 5W 1K5 5%

TE Part #1614746-1
RN 0805 249K 0.5% 50PPM 1K RL

TE Part #1614984-1
LR0204 1% 11R

TE Part #1622207-1
LR0204 1% 27R

TE Part #1622232-1
LR0204 1% 3K9


TE Part #1622263-1
LR0204 1% 620R

TE Part #1622473-8
LR1 1% 422R

TE Part #3-1676915-1
YR1 0.1% 88K7

ROX2SJ1R8

Through-Hole Power Resistor, Metal Oxide Film, 2 W, 1.8 ohm, 5 %, ±350 ppm/°C, Axial-Leaded, Copper Termination, 5.5 x 16 mm, Ammo Packed, Neohm ROX



Documents

Product Drawings

2W SM M/OX 5% 1R8

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-1625890-9_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-1625890-9_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-1625890-9_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

4-1773460-6_RESISTIVE_SOLUTIONS_RAIL

English

1309350_PASSIVE_COMPONENT

English

Flame Proof Power Metal Oxide Film Resistors - Type ROX Series - Tyco Electronics Passives

English

8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS

English