SP010N02GHTQ

100V N-Channel Power MOSFET

Product Summary

$V_{(BR)DSS}$	$R_{DS(on)TYP}$	I_D
100V	2.2mΩ@10V	270A

Feature

- Fast Switching
- Low Gate Charge and Rdson
- Advanced Split Gate Trench Technology
- 100% Single Pulse avalanche energy Test

Applications

- PWM Application
- Hard switched and high frequency circuits
- Power Management

Package



TO-220-3L(1:G 2:D 3:S)

Circuit diagram



Marking



010N02GH :Product code
**** :Week code

Order Information

Device	Package	Unit/Tube
SP010N02GHTQ	TO-220-3L	50

Absolute maximum ratings (Ta=25℃,unless otherwise noted)

Parameter	Symbol	Rating	Unit
Drain-Source Voltage	V_{DS}	100	V
Gate-Source Voltage	V_{GS}	±20	V
Continuous Drain Current (Tc=25℃)	I_D	270	A
Continuous Drain Current (Tc=100℃)	I_D	180	A
Pulsed Drain Current	I_{DM}	1080	A
Single Pulse Avalanche Energy[1]	E_{AS}	1560	mJ
Power Dissipation (Tc=25℃)	P_D	260	W
Thermal Resistance Junction-to-Case	$R_{\theta JC}$	0.48	℃/W
Storage Temperature Range	T_{STG}	-55 to 150	℃
Operating Junction Temperature Range	T_J	-55 to 150	℃

Electrical characteristics (Ta=25℃, unless otherwise noted)

Characteristics	Symbol	Test Condition	Min	Typ	Max	Unit
Static Characteristics						
Drain-Source Breakdown Voltage	BV_{DSS}	VGS=0V , ID=250uA	100	-	-	V
Drain Cut-Off Current	I_{DSS}	VDS=80V , VGS=0V , TJ=25℃	-	-	1	μA
Gate Leakage Current	I_{GSS}	VGS=±20V , VDS=0V	-	-	±100	nA
Gate Threshold Voltage	$V_{GS(th)}$	VGS=VDS , ID =250uA	2	2.8	4	V
Drain-Source ON Resistance	$R_{DS(ON)}$	VGS=10V , ID=20A	-	2.2	2.75	mΩ
Dynamic Characteristics						
Input Capacitance	C_{iss}	VDS=50V , VGS=0V , f=1MHz	-	13420	-	pF
Output Capacitance	C_{oss}		-	2034	-	
Reverse Transfer Capacitance	C_{rss}		-	48	-	
Total Gate Charge	Q_g	VDS=50V , VGS=10V , ID=125A	-	156	-	nC
Gate-Source Charge	Q_{gs}		-	51	-	
Gate-Drain Charge	Q_{gd}		-	45	-	
Switching Characteristics						
Turn-On Delay Time	$t_{d(on)}$	VDD=50V, VGS=10V , RG=1.6Ω, ID=125A	-	35	-	nS
Rise Time	t_r		-	68	-	
Turn-Off Delay Time	$t_{d(off)}$		-	150	-	
Fall Time	t_f		-	105	-	
Drain-Source Body Diode Characteristics						
Source-Drain Diode Forward Voltage	V_{SD}	I_S = 1A, VGS = 0V	-	-	1.2	V
Maximum Body-Diode Continuous Current	I_S		-	-	270	A
Reverse Recovery Time	Trr	I_S=50A, di/dt=100A/us, TJ=25℃	-	106	-	nS
Reverse Recovery Charge	Qrr		-	328	-	nC

Note :

1. The test condition is VDD=50V,VGS=10V,L=0.5mH,RG=25Ω

Typical Characteristics



Saturation Characteristics



Transfer Characteristics



$R_{DS(ON)}$ vs. Drain Current



$R_{DS(ON)}$ vs. Junction Temperature



$V_{GS(th)}$ vs. Junction Temperature



$V_{BR(DSS)}$ vs. Junction Temperature



Body-Diode Characteristics



Capacitance Characteristics



Current De-rating



Power De-rating



Maximum Safe Operating Area



Single Pulse Power Rating, Junction-to-Case

TO-220-3L Package Information



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	4.400	4.600	0.173	0.181
A1	2.250	2.550	0.089	0.100
b	0.710	0.910	0.028	0.036
b1	1.170	1.370	0.046	0.054
c	0.330	0.650	0.013	0.026
c1	1.200	1.400	0.047	0.055
D	9.910	10.250	0.390	0.404
E	8.950	9.750	0.352	0.384
E1	12.650	13.050	0.498	0.514
e	2.540 TYP.		0.100 TYP.	
e1	4.980	5.180	0.196	0.204
F	2.650	2.950	0.104	0.116
H	7.900	8.100	0.311	0.319
h	0.000	0.300	0.000	0.012
L	12.900	13.400	0.508	0.528
L1	2.850	3.250	0.112	0.128
V	6.900 REF.		0.276 REF.	
Φ	3.400	3.800	0.134	0.150