

Product Summary

$V_{(BR)DSS}$	$R_{DS(on)TYP}$	I_D
-20V	7.5mΩ@-4.5V	-18A
	9mΩ@-2.5V	



合肥矽普半导体

Siliup Semiconductor Technology Co., Ltd

技术 品质 服务

www.siliup.com


Feature

- Fast Switching
- Low Gate Charge and Rdson
- 100% Single Pulse avalanche energy Test


Applications

- Power Switching Application
- Hard switched and high frequency circuits
- Uninterruptible Power Supply


Package



Circuit Diagram



Marking



Order Information

Device	Package	Unit/Tape
SP20P08P8	SOP-8L	4000


Absolute maximum ratings (Ta=25°C, unless otherwise noted)

Parameter	Symbol	Rating	Units
Drain-Source Voltage	V_{DS}	-20	V
Gate-Source Voltage	V_{GS}	± 8	V
Continuous Drain Current	I_D	-18	A
Pulsed Drain Current	I_{DM}	-72	A
Power Dissipation	P_D	1.5	W
Thermal Resistance Junction-to-Ambient	$R_{\theta JA}$	83	$^{\circ}C/W$
Storage Temperature Range	T_{STG}	-55 to 150	$^{\circ}C$
Operating Junction Temperature Range	T_J	-55 to 150	$^{\circ}C$


Electrical characteristics (Ta=25°C, unless otherwise noted)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Static Characteristics						
Drain-Source Breakdown Voltage	BV _{DSS}	VGS=0V , ID=-250uA	-20	-	-	V
Drain-Source Leakage Current	IDSS	VDS=-16V , VGS=0V	-	-	-1	uA
Gate-Source Leakage Current	IGSS	VGS=±8V , VDS=0V	-	-	±100	nA
Gate Threshold Voltage	VGS(th)	VGS=VDS , ID =-250uA	-0.5	-0.65	-1.0	V
Static Drain-Source On-Resistance	RDS(ON)	VGS=-4.5V , ID=-10A	-	7.5	9	mΩ
		VGS=-2.5V , ID=-8A	-	9	12	
Dynamic characteristics						
Input Capacitance	Ciss	VDS=-10V , VGS=0V , f=1MHz	-	4600	-	pF
Output Capacitance	Coss		-	460	-	
Reverse Transfer Capacitance	Crss		-	459	-	
Total Gate Charge	Qg	VDS=-10V , VGS=-4.5V , ID=-5A	-	46	-	nC
Gate-Source Charge	Qgs		-	7.3	-	
Gate-Drain Charge	Qgd		-	10	-	
Switching Characteristics						
Turn-On Delay Time	Td(on)	VDD=-10V, VGS=-10V ,RG=3Ω, ID=-5A	-	8	-	nS
Rise Time	Tr		-	59	-	
Turn-Off Delay Time	Td(off)		-	111	-	
Fall Time	Tf		-	43	-	
Diode Characteristics						
Diode Forward Voltage	VSD	VGS=0V , IS=-1A	-	-	-1.2	V
Maximum Body-Diode Continuous Current	IS		-	-	-8	A
Reverse Recovery Time	Trr	IS=-5A, di/dt=100A/us, Tj=25°C	-	24	-	nS
Reverse Recovery Charge	Qrr		-	13	-	nC


Typical Characteristics




Output Characteristics




Transfer Characteristics




Capacitance Characteristics




Gate Charge




Current dissipation




Power dissipation




$R_{DS(on)}$ VS Drain Current




Forward characteristics of reverse diode




Normalized breakdown voltage



Normalized Threshold voltage




Maximum Transient Thermal Impedance



Safe Operation Area

SOP-8L Package Information



Symbol	Dimensions In Millimeters	
	Min.	Max.
A	1.35	1.75
A1	0.10	0.25
A2	1.35	1.55
b	0.33	0.51
c	0.17	0.25
D	4.80	5.00
e	1.27 REF.	
E	5.80	6.20
E1	3.80	4.00
L	0.40	1.27
θ	0°	8°