SP50P20TF

200V P-Channel Planar MOSFET

Product Summary

$V_{(BR)DSS}$	$R_{DS(on)TYP}$	I_D
-200V	70mΩ@10V	-27A

Feature

- Fast Switching
- Low Gate Charge and Rdson
- 100% Single Pulse avalanche energy Test

Applications

- DC-DC Converter
- Ideal for high-frequency switching and synchronous rectification

Package



TO-247(G:1 D:2 S:3)

Circuit diagram



Marking



50P20 :Device Code
**** :Week Code**

Order Information

Device	Package	Unit/Tube
SP50P20TF	TO-247	30

Absolute maximum ratings (Ta=25℃,unless otherwise noted)

Parameter	Symbol	Rating	Units
Drain-Source Voltage	V_{DS}	-200	V
Gate-Source Voltage	V_{GS}	±20	V
Continuous Drain Current(Tc=25℃)	I_D	-27	A
Continuous Drain Current(Tc=100℃)	I_D	-18	A
Pulsed Drain Current	I_{DM}	-108	A
Single Pulse Avalanche Energy[1]	E_{AS}	2494	mJ
Power Dissipation(Tc=25℃)	P_D	453	W
Thermal Resistance Junction-to-Case	$R_{\theta JC}$	0.27	℃/W
Storage Temperature Range	T_{STG}	-55 to 150	℃
Operating Junction Temperature Range	T_J	-55 to 150	℃

Electrical characteristics (Ta=25℃, unless otherwise noted)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Static Characteristics						
Drain-Source Breakdown Voltage	BV_{DSS}	VGS=0V , ID=-250uA	-200	-	-	V
Drain-Source Leakage Current	I_{DSS}	VDS=-160V , VGS=0V , TJ=25℃	-	-	-100	uA
Gate-Source Leakage Current	I_{GSS}	VGS=±20V , VDS=0V	-	-	±100	nA
Gate Threshold Voltage	$V_{GS(th)}$	VGS=VDS , ID =-250uA	-2	-3	-4	V
Drain-Source ON Resistance	$R_{DS(ON)}$	VGS=-10V , ID=-10A	-	70	88	mΩ
Dynamic characteristics						
Input Capacitance	C_{iss}	VDS=-25V , VGS=0V , f=1MHz	-	5421	-	pF
Output Capacitance	C_{oss}		-	1021	-	
Reverse Transfer Capacitance	C_{rss}		-	163	-	
Total Gate Charge	Q_g	VDS=-160V , VGS=-10V , ID=-10A	-	104	-	nC
Gate-Source Charge	Q_{gs}		-	24	-	
Gate-Drain Charge	Q_{gd}		-	43	-	
Switching Characteristics						
Turn-On Delay Time	$T_{d(on)}$	VDD=-100V , VGS=-10V , RG=9.1Ω, ID=-10A	-	31	-	nS
Rise Time	T_r		-	46	-	
Turn-Off Delay Time	$T_{d(off)}$		-	57	-	
Fall Time	T_f		-	27	-	
Drain-Source Body Diode Characteristics						
Source-Drain Diode Forward Voltage	V_{SD}	I_S=-1A,V_{GS}=0V	-	-	-1.2	V

Note :

1. The test condition is VDD=-50V,VGS=-10V,L=10mH,RG=25Ω

Typical Characteristics



Output Characteristics



Transfer Characteristics



Capacitance Characteristics



Gate Charge



Current dissipation



Power dissipation



RDS(on) VS Drain Current



Forward characteristics of reverse diode



Normalized breakdown voltage



Normalized Threshold voltage



Maximum Transient Thermal Impedance



Safe Operation Area

TO-247 Package Information



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	4.850	5.150	0.191	0.200
A1	2.200	2.600	0.087	0.102
b	1.000	1.400	0.039	0.055
b1	2.800	3.200	0.110	0.126
b2	1.800	2.200	0.071	0.087
c	0.500	0.700	0.020	0.028
c1	1.900	2.100	0.075	0.083
D	15.450	15.750	0.608	0.620
E1	3.500 REF.		0.138 REF.	
E2	3.600 REF.		0.142 REF.	
L	40.900	41.300	1.610	1.626
L1	24.800	25.100	0.976	0.988
L2	20.300	20.600	0.799	0.811
Φ	7.100	7.300	0.280	0.287
e	5.450 TYP.		0.215 TYP.	
H	5.980 REF.		0.235 REF.	
h	0.000	0.300	0.000	0.012