

Product Summary

$V_{(BR)DSS}$	$R_{DS(on)TYP}$	I_D
-16V	16mΩ@-4.5V	-8A
	21mΩ@-2.5V	



合肥矽普半导体

Siliup Semiconductor Technology Co., Ltd

技术 品质 服务

www.siliup.com


Feature

- High power and current handling capability
- Surface mount package

Application


- Battery Switch
- DC/DC Converter

Package




SOT-23-3L

Circuit diagram



Marking



Order Information

Device	Package	Unit/Tape
SP1613T1	SOT-23-3L	3000


Absolute maximum ratings (Ta=25°C, unless otherwise noted)

Parameter	Symbol	Value	Unit
Drain-Source Voltage	V_{DS}	-16	V
Gate-Source Voltage	V_{GS}	± 12	V
Continuous Drain Current	I_D	-8	A
Pulse Drain Current Tested	I_{DM}	-32	A
Power Dissipation	P_D	2	W
Thermal Resistance Junction-to-Ambient	$R_{\theta JA}$	62.5	°C/W
Storage Temperature Range	T_{STG}	-55 to 150	°C
Operating Junction Temperature Range	T_J	-55 to 150	°C


Electrical characteristics (Ta=25°C, unless otherwise noted)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Static Characteristics						
Drain-Source Breakdown Voltage	BV _{DSS}	VGS=0V , ID=-250μA	-16	-	-	V
Drain-Source Leakage Current	IDSS	VDS=-13V , VGS=0V	-	-	-1	uA
Gate-Source Leakage Current	IGSS	VGS=±12V , VDS=0V	-	-	±100	nA
Gate Threshold Voltage	VGS(th)	VDS=VGS , ID=-250μA	-0.4	-0.7	-1.0	V
Static Drain-Source On-Resistance	RDS(ON)	VGS= -4.5V, ID=-6A	-	16	20	mΩ
		VGS= -2.5V, ID=-5A	-	21	28	
Dynamic characteristics						
Input Capacitance	Ciss	VDS=-10V , VGS=0V , f=1MHz	-	2050	-	pF
Output Capacitance	Coss		-	411	-	
Reverse Transfer Capacitance	Crss		-	362	-	
Total Gate Charge	Qg	VDS=-16V , VGS=-10V , ID=-9.1A	-	30	-	nC
Gate-Source Charge	Qgs		-	5.3	-	
Gate-Drain Charge	Qgd		-	7.6	-	
Switching Characteristics						
Turn-On Delay Time	td(on)	VDD=-16V VGS=-10V , RG=2.5Ω, ID=-6A	-	14	-	nS
Turn-On Rise Time	tr		-	20	-	
Turn-Off Delay Time	td(off)		-	95	-	
Turn-Off Fall Time	tf		-	65	-	
Source-Drain Diode characteristics						
Diode Forward Voltage	VSD	VGS=0V , IS=-1A , TJ=25℃	-	-	-1.2	V


Typical Characteristics




Output Characteristics




Transfer Characteristics




Capacitance Characteristics




Gate Charge




Current dissipation




Power dissipation




RDS(on) VS Drain Current




Forward characteristics of reverse diode




Normalized breakdown voltage




Normalized Threshold voltage



Maximum Transient Thermal Impedance



Safe Operation Area

SOT-23-3L Package Information


Symbol	Dimensions in millimeters	
	Min.	Max.
A	1.050	1.250
A1	0.000	0.100
A2	1.050	1.150
b	0.300	0.500
c	0.100	0.200
D	2.820	3.020
E	1.500	1.700
E1	2.650	2.950
e	0.950 Typ.	
e1	1.800	2.000
L	0.300	0.600
θ	0°	8°