

Product Summary

$V_{(BR)DSS}$	$R_{DS(on)TYP}$	I_D
30V	28mΩ@10V	7A
	42mΩ@4.5V	
-30V	30mΩ@-10V	-8A
	45mΩ@-4.5V	



合肥矽普半导体

Siliup Semiconductor Technology Co., Ltd

技术 品质 服务

www.siliup.com


Feature

- Fast switching speed
- Surface mount package
- ROHS Compliant & Halogen-Free
- 100% Single Pulse avalanche energy Test

Applications


- DC-DC Converters.
- Motor Control.

Package




PDFN3X3-8L

Circuit diagram



Marking



3033C
*

:Device Code
:Month Code

Order Information

Device	Package	Unit/Tape
SP3033CNJ	PDFN3X3-8L	5000

Absolute maximum ratings (Ta=25°C, unless otherwise noted)

Parameter	Symbol	Rating		Unit
		N-Channel	P-Channel	
Drain-Source Voltage	V_{DS}	30	-30	V
Gate-Source Voltage	V_{GS}	± 20	± 20	V
Continuous Drain Current (Tc=25°C)	I_D	7	-8	A
Pulse Drain Current Tested	I_{DM}	28	-32	A
Single pulsed avalanche energy ¹	E_{AS}	9	36	mJ
Power Dissipation (Tc=25°C)	P_D	10		W
Thermal Resistance Junction-to-Case	$R_{\theta JC}$	12.5		°C/W
Storage Temperature Range	T_{STG}	-55 to 150		°C
Operating Junction Temperature Range	T_J	-55 to 150		°C

N-Electrical characteristics (Ta=25°C, unless otherwise noted)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Static Characteristics						
Drain-Source Breakdown Voltage	BV _{DSS}	VGS=0V , ID=250uA	30	-	-	V
Drain-Source Leakage Current	IDSS	VDS=24V , VGS=0V , TJ=25℃	-	-	1	uA
Gate-Source Leakage Current	IGSS	VGS=±20V , VDS=0V	-	-	±100	nA
Gate Threshold Voltage	VGS(th)	VGS=VDS , ID =250uA	1.0	1.5	2.2	V
Static Drain-Source On-Resistance	RDS(ON)	VGS = 10V, ID = 3.6A	-	28	38	mΩ
		VGS = 4.5V, ID = 3A	-	42	55	
Dynamic characteristics						
Input Capacitance	Ciss	VDS=15V , VGS=0V , f=1MHz	-	235	-	pF
Output Capacitance	Coss		-	45	-	
Reverse Transfer Capacitance	Crss		-	17	-	
Total Gate Charge	Qg	VDS=15V , VGS=10V , ID=4A	-	1	-	nC
Gate-Source Charge	Qgs		-	1.2	-	
Gate-Drain Charge	Qgd		-	1.3	-	
Switching Characteristics						
Turn-On Delay Time	Td(on)	VDD=15V VGS=10V , RG=1Ω, ID=4A	-	4	-	nS
Rise Time	Tr		-	25	-	
Turn-Off Delay Time	Td(off)		-	7	-	
Fall Time	Tf		-	19	-	
Diode Characteristics						
Diode Forward Voltage	VSD	VGS=0V , IS=1A , TJ=25℃	-	-	1.2	V
Maximum Body-Diode Continuous Current	IS	IS=4A, di/dt=100A/us, Tj=25℃	-	-	7	A
Reverse recover time	Trr		-	16	-	nS
Reverse recovery charge	Qrr		-	1.9	-	nC

Note:

- The EAS Test condition is $V_{DD}=15V, V_{GS}=10V, L=0.5mH, R_G=25\Omega$


P-Electrical characteristics (Ta=25°C, unless otherwise noted)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Static Characteristics						
Drain-Source Breakdown Voltage	BV _{DSS}	VGS=0V , ID=-250uA	-30	-	-	V
Drain-Source Leakage Current	Idss	VDS=-24V , VGS=0V , TJ=25℃	-	-	-1	uA
Gate-Source Leakage Current	Igss	VGS=±20V , VDS=0V	-	-	±100	nA
Gate Threshold Voltage	VGS(th)	VGS=VDS , ID =-250uA	-1.0	-1.5	-2.5	V
Static Drain-Source On-Resistance	RDS(ON)	VGS =-10V, ID =-7A	-	30	40	mΩ
		VGS =-4.5V, ID =-4A	-	45	65	
Dynamic characteristics						
Input Capacitance	Ciss	VDS=-15V , VGS=0V , f=1MHz	-	850	-	pF
Output Capacitance	Coss		-	116	-	
Reverse Transfer Capacitance	Crss		-	112	-	
Total Gate Charge	Qg	VDS=-15V , VGS=-10V , ID=-6.5A	-	13	-	nC
Gate-Source Charge	Qgs		-	2.6	-	
Gate-Drain Charge	Qgd		-	2.2	-	
Switching Characteristics						
Turn-On Delay Time	Td(on)	VDD=-15V VGS=-10V , RG=3Ω, ID=-4A	-	7.5	-	nS
Rise Time	Tr		-	5.5	-	
Turn-Off Delay Time	Td(off)		-	19	-	
Fall Time	Tf		-	7	-	
Diode Characteristics						
Diode Forward Voltage	VSD	VGS=0V , IS=-1A , TJ=25℃	-	-	-1.2	V
Maximum Body-Diode Continuous Current	IS		-	-	-8	A
Reverse recover time	Trr	IS=-20A, di/dt=-100A/us, Tj=25℃	-	0.9	-	nS
Reverse recovery charge	Qrr		-	7	-	nC


Note:

2. The EAS Test condition is $V_{DD}=-15V$, $V_{GS}=-10V$, $L=0.5mH$, $R_G=25\Omega$


N-Channel Typical Characteristics




Output Characteristics




Transfer Characteristics




Capacitance Characteristics




Gate Charge




Current dissipation




Power dissipation




RDS(on) VS Drain Current




Forward characteristics of reverse diode




Normalized breakdown voltage



Normalized Threshold voltage




Maximum Transient Thermal Impedance




Safe Operation Area


P-Channel Typical Characteristics




Output Characteristics




Transfer Characteristics




Capacitance Characteristics




Gate Charge




Current dissipation




Power dissipation




$R_{DS(on)}$ VS Drain Current




Forward characteristics of reverse diode




Normalized breakdown voltage



Normalized Threshold voltage






Maximum Transient Thermal Impedance



Safe Operation Area



PDFN3X3-8L Package Information

Top View
[顶视图]Bottom View
[背视图]Side View
[侧视图]

Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	0.650	0.850	0.026	0.033
A1	0.152 REF.		0.006 REF.	
A2	0~0.05		0~0.002	
D	2.900	3.100	0.114	0.122
D1	0.935	1.135	0.037	0.045
D2	0.280	0.480	0.011	0.019
E	2.900	3.100	0.114	0.122
E1	3.150	3.450	0.124	0.136
E2	1.535	1.935	0.060	0.076
b	0.200	0.400	0.008	0.016
e	0.550	0.750	0.022	0.030
L	0.300	0.500	0.012	0.020
L1	0.180	0.480	0.007	0.019
L2	0~0.100		0~0.004	
L3	0~0.100		0~0.004	
H	0.315	0.515	0.012	0.020
θ	9°	13°	9°	13°