

## Product Summary

$V_{(BR)DSS}$	$R_{DS(on)TYP}$	$I_D$
85V	4.3mΩ@10V	90A



合肥矽普半导体

Siliup Semiconductor Technology Co.Ltd

技术 品质 服务

www.siliup.com


## Feature

- Fast Switching
- Low Gate Charge and R<sub>DS(on)</sub>
- Advanced Split Gate Trench Technology
- 100% Single Pulse avalanche energy Test

## Applications


- Power switching application
- DC-DC Converter
- Power Management

## Package




PDFN5X6-8L

## Circuit diagram



## Marking



85N05AGH :Device Code  
\* :Month Code

## Order Information

Device	Package	Unit/Tape
SP85N05AGHNK	PDFN5X6-8L	5000

**Absolute maximum ratings (Ta=25°C unless otherwise noted)**

Parameter	Symbol	Rating	Unit
Drain-Source Voltage	V <sub>DS</sub>	85	V
Gate-Source Voltage	V <sub>GS</sub>	±20	V
Continuous Drain Current (Tc=25°C)	I <sub>D</sub>	90	A
Continuous Drain Current (Tc=100°C)	I <sub>D</sub>	60	A
Pulsed Drain Current	I <sub>DM</sub>	360	A
Single Pulse Avalanche Energy <sup>1</sup>	E <sub>AS</sub>	784	mJ
Power Dissipation (Tc=25°C)	P <sub>D</sub>	125	W
Thermal Resistance Junction-to-Case	R <sub>θJC</sub>	1	°C/W
Storage Temperature Range	T <sub>STG</sub>	-55 to 150	°C
Operating Junction Temperature Range	T <sub>J</sub>	-55 to 150	°C


**Electrical characteristics (Ta=25°C, unless otherwise noted)**

Characteristics	Symbol	Test Condition	Min	Typ	Max	Unit
<b>Static Characteristics</b>						
Drain-Source Breakdown Voltage	BV <sub>DSS</sub>	I <sub>D</sub> = 250μA, V <sub>GS</sub> = 0V	85	90	-	V
Drain Cut-Off Current	I <sub>DSS</sub>	V <sub>DS</sub> = 68V, V <sub>GS</sub> = 0V	-	-	1	μA
Gate Leakage Current	I <sub>GSS</sub>	V <sub>GS</sub> = ±20V, V <sub>DS</sub> = 0V	-	-	±0.1	
Gate Threshold Voltage	V <sub>GS(th)</sub>	V <sub>DS</sub> = V <sub>GS</sub> , I <sub>D</sub> = 250μA	2	3	4	V
Drain-Source ON Resistance	R <sub>DS(ON)</sub>	V <sub>GS</sub> = 10V, I <sub>D</sub> = 20A	-	4.3	5.5	mΩ
<b>Dynamic Characteristics</b>						
Input Capacitance	C <sub>iss</sub>	V <sub>DS</sub> = 40V, V <sub>GS</sub> = 0V, f = 1.0MHz	-	3543	-	pF
Output Capacitance	C <sub>oss</sub>		-	1058	-	
Reverse Transfer Capacitance	C <sub>riss</sub>		-	23	-	
Total Gate Charge	Q <sub>g</sub>	V <sub>DS</sub> =40V, V <sub>GS</sub> =10V, I <sub>D</sub> =165A	-	49	-	nC
Gate-Source Charge	Q <sub>gs</sub>		-	16	-	
Gate-Drain Charge	Q <sub>gd</sub>		-	13	-	
<b>Switching Characteristics</b>						
Turn-On Delay Time	t <sub>d(on)</sub>	V <sub>GS</sub> = 10V, V <sub>DS</sub> = 40V, I <sub>D</sub> =165A, RG = 1.6Ω	-	17	-	nS
Rise Time	t <sub>r</sub>		-	25	-	
Turn-Off Delay Time	t <sub>d(off)</sub>		-	36	-	
Fall Time	t <sub>f</sub>		-	15	-	
<b>Drain-Source Body Diode Characteristics</b>						
Source-Drain Diode Forward Voltage	V <sub>SD</sub>	I <sub>S</sub> = 1A, V <sub>GS</sub> = 0V	-	-	1.2	V
Maximum Body-Diode Continuous Current	I <sub>S</sub>		-	-	90	A
Reverse Recovery Time	T <sub>rr</sub>	I <sub>S</sub> =20A, di/dt=100A/us, T <sub>J</sub> =25°C	-	62	-	nS
Reverse Recovery Charge	Q <sub>rr</sub>		-	103	-	nC


**Note :**

- The test condition is V<sub>DD</sub>=45V, V<sub>GS</sub>=10V, L=0.5mH, R<sub>G</sub>=25Ω


**Typical Characteristics**




**Output Characteristics**




**Transfer Characteristics**




**Capacitance Characteristics**




**Gate Charge**




**Current dissipation**




**Power dissipation**




RDS(on) VS Drain Current




Forward characteristics of reverse diode




Normalized breakdown voltage



Normalized Threshold voltage




Maximum Transient Thermal Impedance




Safe Operation Area


**PDFN5X6-8L Package Information**



Top View  
[顶视图]



Bottom View  
[背视图]



Side View  
[侧视图]

Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	0.900	1.000	0.035	0.039
A3	0.254REF.		0.010REF.	
D	4.944	5.096	0.195	0.201
E	5.974	6.126	0.235	0.241
D1	3.910	4.110	0.154	0.162
E1	3.375	3.575	0.133	0.141
D2	4.824	4.976	0.190	0.196
E2	5.674	5.826	0.223	0.229
k	1.190	1.390	0.047	0.055
b	0.350	0.450	0.014	0.018
e	1.270TYP.		0.050TYP.	
L	0.559	0.711	0.022	0.028
L1	0.424	0.576	0.017	0.023
H	0.574	0.726	0.023	0.029
θ	10°	12°	10°	12°