

Z-PACK 2mm HM

TE Internal #: 120954-1
PCB Mount Header, Right Angle, Board-to-Board, 4 Position, 3 mm
[.118 in] Centerline, Fully Shrouded, Gold, Through Hole - Press-Fit,
Z-PACK 2mm HM

[View on TE.com >](#)



Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Header**
PCB Mount Orientation: **Right Angle**
Connector System: **Board-to-Board**
Number of Positions: **4**
Number of Rows: **1**

Features

Electrical Characteristics

Operating Voltage	250 VDC
-------------------	---------

Dimensions

Connector Width	15 mm[.59 in]
PCB Thickness (Recommended)	1.4 mm[.055 in]
Connector Height	9.7 mm[.381 in]
Connector Length	22.34 mm[.88 in]

Packaging Features

Packaging Quantity	38
Packaging Method	Tube

Industry Standards

Compatible With Approved Standards Products	UL E28476
Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-0

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]

Mechanical Attachment

PCB Mount Alignment Type	Pegs
--------------------------	------



PCB Mount Retention	Without
PCB Mount Alignment	With
Connector Mounting Type	Board Mount
Mating Alignment	Without

Termination Features

Termination Post & Tail Length	3.22 mm[.126 in]
Termination Method to PCB	Through Hole - Press-Fit

Contact Features

Contact Underplating Material	Nickel
Contact Underplating Material Thickness	1.27 µm[50 µin]
Contact Mating Area Plating Material Thickness	.76 µm[30 µin]
PCB Contact Termination Area Plating Material Thickness	.5 – 1.25 µm[19.68 – 49.21 µin]
Contact Layout	Inline
Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material	Gold
Contact Type	Blade
Contact Current Rating (Max)	16 A

Housing Features

Housing Material	Polyester
Centerline (Pitch)	3 mm[.118 in]

Configuration Features

Number of Loaded Positions	4
Number of Power Positions	4
PCB Mount Orientation	Right Angle
Number of Positions	4
Number of Rows	1

Product Type Features

Connector Shape	Rectangular
PCB Connector Assembly Type	PCB Mount Header
Connector System	Board-to-Board
Header Type	Fully Shrouded



Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Body Features

Primary Product Color	Gray
-----------------------	------

Operation/Application

Circuit Application	Power
---------------------	-------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # 120953-1
TE UPM Ver Receptacle 4P HC Power



TE Part # 120953-6
UPM EXPANDED RCPT ASSEMBLY




TE Part # 120943-2
UPM R/A REC HC 4P Power Connector




TE Part # 224441-1
SEATING TOOL

Also in the Series


Z-PACK 2mm HM




Board-to-Board Headers & Receptacles(46)




Connector Contacts(2)




Connector Hardware(91)



Hard Metric Backplane Connectors (267)




High Speed Backplane Connectors(1)




Power Contacts(2)


Customers Also Bought




TE Part #100668-1
Z-PACK M.ASSY.154P.




TE Part #1469028-1
HM-ZD 2PR RECP 40P




TE Part #5188578-1
Z-PACK/A M HDR.154P




TE Part #646478-5
2MM H.M., "A" SHROUD, 4.5MM




TE Part #2-2330550-2
SOCKET P4 BOLSTER PLATE ASSY, W/ COVER



TE Part #2-2330552-2
ICX POINT PHM CARRIER ASSY, P4




TE Part #2007637-5
SFP+ assy 2x2 Spring Fingers 4 LP Sn



TE Part #1-2351052-5
LGA4677 E1A CARRIER ASSY



TE Part #2176550-1
[RLW73P A3 1% R010 600ppm 4k RL](#)



TE Part #3-2176467-1
[TLRP 1206 1.0W R025 1% 100PPM 5K RL](#)

Documents

Product Drawings

[TE UPM R/A Header 4P HC Power, LLLL](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_120954-1_B.2d_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_120954-1_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_120954-1_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[POWER_CONNECTORS_CATALOG_SEC01_BOARD_TO_BOARD](#)

English

[Solutions for AdvancedTCA, AdvancedTCA 300, MicroTCA, and AdvancedMC Standards Datasheet 3-1773445-8](#)

English

[2_PIECE_POWER_CONNECTORS_qrg_4-1773458-1](#)

English

Product Specifications

English