

Product Summary

$V_{(BR)DSS}$	$R_{DS(on)TYP}$	I_D
40V	16mΩ@10V	8A
	19mΩ@4.5V	



合肥矽普半导体

Siliup Semiconductor Technology Co., Ltd

技术 品质 服务

www.siliup.com


Feature

- High power and current handling capability
- Surface mount package

Application


- Battery Switch
- DC/DC Converter

Package




SOT-23-6L

Circuit diagram



Marking



Order Information

Device	Package	Unit/Tape
SP40N16TS	SOT-23-6L	3000


Absolute maximum ratings (Ta=25°C, unless otherwise noted)

Parameter	Symbol	Value	Unit
Drain-Source Voltage	V_{DS}	40	V
Gate-Source Voltage	V_{GS}	± 20	V
Continuous Drain Current	I_D	8	A
Pulse Drain Current Tested	I_{DM}	32	A
Power Dissipation	P_D	1.1	W
Thermal Resistance Junction-to-Ambient	$R_{\theta JA}$	113	°C/W
Storage Temperature Range	T_{STG}	-55 to 150	°C
Operating Junction Temperature Range	T_J	-55 to 150	°C


Electrical characteristics (Ta=25°C, unless otherwise noted)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Static Characteristics						
Drain-Source Breakdown Voltage	BV _{DSS}	VGS=0V , ID=250μA	40	-	-	V
Drain-Source Leakage Current	I _{DSS}	VDS=32V , VGS=0V	-	-	1	uA
Gate-Source Leakage Current	I _{GSS}	VGS=±20V , VDS=0V	-	-	±100	nA
Gate Threshold Voltage	VGS(th)	VDS=VGS , ID=250μA	1	1.6	2.5	V
Static Drain-Source On-Resistance	R _{DS(ON)}	VGS=10V , ID =7A	-	16	22	mΩ
		VGS=4.5V , ID =6A	-	19	26	
Dynamic characteristics						
Input Capacitance	C _{iss}	VDS=15V , VGS=0V , f=1MHz	-	1061	-	pF
Output Capacitance	C _{oss}		-	110	-	
Reverse Transfer Capacitance	C _{rss}		-	95	-	
Total Gate Charge	Q _g	VDS=15V , VGS=10V , ID=10A	-	23	-	nC
Gate-Source Charge	Q _{gs}		-	6.3	-	
Gate-Drain Charge	Q _{gd}		-	5.3	-	
Switching Characteristics						
Turn-On Delay Time	t _{d(on)}	VDD=15V VGS=10V , RG=1.5Ω , ID=8A	-	5.5	-	nS
Turn-On Rise Time	t _r		-	14	-	
Turn-Off Delay Time	t _{d(off)}		-	25	-	
Turn-Off Fall Time	t _f		-	4.6	-	
Source-Drain Diode characteristics						
Diode Forward Voltage	V _{SD}	VGS=0V , IS=1A , TJ=25℃	-	-	1.2	V


Typical Characteristics




Output Characteristics




Transfer Characteristics




Capacitance Characteristics




Gate Charge




Current dissipation




Power dissipation




$R_{DS(on)}$ VS Drain Current




Forward characteristics of reverse diode




Normalized breakdown voltage




Normalized Threshold voltage



Maximum Transient Thermal Impedance



Safe Operation Area

SOT-23-6L Package Information


Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	1.050	1.250	0.041	0.049
A1	0.000	0.100	0.000	0.004
A2	1.050	1.150	0.041	0.045
b	0.300	0.500	0.012	0.020
c	0.100	0.200	0.004	0.008
D	2.820	3.020	0.111	0.119
E	1.500	1.700	0.059	0.067
E1	2.650	2.950	0.104	0.116
e	0.950(BSC)		0.037(BSC)	
e1	1.800	2.000	0.071	0.079
L	0.300	0.600	0.012	0.024
θ	0°	8°	0°	8°