

Product Summary

$V_{(BR)DSS}$	$R_{DS(on)TYP}$	I_D
20V	75mΩ@4.5V	1.2A
	90mΩ@2.5V	



合肥矽普半导体

Siliup Semiconductor Technology Co., Ltd

技术 品质 服务

www.siliup.com


Feature

- High power and current handling capability
- Surface mount package

Application


- Battery Switch
- DC/DC Converter

Package




SOT-523

Circuit diagram



Marking



Order Information

Device	Package	Unit/Tape
SP2620F	SOT-523	3000


Absolute maximum ratings (Ta=25°C, unless otherwise noted)

Parameter	Symbol	Value	Unit
Drain-Source Voltage	V_{DS}	20	V
Gate-Source Voltage	V_{GS}	± 12	V
Continuous Drain Current	I_D	1.2	A
Pulse Drain Current Tested	I_{DM}	4.8	A
Power Dissipation	P_D	150	mW
Thermal Resistance Junction-to-Ambient	$R_{\theta JA}$	833	°C/W
Storage Temperature Range	T_{STG}	-55 to 150	°C
Operating Junction Temperature Range	T_J	-55 to 150	°C


Electrical characteristics (Ta=25°C, unless otherwise noted)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Static Characteristics						
Drain-Source Breakdown Voltage	BV _{DSS}	VGS=0V , ID=250μA	20	-	-	V
Drain-Source Leakage Current	I _{DSS}	VDS=16V , VGS=0V	-	-	1	uA
Gate-Source Leakage Current	I _{GSS}	VGS=±20V , VDS=0V	-	-	±100	nA
Gate Threshold Voltage	VGS(th)	VDS=VGS , ID=250μA	0.4	0.65	1	V
Static Drain-Source On-Resistance	R _{DS(ON)}	VGS=4.5V, ID =1A	-	75	90	mΩ
		VGS=2.5V, ID =0.5A	-	90	110	
Dynamic characteristics						
Input Capacitance	C _{iss}	VDS=10V , VGS=0V , f=1MHz	-	226	-	pF
Output Capacitance	C _{oss}		-	35	-	
Reverse Transfer Capacitance	C _{rss}		-	21	-	
Total Gate Charge	Q _g	VDS=10V , VGS=4.5V , ID=1.2A	-	4.0	-	nC
Gate-Source Charge	Q _{gs}		-	0.85	-	
Gate-Drain Charge	Q _{gd}		-	0.67	-	
Switching Characteristics						
Turn-On Delay Time	t _{d(on)}	VDD=10V VGS=4.5V , RG=6Ω , ID=1.2A	-	7	-	nS
Turn-On Rise Time	t _r		-	55	-	
Turn-Off Delay Time	t _{d(off)}		-	14	-	
Turn-Off Fall Time	t _f		-	43	-	
Source-Drain Diode characteristics						
Diode Forward Voltage	V _{SD}	VGS=0V , IS=1A , TJ=25℃	-	-	1.2	V


Typical Characteristics




Output Characteristics




Transfer Characteristics




Capacitance Characteristics




Gate Charge




Current dissipation




Power dissipation




RDS(on) VS Drain Current




Forward characteristics of reverse diode




Normalized breakdown voltage



Normalized Threshold voltage




Maximum Transient Thermal Impedance



Safe Operation Area

SOT-523 Package Information



Symbol	Dimensions In Millimeters	
	Min	Max
A	0.700	0.900
A1	0.000	0.100
A2	0.700	0.800
b1	0.150	0.250
b2	0.250	0.350
C	0.100	0.200
D	1.500	1.700
E	0.700	0.900
E1	1.450	1.750
e	0.500 TYP	
e1	0.900	1.100
L	0.400 REF	
L1	0.260	0.460
θ	0°	8°