



$2.00 \pm 0.15 (\text{PITCH})$ 


Technical Index:

1. Temperature range: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
2. Rated voltage: 200V DC/AC(rms).
3. Rated current: 2.0A.
4. Contact resistance: $\leq 25\text{m}\Omega$.
5. Withstanding voltage: 500V AC/minute.
6. Insulation resistance: $\geq 1000\text{M}\Omega$.

 4.75 ± 0.25 3.02 ± 0.20 6.00 ± 0.25 3.40 ± 0.20 (4.75)
 (3.90) $\text{DIMA} \pm 0.10$ 2.00 $\phi 0.80$

适用线路板(PCB LAYOUT)

序号	品名	材质
1	PH2.0 直针 胶芯	PA66 UL94V-2 Beige
2	PH2.0 弯针 端子	Copper Alloy/ Tin Plating



SECTION A-A

Part No	Pin	A	B
WAfer-PH2.0-2PWZ-Y62	2	2.00	6.00
WAfer-PH2.0-3PWZ-Y62	3	4.00	8.00
WAfer-PH2.0-4PWZ-Y62	4	6.00	10.00
WAfer-PH2.0-5PWZ-Y62	5	8.00	12.00
WAfer-PH2.0-6PWZ-Y62	6	10.00	14.00
WAfer-PH2.0-7PWZ-Y62	7	12.00	16.00
WAfer-PH2.0-8PWZ-Y62	8	14.00	18.00
WAfer-PH2.0-9PWZ-Y62	9	16.00	20.00
WAfer-PH2.0-10PWZ-Y62	10	18.00	22.00
WAfer-PH2.0-11PWZ-Y62	11	20.00	24.00
WAfer-PH2.0-12PWZ-Y62	12	22.00	26.00
WAfer-PH2.0-13PWZ-Y62	13	24.00	28.00
WAfer-PH2.0-14PWZ-Y62	14	26.00	30.00
WAfer-PH2.0-15PWZ-Y62	15	28.00	32.00
WAfer-PH2.0-16PWZ-Y62	16	30.00	34.00
WAfer-PH2.0-17PWZ-Y62	17	32.00	36.00
WAfer-PH2.0-18PWZ-Y62	18	34.00	38.00
WAfer-PH2.0-19PWZ-Y62	19	36.00	40.00
WAfer-PH2.0-20PWZ-Y62	20	38.00	42.00

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: PH2.0 弯针	
DECIMALS:	ANGLES:	PAR	WAfer-PH2.0-NPWZ-Y62
X.: ± 0.50	X':: $\pm 5^{\circ}$	DWN	
.X: ± 0.20	X.X':: $\pm 3^{\circ}$	CHKD	
.XX: ± 0.10	X.XX':: $\pm 1^{\circ}$	APVD	
CUSTOMER COPY		SCALE:1:1	UNIT:MM
		SIZE:A4	SHEET:1F1
			REV:A