






Color: ■ gray

Similar to illustration



Dimensions in mm
 $L = (\text{pole no.} - 1) \times \text{pin spacing} + 6.5 \text{ mm}$



PCB terminal block, 2624 Series, operating tool

This PCB terminal block (item number 2624-1109) is designed for quick and easy connections. It offers the flexibility needed for different mounting types. Our PCB terminal block is rated for 400 V and is designed to handle a rated current of up to 41 A. It can therefore be used in high-load applications. Ensure that the strip lengths are between 10 mm and 12 mm when connecting conductors to this PCB terminal block. This product features one conductor terminal and utilizes Push-in CAGE CLAMP®. Push-in CAGE CLAMP® technology provides a universal connection solution for any type of conductor. It allows both solid and fine-stranded conductors with ferrules to be inserted directly into the clamping point without the need for tools. The item's dimensions are 46.5 x 19.4 x 16.3 mm (width x height x depth). This PCB terminal block is suitable for conductor cross sections ranging from 0.2 mm² to 6 mm². Up to nine potentials / nine poles can be connected to this terminal strip using nine clamping points on one level. The contacts are made of electrolytic copper (ECu), the gray housing is made of polyamide (PA66) for insulation, and the clamping spring is made of chrome-nickel spring steel (CrNi). The contact surface is coated with tin. An operating tool is used to operate this PCB terminal block. The PCB terminal block is designed for THT soldering. These PCB terminal blocks are mounted using feed-through mounts.. The conductor is designed to be inserted at a 0° angle.. The solder pins are organized over the entire terminal strip (in-line). They are 0.8 x 1 mm cross-section and 4 mm in length. Each potential has two solder pins.

| Notes | |
|-----------|--|
| Variants: | Other versions (or variants) can be requested from WAGO Sales or configured at https://configurator.wago.com/ . Other pole numbers Direct marking Other colors |



Electrical data

| Ratings per IEC/EN 60664-1 | | | | Approvals per UL 1059 | | | |
|----------------------------|-------|-------|-------|-----------------------|-------|---|-------|
| Overvoltage category | III | III | II | Use group | B | C | D |
| Pollution degree | 3 | 2 | 2 | Rated voltage | 300 V | - | 300 V |
| Nominal voltage | 320 V | 400 V | 630 V | Rated current | 26 A | - | 10 A |
| Rated surge voltage | 4 kV | 4 kV | 4 kV | | | | |
| Rated current | 41 A | 41 A | 41 A | | | | |

| Approvals per CSA | | | |
|-------------------|-------|---|-------|
| Use group | B | C | D |
| Rated voltage | 300 V | - | 300 V |
| Rated current | 26 A | - | 5 A |

Connection data

| | | | |
|----------------------------|---|---|-------------------------------------|
| Clamping units | 9 | Connection 1 | |
| Total number of potentials | 9 | Connection technology | Push-in CAGE CLAMP® |
| Number of connection types | 1 | Actuation type | Operating tool |
| Number of levels | 1 | Solid conductor | 0.2 ... 6 mm² / 24 ... 10 AWG |
| | | Fine-stranded conductor | 0.2 ... 6 mm² / 24 ... 10 AWG |
| | | Fine-stranded conductor; with insulated ferrule | 0.25 ... 2.5 mm² |
| | | Fine-stranded conductor; with uninsulated ferrule | 0.25 ... 2.5 mm² |
| | | Fine-stranded conductor; with twin ferrule | 0.25 ... 1.5 mm² |
| | | Strip length | 10 ... 12 mm / 0.39 ... 0.47 inches |
| | | Conductor connection direction to PCB | 0° |
| | | Pole number | 9 |

Physical data

| | |
|--------------------------------------|------------------------|
| Pin spacing | 5 mm / 0.197 inches |
| Width | 46.5 mm / 1.831 inches |
| Height | 19.4 mm / 0.764 inches |
| Height from the surface | 15.4 mm / 0.606 inches |
| Depth | 16.3 mm / 0.642 inches |
| Solder pin length | 4 mm |
| Solder pin dimensions | 0.8 x 1 mm |
| Drilled hole diameter with tolerance | 1.3 (+0.1) mm |

Mechanical data

| | |
|---------------|-----------------------|
| Mounting type | Feed-through mounting |
|---------------|-----------------------|



| PCB contact | | |
|-------------------------------------|--|--|
| PCB contact | | THT |
| Solder pin arrangement | | over the entire terminal strip (in-line) |
| Number of solder pins per potential | | 2 |

| Material data | | |
|------------------------------------|--|--|
| Note (material data) | | Information on material specifications can be found here |
| Color | | gray |
| Material group | | I |
| Insulation material (main housing) | | Polyamide (PA66) |
| Flammability class per UL94 | | V0 |
| Clamping spring material | | Chrome-nickel spring steel (CrNi) |
| Contact material | | Electrolytic copper (E _{Cu}) |
| Contact Plating | | Tin |
| Fire load | | 0 MJ |
| Weight | | 14 g |

| Environmental requirements | | |
|----------------------------------|--|-----------------|
| Limit temperature range | | -60 ... +105 °C |
| Processing temperature | | -35 ... +60 °C |
| Continuous operating temperature | | -60 ... +105 °C |

| Commercial data | | |
|-----------------------|--|---------------|
| eCl@ss 10.0 | | 27-44-04-01 |
| eCl@ss 9.0 | | 27-44-04-01 |
| ETIM 9.0 | | EC002643 |
| ETIM 8.0 | | EC002643 |
| PU (SPU) | | 50 pcs |
| Packaging type | | Box |
| Country of origin | | PL |
| GTIN | | 4055143578370 |
| Customs tariff number | | 85369010000 |

| Environmental Product Compliance | | |
|----------------------------------|--|-------------------------|
| RoHS Compliance Status | | Compliant, No Exemption |

Approvals / Certificates

General approvals



| Approval | Standard | Certificate Name |
|---|---------------|------------------|
| CB DEKRA Certification B.V. | IEC 60947-7-4 | NL-61583 |
| CSA DEKRA Certification B.V. | C22.2 No. 158 | 70117145 |
| cURus Underwriters Laboratories Inc. | UL 1059 | E45172 |
| KEMA/KEUR DEKRA Certification B.V. | EN 60947-7-4 | 71-100535 |

Declarations of conformity and manufacturer's declarations



| Approval | Standard | Certificate Name |
|-------------------------------|----------|------------------|
| Railway WAGO GmbH & Co. KG | - | Z00004415.000 |



Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 2624-1109

Download icon

Documentation

Additional Information

Technical Section

03.04.2019

pdf

2027.26 KB

Download icon

CAD/CAE-Data

CAD data

2D/3D Models 2624-1109

Download icon

CAE data

ZUKEN Portal 2624-1109

Download icon

PCB Design

Symbol and Footprint via SamacSys 2624-1109

Download icon

Symbol and Footprint via Ultra Librarian 2624-1109


Download icon

1 Compatible Products


1.1 Optional Accessories


1.1.1 Ferrule

1.1.1.1 Ferrule





Item No.: 216-241
Ferrule; Sleeve for 0.5 mm² / 20 AWG; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; white







Item No.: 216-242
Ferrule; Sleeve for 0.75 mm² / 18 AWG; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; gray







Item No.: 216-262
Ferrule; Sleeve for 0.75 mm² / 18 AWG; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; gray







Item No.: 216-243
Ferrule; Sleeve for 1 mm² / AWG 18; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; red







Item No.: 216-263
Ferrule; Sleeve for 1 mm² / AWG 18; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; red







Item No.: 216-244
Ferrule; Sleeve for 1.5 mm² / AWG 16; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; black







Item No.: 216-264
Ferrule; Sleeve for 1.5 mm² / AWG 16; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; black







Item No.: 216-246
Ferrule; Sleeve for 2.5 mm² / AWG 14; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; blue






Item No.: 216-266
Ferrule; Sleeve for 2.5 mm² / AWG 14; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; blue





Item No.: 216-106
Ferrule; Sleeve for 2.5 mm² / AWG 14; un-insulated; electro-tin plated; silver-colored



1.1.2 Tool

1.1.2.1 Operating tool



Item No.: 210-720

Operating tool; Blade: 3.5 x 0.5 mm; with a partially insulated shaft; multicoloured

Installation Notes

Conductor termination



Insert fine-stranded conductors and remove all conductor types via operating tool.

Conductor termination



Insert solid conductors via push-in termination.