


### 1、 Physical Dimensions(size of 0805)

Unit:mm

Part Number	A		B		C		D	Marking
	Min	Max	Min	Max	Min	Max	Min	
KPSMD150	2.0	2.3	1.2	1.5	0.75	1.25	0.20	7



### 2、 Electrical Characteristics

Part Number	I <sub>H</sub> (A)	I <sub>T</sub> (A)	V <sub>max</sub> (V)	I <sub>max</sub> (A)	T <sub>trip</sub> (Max time to trip)		Pd <sub>typ</sub> (W)	R <sub>min</sub> (Ω)	R1 <sub>max</sub> (Ω)
					Current(A)	Time(S)			
KPSMD150	1.50	3.00	6.0	100	8.0	0.50	0.60	0.040	0.160

I<sub>H</sub>: Holding Current: maximum current at which the device will not trip in 25°C still air.

I<sub>T</sub>: Tripping Current minimum current at which the device will trip in 25°C still air.

V<sub>max</sub>: Maximum voltage device can withstand without damage at rated current.

I<sub>max</sub>: Maximum fault current device can withstand without damage at rated voltage.

T<sub>trip</sub>: Maximum time to trip(s) at assigned current.

Pd<sub>typ</sub>: Rated working power.

R<sub>min</sub>: Minimum resistance of device prior to trip at 25°C.


R1<sub>max</sub>: Maximum resistance of device is measured one hours post reflow at 25°C.

Noted: All electrical function test is conducted after PCB mounted.


### 3、 Thermal Derating

KPSMD150	Maximum ambient operating temperature								
	-40°C	-20°C	0°C	25°C	40°C	50°C	60°C	70°C	85°C
Hold Current(A)	1.98	1.84	1.64	1.50	1.25	1.15	1.02	0.89	0.71
Trip Current(A)	3.96	3.68	3.28	3.00	2.50	2.30	2.02	1.78	1.42

### 4、 Solder Reflow Recommendations



Recommended Pad Layout(mm)



Notes : If reflow temperatures exceed the recommended profile, devices may not meet the performance requirements.

### 5、 Package Information

Packing quantity:3500PCS/Reel

Note:Reel packaging per EIA-481-1 standard