



12A, 650V N-CHANNEL MOSFET


GENERAL DESCRIPTION

SVF12N65F/K/S is an N-channel enhancement mode power MOS field effect transistor which is produced using Silan proprietary F-Cell™ structure VDMOS technology. The improved process and cell structure have been especially tailored to minimize on-state resistance, provide superior switching performance, and withstand high energy pulse in the avalanche and commutation mode.

These devices are widely used in AC-DC power supplies, DC-DC converters and H-bridge PWM motor drivers.

FEATURES

- 12A,650V, $R_{DS(on)(typ.)}=0.64\Omega @ V_{GS}=10V$
- Low gate charge
- Low Crss
- Fast switching
- Improved dv/dt capability



ORDERING INFORMATION

Part No.	Package	Marking	Hazardous Substance Control	Packing Type
SVF12N65F	TO-220F-3L	SVF12N65F	Pb free	Tube
SVF12N65K	TO-262-3L	SVF12N65K	Pb free	Tube
SVF12N65S	TO-263-2L	SVF12N65S	Halogen free	Tube
SVF12N65STR	TO-263-2L	SVF12N65S	Halogen free	Tape &Reel



ABSOLUTE MAXIMUM RATINGS (T_A=25°C UNLESS OTHERWISE NOTED)

Characteristics	Symbol	Ratings			Unit
		SVF12N65F	SVF12N65K	SVF12N65S	
Drain-Source Voltage	V _{DS}	650			V
Gate-Source Voltage	V _{GS}	±30			V
Drain Current	I _D	12			A
		7.6			
Drain Current Pulsed	I _{DM}	48			A
Power Dissipation(T _C =25°C) -Derate above 25°C	P _D	51	209	210	W
		0.41	1.67	1.68	W/°C
Single Pulsed Avalanche Energy (Note 1)	E _{AS}	790			mJ
Reverse Diode dv/dt (Note 2)	dv/dt	4.5			V/ns
MOSFET dv/dt Ruggedness (Note 3)	dv/dt	50			V/ns
Operation Junction Temperature Range	T _J	-55~+150			°C
Storage Temperature Range	T _{stg}	-55~+150			°C

THERMAL CHARACTERISTICS

Characteristics	Symbol	Ratings			Unit
		SVF12N65F	SVF12N65K	SVF12N65S	
Thermal Resistance, Junction-to-Case	R _{θJC}	2.44	0.6	0.60	°C/W
Thermal Resistance, Junction-to-Ambient	R _{θJA}	62.5	62.5	62.5	°C/W



ELECTRICAL CHARACTERISTICS ($T_c=25^\circ\text{C}$ UNLESS OTHERWISE NOTED)

Characteristics	Symbol	Test conditions	Min.	Typ.	Max.	Unit
Drain -Source Breakdown Voltage	BV_{DSS}	$V_{\text{GS}}=0\text{V}, I_{\text{D}}=250\mu\text{A}$	650	--	--	V
Drain-Source Leakage Current	I_{DSS}	$V_{\text{DS}}=650\text{V}, V_{\text{GS}}=0\text{V}$	--	--	1.0	μA
Gate-Source Leakage Current	I_{GSS}	$V_{\text{GS}}=\pm30\text{V}, V_{\text{DS}}=0\text{V}$	--	--	±100	nA
Gate Threshold Voltage	$V_{\text{GS}(\text{th})}$	$V_{\text{GS}}=V_{\text{DS}}, I_{\text{D}}=250\mu\text{A}$	2.0	--	4.0	V
Static Drain- Source On State Resistance	$R_{\text{DS}(\text{on})}$	$V_{\text{GS}}=10\text{V}, I_{\text{D}}=6.0\text{A}$	--	0.64	0.8	Ω
Input Capacitance	C_g	$f=1.0\text{MHz}$	--	5.0	--	Ω
Input Capacitance	C_{iss}	$V_{\text{DS}}=25\text{V}, V_{\text{GS}}=0\text{V}, f=1.0\text{MHz}$	--	1390	--	pF
Output Capacitance	C_{oss}		--	156	--	
Reverse Transfer Capacitance	C_{rss}		--	15	--	
Turn-on Delay Time	$t_{\text{d}(\text{on})}$	$V_{\text{DD}}=325\text{V}, I_{\text{D}}=12\text{A}, V_{\text{GS}}=10\text{V}, R_{\text{G}}=24\Omega$	--	26	--	ns
Turn-on Rise Time	t_r		--	46	--	
Turn-off Delay Time	$t_{\text{d}(\text{off})}$		--	82	--	
Turn-off Fall Time	t_f		--	42	--	
Total Gate Charge	Q_g	$V_{\text{DS}}=520\text{V}, I_{\text{D}}=12\text{A}, V_{\text{GS}}=10\text{V}$	--	33	--	nC
Gate-Source Charge	Q_{gs}		--	7.4	--	
Gate-Drain Charge	Q_{gd}		--	14	--	

SOURCE-DRAIN DIODE RATINGS AND CHARACTERISTICS

Characteristics	Symbol	Test conditions	Min.	Typ.	Max.	Unit
Continuous Source Current	I_s	Integral Reverse P-N Junction Diode in the MOSFET	--	--	12	A
Pulsed Source Current	I_{SM}		--	--	48	
Diode Forward Voltage	V_{SD}	$I_s=12\text{A}, V_{\text{GS}}=0\text{V}$	--	--	1.4	V
Reverse Recovery Time	T_{rr}	$I_s=12\text{A}, V_{\text{GS}}=0\text{V},$ $dI_F/dt=100\text{A}/\mu\text{s}$	--	562	--	ns
Reverse Recovery Charge	Q_{rr}		--	5.1	--	μC

Notes:

1. $L=30\text{mH}, I_{\text{AS}}=6.0\text{A}, V_{\text{DD}}=100\text{V}, R_{\text{G}}=25\Omega$, starting temperature $T_J=25^\circ\text{C}$;
2. $V_{\text{DS}}=0\sim400\text{V}, I_{\text{SD}}<12\text{A}, T_J=25^\circ\text{C}$;
3. $V_{\text{DS}}=0\sim480\text{V}$;
4. Pulse Test: Pulse width $\leq300\mu\text{s}$, Duty cycle $\leq2\%$;
5. Essentially independent of operating temperature.



TYPICAL CHARACTERISTICS

Figure 1. On-Region Characteristics




Figure 2. Transfer Characteristics




Figure 3. On-Resistance Variation vs.
Drain Current and Gate Voltage




Figure 4. Body Diode Forward Voltage Variation
vs. Source Current and Temperature




Figure 5. Capacitance Characteristics





Figure 6. Gate Charge Characteristics





TYPICAL CHARACTERISTICS (continued)

Figure 7. Breakdown Voltage Variation vs. Temperature




Figure 8. On-resistance vs. Temperature




Figure 9-1. Max. Safe Operating Area(SVF12N65F)




Figure 9-2. Max. Safe Operating Area(SVF12N65K)




Figure 9-3. Max. Safe Operating Area(SVF12N65S)






Figure 10. Max. Drain Current vs. Case Temperature








TYPICAL TEST CIRCUIT



Gate Charge Test Circuit & Waveform



Resistive Switching Test Circuit & Waveform




Unclamped Inductive Switching Test Circuit & Waveform



PACKAGE OUTLINE

TO-220F-3L


UNIT: mm



SYMBOL	MIN	NOM	MAX
A	4.42	4.70	5.02
A1	2.30	2.54	2.80
A3	2.50	2.76	3.10
b	0.70	0.80	0.90
b2	—	—	1.47
c	0.35	0.50	0.65
D	15.25	15.87	16.25
D1	15.30	15.75	16.30
D2	9.30	9.80	10.30
E	9.73	10.16	10.36
e		2.54BCS	
H1	6.40	6.68	7.00
L	12.48	12.98	13.48
L1	/	/	3.50
ØP	3.00	3.18	3.40
Q	3.05	3.30	3.55

TO-262-3L



UNIT: mm



SYMBOL	MIN	NOM	MAX
A	4.30	4.50	4.70
A1	2.20	---	2.92
b	0.71	0.80	0.90
b2	1.20	---	1.50
c	0.34	---	0.65
c2	1.22	1.30	1.35
D	8.38	---	9.30
E	9.80	10.16	10.54
e		2.54 BSC	
L	12.80	---	14.10
L1	---	---	0.75
L2	1.12	---	1.42



PACKAGE OUTLINE(continued)

TO-263-2L		UNIT: mm																																																						
																																																								
		<table border="1"><thead><tr><th>SYMBOL</th><th>MIN</th><th>NOM</th><th>MAX</th></tr></thead><tbody><tr><td>A</td><td>4.30</td><td>4.57</td><td>4.72</td></tr><tr><td>A1</td><td>0</td><td>0.10</td><td>0.25</td></tr><tr><td>b</td><td>0.71</td><td>0.81</td><td>0.91</td></tr><tr><td>c</td><td>0.30</td><td>---</td><td>0.60</td></tr><tr><td>c2</td><td>1.17</td><td>1.27</td><td>1.37</td></tr><tr><td>D</td><td>8.50</td><td>---</td><td>9.35</td></tr><tr><td>E</td><td>9.80</td><td>---</td><td>10.45</td></tr><tr><td>e</td><td colspan="3">2.54BSC</td></tr><tr><td>H</td><td>14.70</td><td>---</td><td>15.75</td></tr><tr><td>L</td><td>2.00</td><td>2.30</td><td>2.74</td></tr><tr><td>L1</td><td>1.12</td><td>1.27</td><td>1.42</td></tr><tr><td>L2</td><td>---</td><td>---</td><td>1.75</td></tr></tbody></table>			SYMBOL	MIN	NOM	MAX	A	4.30	4.57	4.72	A1	0	0.10	0.25	b	0.71	0.81	0.91	c	0.30	---	0.60	c2	1.17	1.27	1.37	D	8.50	---	9.35	E	9.80	---	10.45	e	2.54BSC			H	14.70	---	15.75	L	2.00	2.30	2.74	L1	1.12	1.27	1.42	L2	---	---	1.75
SYMBOL	MIN	NOM	MAX																																																					
A	4.30	4.57	4.72																																																					
A1	0	0.10	0.25																																																					
b	0.71	0.81	0.91																																																					
c	0.30	---	0.60																																																					
c2	1.17	1.27	1.37																																																					
D	8.50	---	9.35																																																					
E	9.80	---	10.45																																																					
e	2.54BSC																																																							
H	14.70	---	15.75																																																					
L	2.00	2.30	2.74																																																					
L1	1.12	1.27	1.42																																																					
L2	---	---	1.75																																																					

Important notice :

- The instructions are subject to change without notice! Customers should obtain the latest relevant information before placing orders and should verify that such information is complete and current.
- Our products are consumer electronic products, and / or civil electronic products.
- When using our products, please do not exceed the maximum rating of the products, otherwise the reliability of the whole machine will be affected. There is a certain possibility of failure or malfunction of any semiconductor product under specific conditions. The buyer is responsible for complying with safety standards and taking safety measures when using our products for system design, sample and whole machine manufacturing, so as to avoid potential failure risk that may cause personal injury or property loss.
- It is strongly recommended to identify the trademark when buying our products. Please contact us if there is any question.
- When exporting, using and reselling our products, buyer must comply with the international export control laws and regulations of China, the United States, the United Kingdom, the European Union and other countries & regions.
- Product promotion is endless, our company will wholeheartedly provide customers with better products!
- Website: <http://www.silan.com.cn>



Part No.: **SVF12N65F/K/S** Document Type: **Datasheet**
Copyright: **HANGZHOU SILAN MICROELECTRONICS CO.,LTD** Website: **<http://www.silan.com.cn>**

Rev.: **3.0**

Revision History:

1. Update the package outline of TO-262-3L
 2. Update Electrical schematic and typical test circuit
-

Rev.: **2.9**

Revision History:

1. Delete the package outline of TO-220-3L
-

Rev.: **2.8**

Revision History:

1. Modify the Electrical characteristics
-

Rev.: **2.7**

Revision History:

1. Revise the hazardous substance control of TO-262-3L from halogen free to Pb free
-

Rev.: **2.6**

Revision History:

1. Add the ordering information
-

Rev.: **2.5**

Revision History:

1. Modify the package information of TO-220F-3L; Modify the package information of TO-220-3L
-

Rev.: **2.4**

Revision History:

1. Modify the thermal characteristics
-

Rev.: **2.3**

Revision History:

1. Modify the ordering information
-

Rev.: **2.2**

Revision History:

1. Add the pin No.
-

Rev.: **2.1**

Revision History:

1. Modify the ordering information
 1. Change the schematic diagram of MOS
-

Rev.: **1.9**

Revision History:

1. Modify "PACKAGE OUTLINE"
-

Rev.: **1.8**

Revision History:

1. Modify "TYPICAL CHARACTERISTICS (continued)"
-



Rev.: 1.7

Revision History:

1. Add the package of TO-263-2L
-

Rev.: 1.6

Revision History:

1. Add the package of TO-262-3L
-

Rev.: 1.5

Revision History:

1. Modify the typ. Value of $R_{DS(on)}$
 1. Modify the values of T_{rr} and Q_{rr}
-

Rev.: 1.3

Revision History:

1. Add the halogen free information of SVF12N65F
-

Rev.: 1.2

Revision History:

1. Modify "ELECTRICAL CHARACTERISTICS" and the capacitance characteristic curve
-

Rev.: 1.1

Revision History:

1. Modify "PACKAGE OUTLINE"
 1. Original
-